

Bandpass Filter

Maximum Ratings

Pin Connections

Outline Drawing



Note: Please refer to case style drawing for details


Demo Board MCL P/N: TB-500+
Suggested PCB Layout (PL-294)



1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B,
DIELECTRIC THICKNESS: .030"±.002"; COPPER: 1/2 OZ EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



Features


- High rejection
- Good VSWR, 1.3:1 typ @ passband
- Shielded case
- Aqueous washable

Applications


- Receivers / transmitters
- Wireless communication systems

Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	σ			
0.5	75.17	2.99	0.00	105.0	22.71
70.0	50.00	1.11	0.15	110.0	17.94
87.0	35.58	4.91	0.53	115.0	15.36
90.0	20.97	2.27	0.79	120.0	13.76
93.0	11.31	1.32	1.56	125.0	12.69
95.0	6.55	0.86	3.07	130.0	11.93
97.0	3.52	0.43	6.44	135.0	11.52
99.0	2.09	0.16	12.18	138.0	11.35
105.0	1.19	0.02	16.74	140.0	11.32
138.0	0.70	0.02	21.71	145.0	11.34
180.0	1.38	0.05	19.36	150.0	11.58
188.0	2.62	0.20	12.94	155.0	11.95
192.0	6.52	0.76	4.97	160.0	12.56
195.0	12.89	1.09	2.34	162.0	12.88
200.0	27.70	1.49	1.21	168.0	14.24
201.0	31.52	1.70	1.12	170.0	14.86
220.0	45.26	1.10	0.58	175.0	17.10
750.0	73.96	8.40	0.48	180.0	20.64



Notes

- A.** Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B.** Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C.** The rights covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCJStore/terms.htm.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com



Generic photo used for illustration purposes only
CASE STYLE: HU1186

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Surface Mount Band Pass Filter

BPF-C138+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	75.19	75.15	74.80	0.01	0.01	0.00	0.00	0.00	0.01
10	49.64	49.67	49.67	0.02	0.01	0.01	0.03	0.03	0.04
20	45.15	45.17	45.08	0.00	0.01	0.00	0.04	0.06	0.08
30	44.85	44.87	44.87	0.01	0.01	0.02	0.11	0.16	0.19
40	48.86	49.06	49.25	0.02	0.03	0.03	0.23	0.28	0.32
50	73.18	72.72	70.38	0.03	0.04	0.04	0.37	0.42	0.45
60	53.41	53.67	53.73	0.07	0.09	0.09	0.44	0.52	0.58
70	48.11	47.40	46.93	0.14	0.17	0.18	0.51	0.61	0.71
80	34.05	33.98	33.98	0.29	0.33	0.36	0.68	0.81	0.95
87	34.85	33.40	31.81	0.59	0.65	0.72	1.03	1.21	1.39
90	19.47	18.88	18.23	0.93	1.04	1.15	1.45	1.73	1.95
93	10.05	9.76	9.42	2.05	2.27	2.53	2.69	3.15	3.57
95	5.68	5.56	5.42	4.07	4.43	4.85	4.84	5.56	6.24
97	3.06	3.10	3.13	7.85	8.32	8.88	8.95	10.00	11.02
99	1.84	1.97	2.06	13.34	13.70	14.18	15.44	16.94	18.55
100	1.54	1.69	1.80	16.34	16.48	16.75	19.79	21.59	23.67
105	1.03	1.16	1.26	19.24	18.88	18.65	21.41	20.98	20.70
110	0.86	0.99	1.07	18.57	18.38	18.21	19.16	19.02	18.85
120	0.69	0.81	0.88	21.65	21.51	21.28	20.36	20.24	19.95
130	0.64	0.73	0.82	21.86	22.25	22.54	20.68	21.03	21.10
138	0.61	0.72	0.79	21.88	22.52	22.89	21.52	22.21	22.36
140	0.61	0.72	0.80	22.30	23.01	23.38	22.13	22.89	23.03
150	0.62	0.74	0.83	29.26	29.01	27.00	28.75	27.63	25.16
160	0.72	0.86	0.97	21.80	21.39	20.62	21.20	20.70	19.79
170	0.95	1.10	1.23	16.57	17.21	17.79	16.78	17.59	18.34
180	1.29	1.53	1.72	18.95	19.81	20.52	20.91	22.61	24.40
188	3.40	4.08	4.70	8.53	8.05	7.68	10.29	9.87	9.48
190	5.75	6.66	7.49	4.76	4.61	4.52	5.86	5.78	5.66
192	9.52	10.59	11.55	2.69	2.74	2.79	3.43	3.54	3.59
195	17.11	18.32	19.36	1.43	1.57	1.68	1.87	2.07	2.18
200	35.19	36.67	37.75	0.87	0.99	1.10	1.09	1.26	1.36
201	40.57	41.60	42.01	0.82	0.95	1.05	1.01	1.18	1.28
210	38.94	39.31	39.69	0.59	0.67	0.76	0.63	0.76	0.83
220	49.02	49.92	50.70	0.47	0.56	0.61	0.46	0.56	0.62
230	58.88	58.34	57.76	0.45	0.51	0.56	0.38	0.48	0.51
240	52.95	53.18	53.19	0.40	0.46	0.49	0.30	0.39	0.42
250	55.14	55.78	55.93	0.37	0.44	0.48	0.26	0.35	0.39
260	62.77	63.70	64.65	0.38	0.44	0.46	0.21	0.30	0.33
270	66.31	65.81	64.36	0.37	0.43	0.46	0.18	0.27	0.31
280	56.82	56.35	56.55	0.35	0.41	0.45	0.16	0.25	0.29
290	52.48	52.72	52.65	0.34	0.41	0.44	0.15	0.22	0.27
300	50.62	50.59	50.57	0.38	0.44	0.47	0.14	0.22	0.27
310	49.40	49.38	49.48	0.37	0.44	0.47	0.13	0.20	0.25
320	48.80	48.76	48.81	0.35	0.42	0.46	0.12	0.20	0.24
330	48.63	48.44	48.49	0.35	0.42	0.47	0.11	0.18	0.23
340	48.57	48.53	48.63	0.34	0.41	0.46	0.09	0.17	0.21
350	48.62	48.64	48.59	0.36	0.43	0.48	0.09	0.17	0.21
400	51.03	50.90	50.88	0.32	0.40	0.46	0.05	0.14	0.18
450	54.64	54.61	54.55	0.30	0.40	0.46	0.03	0.13	0.18
500	59.44	59.41	59.68	0.28	0.39	0.46	0.03	0.13	0.17
550	67.71	66.95	68.11	0.29	0.42	0.49	0.03	0.14	0.18
600	80.83	81.68	92.97	0.30	0.43	0.51	0.03	0.15	0.19
650	68.72	68.48	71.10	0.33	0.48	0.57	0.04	0.16	0.23
700	65.36	65.79	66.23	0.34	0.51	0.60	0.05	0.18	0.23
750	64.76	65.58	66.53	0.37	0.55	0.65	0.06	0.20	0.25

REV. X1

BPF-C138+

091217

Page 1 of 2



Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

BPF-C138+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
105	22.80	22.48	22.14
106	21.49	21.30	21.01
108	19.40	19.19	19.06
110	17.76	17.65	17.47
112	16.83	16.74	16.61
113	16.32	16.21	16.08
114	15.84	15.71	15.62
115	15.40	15.26	15.21
116	15.02	14.90	14.83
118	14.37	14.25	14.18
120	13.79	13.72	13.62
122	13.31	13.25	13.17
123	13.08	13.07	12.99
124	12.94	12.87	12.82
125	12.76	12.74	12.69
126	12.59	12.56	12.52
128	12.31	12.23	12.19
130	12.06	12.05	11.99
132	11.84	11.80	11.79
133	11.72	11.75	11.73
134	11.66	11.69	11.64
135	11.60	11.61	11.59
136	11.55	11.59	11.58
137	11.55	11.55	11.55
138	11.50	11.50	11.49
140	11.44	11.45	11.43
142	11.43	11.45	11.43
143	11.49	11.45	11.46
144	11.48	11.51	11.50
145	11.47	11.48	11.50
146	11.55	11.55	11.55
147	11.54	11.55	11.54
148	11.55	11.60	11.62
150	11.75	11.76	11.73
152	11.85	11.86	11.88
153	11.95	11.97	11.96
154	12.08	12.05	12.05
155	12.14	12.11	12.15
156	12.26	12.27	12.27
158	12.46	12.50	12.50
160	12.73	12.79	12.77
162	13.09	13.09	13.15
163	13.25	13.27	13.32
164	13.40	13.48	13.53
165	13.62	13.70	13.78
166	13.90	13.97	14.05
168	14.37	14.52	14.60
170	15.01	15.17	15.27
172	15.79	15.99	16.16
173	16.25	16.48	16.66
174	16.81	17.03	17.24
175	17.35	17.61	17.87
176	18.03	18.32	18.59
178	19.66	19.99	20.28
180	21.77	22.23	22.56

REV. X1
BPF-C138+
091217
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE




Typical Performance Curves




Outline Dimensions

HU1186



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1186	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	- -	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	- -	.060 (1.52)	.060 (1.52)	- -	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf





INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M119979	NEW RELEASE (FROM RAVON)	11/08	DK	HH
OR	R74463	NEW RELEASE (FROM RAVON)	11/08	DK	HH

**SUGGESTED MOUNTING CONFIGURATION FOR
HU1186 CASE STYLE, "14FL03" PIN CODE**



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B, DIELECTRIC THICKNESS: .030" $\pm$.002"; COPPER: 1/2 OZ ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$ 

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 14FL03, HU1186, BPF-C
TB-500+ (50 OHM)

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-294



REV:
OR

FILE: 98PL294

SCALE: 3:1

SHEET: 1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.5, Thickness=.030 inch.

Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D