

Coaxial

Voltage Controlled Oscillator

ZX95-975-S+

Linear Tuning 900 to 975 MHz

Features

- Linear tuning characteristics
- Low phase noise
- Low pulling
- Low pushing
- Protected by US patent 6,790,049

Applications

- R&D
- LAB
- Instrumentation
- Wireless communications
- Line for receiver
- Defence systems
- Land mobile
- GSM



Generic photo used for illustration purposes only
CASE STYLE: GB956

Connectors	Model
SMA	ZX95-975-S+

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @12 dB @ 12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER				
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)		PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)		Typ.	Typ.			Max.	Typ.	Typ.	Vcc (volts)	Current (mA)
									Min.	Max.												
ZX95-975-S+	900	975	+0.8	-90	-114	-135	-154	0.5	14	8	35	70	-90	-25	-15	0.3	0.3	5	40			

Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	6V
Absolute Max. Tuning Voltage (Vtune)	16V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note [AN-40-10](#).

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.08	1.00	.50	.35	.18	.106	grams
30.48	19.15	11.61	30.07	1.02	9.53	9.53	14.43	4.62	8.31	5.28	5.59	2.03	25.40	12.70	8.89	4.57	2.69	35.0

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp









Performance Data & Curves*

ZX95-975-S+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 939 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	8.49	883.8	880.0	877.2	1.71	0.69	-0.88	33.24	-27.7	-27.0	-37.2	0.10	0.47	-87.6	-112.9	-134.1	-153.5	1.0	-88.80
0.50	7.80	888.0	884.3	881.5	1.70	0.70	-0.86	33.23	-27.6	-27.0	-36.9	0.09	0.49	-88.0	-112.2	-135.3	-154.0	2.0	-98.04
1.00	7.61	891.9	888.2	885.4	1.69	0.71	-0.85	33.23	-27.4	-26.9	-36.5	0.09	0.49	-90.1	-114.4	-135.4	-153.9	3.5	-104.02
2.50	7.78	903.4	899.6	896.9	1.68	0.74	-0.81	33.22	-26.4	-26.3	-36.7	0.11	0.46	-89.5	-114.5	-135.5	-153.3	6.0	-109.50
3.00	7.88	907.3	903.5	900.7	1.69	0.76	-0.80	33.22	-26.1	-26.5	-36.8	0.12	0.43	-90.1	-114.5	-135.5	-154.0	8.5	-113.14
3.50	7.97	911.2	907.4	904.7	1.69	0.77	-0.78	33.22	-25.9	-26.0	-36.7	0.14	0.40	-90.2	-114.3	-135.6	-154.1	10.0	-114.21
4.00	8.05	915.2	911.4	908.6	1.70	0.77	-0.77	33.22	-26.0	-26.0	-36.2	0.15	0.36	-88.7	-114.4	-135.4	-153.9	20.8	-121.19
4.50	8.12	919.2	915.4	912.7	1.71	0.78	-0.77	33.22	-25.8	-26.1	-36.7	0.17	0.31	-89.6	-114.4	-135.4	-154.2	35.5	-126.07
5.50	8.22	927.3	923.6	920.8	1.73	0.77	-0.77	33.22	-25.5	-26.1	-37.0	0.20	0.21	-90.3	-114.3	-135.5	-154.5	60.7	-130.43
6.00	8.27	931.5	927.7	924.9	1.74	0.76	-0.78	33.22	-25.3	-26.0	-37.2	0.21	0.15	-90.1	-114.2	-135.4	-153.5	86.7	-133.90
6.50	8.30	935.6	931.8	929.0	1.75	0.76	-0.79	33.22	-24.8	-25.9	-37.1	0.23	0.10	-90.5	-114.2	-135.1	-154.4	100.0	-135.17
7.00	8.33	939.7	936.0	933.1	1.76	0.74	-0.80	33.22	-24.9	-25.7	-37.6	0.24	0.04	-90.0	-114.2	-135.3	-154.2	148.1	-138.51
7.50	8.34	943.9	940.1	937.3	1.76	0.73	-0.82	33.22	-24.6	-25.6	-37.2	0.26	0.02	-89.9	-113.8	-135.1	-154.5	177.0	-139.99
8.50	8.32	952.3	948.5	945.6	1.74	0.69	-0.87	33.22	-24.5	-25.6	-38.7	0.29	0.14	-90.4	-113.2	-134.7	-154.4	211.6	-141.57
9.50	8.20	960.6	956.8	954.0	1.70	0.65	-0.93	33.23	-24.2	-25.6	-39.5	0.34	0.25	-90.5	-113.3	-134.5	-154.3	302.4	-144.66
10.00	8.10	964.7	960.9	958.1	1.68	0.63	-0.95	33.22	-24.1	-25.5	-39.2	0.36	0.30	-89.2	-113.0	-134.6	-153.7	361.5	-145.90
11.00	7.81	972.7	968.9	966.2	1.64	0.61	-0.98	33.23	-24.0	-25.7	-39.3	0.41	0.38	-90.4	-113.3	-134.8	-154.3	507.5	-149.41
12.00	7.43	980.4	976.6	973.9	1.59	0.61	-0.99	33.23	-23.7	-25.7	-40.0	0.45	0.43	-89.0	-113.0	-134.4	-154.3	606.7	-150.78
13.50	6.76	991.3	987.4	984.7	1.55	0.60	-1.01	33.24	-23.9	-25.9	-41.1	0.48	0.47	-89.2	-112.9	-134.6	-154.7	851.6	-153.20
14.00	6.53	994.7	990.8	988.1	1.55	0.61	-1.01	33.24	-23.8	-25.8	-40.7	0.48	0.47	-89.3	-113.0	-134.4	-155.2	1000.0	-154.27

*at 25°C unless mentioned otherwise



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

