

# Surface Mount Bandpass Filter

50Ω 60 to 90 MHz


## Maximum Ratings

|                                                                 |                |
|-----------------------------------------------------------------|----------------|
| Operating Temperature                                           | -40°C to 85°C  |
| Storage Temperature                                             | -55°C to 100°C |
| RF Power Input                                                  | 0.5W Max.      |
| Permanent damage may occur if any of these limits are exceeded. |                |

## Pin Connections

|               |                                  |
|---------------|----------------------------------|
| INPUT         | 2                                |
| OUTPUT        | 9                                |
| NOT CONNECTED | 6, 13                            |
| GROUND        | 1, 3, 4, 5, 7, 8, 10, 11, 12, 14 |

## Outline Drawing




## Outline Dimensions (inch/mm)

|  | A     | B     | C    | D    | E    | G    | H    | J    | K     | M    | N    | wt.   |
|--|-------|-------|------|------|------|------|------|------|-------|------|------|-------|
|  | .870  | .800  | .25  | .100 | .097 | .060 | .040 | .105 | .910  | .060 | .060 | grams |
|  | 22.10 | 20.32 | 6.35 | 2.54 | 2.46 | 1.52 | 1.02 | 2.67 | 23.11 | 1.52 | 1.52 | 2.85  |


Note: Please refer to case style drawing for details

## Demo Board MCL P/N: TB-500+ Suggested PCB Layout (PL-294)



### NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B, DIELECTRIC THICKNESS: .030"±.002"; COPPER: 1/2 OZ EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

BPF-C75+



Generic photo used for illustration purposes only  
CASE STYLE: HU1186

## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Features

- High rejection
- Good VSWR, 1.2:1 typ @ passband
- Shielded case
- Aqueous washable


## Applications

- Industrial microwave and RF
- Receivers / transmitters
- Harmonic rejection


## Bandpass Filter Electrical Specifications (T<sub>AMB</sub> = 25°C)

| CENTER FREQ. (MHz) | PASSBAND (MHz)<br>(Loss < 3dB)  | STOPBANDS (MHz) |                |                |                | VSWR (:1) |      |          |
|--------------------|---------------------------------|-----------------|----------------|----------------|----------------|-----------|------|----------|
|                    |                                 | Loss > 20dB     |                | Loss > 40dB    |                | Passband  |      | Stopband |
| F <sub>c</sub>     | F <sub>1</sub> - F <sub>2</sub> | F <sub>3</sub>  | F <sub>4</sub> | F <sub>5</sub> | F <sub>6</sub> | Typ.      | Max. | Typ.     |
| 75                 | 60 - 90                         | 46              | 102            | 42             | 108 - 1800     | 1.2       | 1.6  | 18       |

## Typical Frequency Response





## Functional Schematic



## Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) |          | Return Loss (dB) | Frequency (MHz) | Group Delay (nSec) |
|-----------------|---------------------|----------|------------------|-----------------|--------------------|
|                 | $\bar{x}$           | $\sigma$ |                  |                 |                    |
| 0.5             | 79.67               | 1.09     | 0.01             | 60.0            | 40.28              |
| 42.0            | 63.82               | 3.90     | 0.41             | 62.0            | 35.98              |
| 46.0            | 37.45               | 5.83     | 0.59             | 64.0            | 32.52              |
| 53.0            | 11.02               | 3.22     | 3.86             | 66.0            | 30.64              |
| 55.0            | 5.30                | 2.56     | 5.74             | 68.0            | 29.36              |
| 57.0            | 2.41                | 1.17     | 10.55            | 70.0            | 28.50              |
| 60.0            | 1.06                | 0.16     | 19.07            | 72.0            | 26.84              |
| 66.0            | 0.83                | 0.05     | 25.39            | 74.0            | 27.19              |
| 75.0            | 0.95                | 0.04     | 19.29            | 75.0            | 27.77              |
| 80.0            | 1.10                | 0.05     | 24.31            | 76.0            | 28.24              |
| 90.0            | 2.09                | 0.09     | 26.65            | 78.0            | 28.76              |
| 93.0            | 4.17                | 0.46     | 12.07            | 80.0            | 29.98              |
| 95.0            | 8.13                | 0.86     | 5.05             | 82.0            | 30.52              |
| 97.0            | 14.22               | 0.93     | 3.53             | 84.0            | 32.29              |
| 102.0           | 30.02               | 1.06     | 1.07             | 86.0            | 35.19              |
| 108.0           | 51.30               | 1.66     | 0.67             | 87.0            | 37.89              |
| 500.0           | 61.34               | 5.48     | 0.31             | 88.0            | 38.39              |
| 1800.0          | 49.59               | 0.61     | 0.85             | 90.0            | 45.97              |



# Surface Mount Band Pass Filter

**BPF-C75+**

## Typical Performance Data

| FREQ.<br>(MHz) | INSERTION LOSS<br>(dB) |          |          | INPUT RETURN LOSS<br>(dB) |          |          | OUTPUT RETURNLOSS<br>(dB) |          |          |
|----------------|------------------------|----------|----------|---------------------------|----------|----------|---------------------------|----------|----------|
|                | @ -40° C               | @ +25° C | @ +85° C | @ -40° C                  | @ +25° C | @ +85° C | @ -40° C                  | @ +25° C | @ +85° C |
| 0.5            | 78.24                  | 78.14    | 77.80    | 0.00                      | 0.00     | 0.00     | 0.00                      | 0.01     | 0.01     |
| 10             | 54.52                  | 54.55    | 54.50    | 0.00                      | 0.01     | 0.00     | 0.03                      | 0.05     | 0.06     |
| 20             | 59.90                  | 59.67    | 60.01    | 0.01                      | 0.02     | 0.02     | 0.15                      | 0.18     | 0.21     |
| 30             | 57.98                  | 57.99    | 58.19    | 0.04                      | 0.05     | 0.05     | 0.30                      | 0.33     | 0.35     |
| 40             | 61.89                  | 61.61    | 61.54    | 0.11                      | 0.12     | 0.14     | 0.39                      | 0.44     | 0.49     |
| 42             | 63.96                  | 63.85    | 64.56    | 0.14                      | 0.15     | 0.17     | 0.41                      | 0.47     | 0.53     |
| 46             | 40.96                  | 40.54    | 40.21    | 0.22                      | 0.24     | 0.27     | 0.49                      | 0.57     | 0.64     |
| 50             | 23.73                  | 23.52    | 23.40    | 0.39                      | 0.42     | 0.47     | 0.71                      | 0.79     | 0.86     |
| 52             | 16.69                  | 16.52    | 16.47    | 0.62                      | 0.68     | 0.74     | 0.99                      | 1.07     | 1.15     |
| 53             | 13.35                  | 13.21    | 13.17    | 0.87                      | 0.94     | 1.02     | 1.26                      | 1.35     | 1.44     |
| 54             | 10.18                  | 10.05    | 10.03    | 1.32                      | 1.42     | 1.52     | 1.73                      | 1.85     | 1.95     |
| 55             | 7.27                   | 7.16     | 7.15     | 2.14                      | 2.29     | 2.44     | 2.58                      | 2.75     | 2.89     |
| 56             | 4.82                   | 4.74     | 4.74     | 3.61                      | 3.85     | 4.09     | 4.07                      | 4.33     | 4.56     |
| 57             | 3.01                   | 2.96     | 2.99     | 6.07                      | 6.46     | 6.85     | 6.55                      | 6.98     | 7.37     |
| 58             | 1.89                   | 1.89     | 1.94     | 9.84                      | 10.48    | 11.12    | 10.31                     | 11.01    | 11.74    |
| 60             | 1.06                   | 1.12     | 1.20     | 24.51                     | 26.91    | 29.14    | 23.88                     | 26.79    | 31.27    |
| 66             | 0.81                   | 0.87     | 0.94     | 22.28                     | 22.84    | 23.79    | 25.14                     | 26.47    | 28.48    |
| 70             | 0.80                   | 0.87     | 0.95     | 21.10                     | 20.61    | 20.20    | 22.50                     | 22.01    | 21.40    |
| 75             | 0.89                   | 0.97     | 1.07     | 17.95                     | 17.41    | 16.81    | 18.12                     | 17.51    | 16.75    |
| 80             | 0.96                   | 1.04     | 1.14     | 22.48                     | 22.29    | 22.09    | 22.23                     | 21.88    | 21.28    |
| 85             | 1.19                   | 1.29     | 1.41     | 26.01                     | 25.30    | 24.35    | 24.73                     | 23.93    | 22.64    |
| 90             | 1.82                   | 1.98     | 2.17     | 26.75                     | 27.16    | 27.32    | 23.53                     | 22.26    | 20.76    |
| 93             | 3.82                   | 4.18     | 4.53     | 8.85                      | 8.56     | 8.42     | 8.33                      | 7.93     | 7.64     |
| 95             | 7.94                   | 8.46     | 8.94     | 3.92                      | 3.87     | 3.89     | 3.36                      | 3.28     | 3.24     |
| 97             | 13.78                  | 14.33    | 14.83    | 2.25                      | 2.30     | 2.37     | 1.65                      | 1.68     | 1.71     |
| 100            | 23.19                  | 23.70    | 24.16    | 1.56                      | 1.62     | 1.70     | 0.92                      | 0.97     | 1.02     |
| 102            | 29.52                  | 30.01    | 30.44    | 1.39                      | 1.45     | 1.52     | 0.75                      | 0.80     | 0.85     |
| 105            | 39.29                  | 39.79    | 40.17    | 1.24                      | 1.30     | 1.37     | 0.61                      | 0.67     | 0.72     |
| 108            | 49.76                  | 50.24    | 50.67    | 1.14                      | 1.19     | 1.25     | 0.54                      | 0.59     | 0.64     |
| 110            | 57.02                  | 57.61    | 57.85    | 1.08                      | 1.13     | 1.19     | 0.51                      | 0.56     | 0.60     |
| 120            | 61.36                  | 61.28    | 61.46    | 0.84                      | 0.90     | 0.95     | 0.43                      | 0.47     | 0.51     |
| 130            | 61.97                  | 62.29    | 62.17    | 0.70                      | 0.75     | 0.79     | 0.39                      | 0.43     | 0.46     |
| 140            | 77.56                  | 78.04    | 77.65    | 0.63                      | 0.66     | 0.71     | 0.37                      | 0.41     | 0.43     |
| 150            | 63.35                  | 63.17    | 63.47    | 0.60                      | 0.62     | 0.66     | 0.35                      | 0.39     | 0.41     |
| 160            | 58.41                  | 58.40    | 58.39    | 0.59                      | 0.61     | 0.64     | 0.34                      | 0.38     | 0.40     |
| 170            | 56.29                  | 56.39    | 56.26    | 0.60                      | 0.61     | 0.64     | 0.32                      | 0.37     | 0.40     |
| 180            | 55.45                  | 55.45    | 55.46    | 0.61                      | 0.62     | 0.65     | 0.31                      | 0.36     | 0.40     |
| 190            | 55.17                  | 55.19    | 55.31    | 0.63                      | 0.64     | 0.67     | 0.31                      | 0.36     | 0.39     |
| 200            | 55.38                  | 55.45    | 55.47    | 0.65                      | 0.66     | 0.69     | 0.30                      | 0.36     | 0.39     |
| 300            | 62.80                  | 62.93    | 62.55    | 0.69                      | 0.77     | 0.83     | 0.25                      | 0.33     | 0.37     |
| 400            | 69.91                  | 70.24    | 69.39    | 0.74                      | 0.83     | 0.91     | 0.24                      | 0.33     | 0.38     |
| 500            | 68.51                  | 68.52    | 67.78    | 0.79                      | 0.90     | 0.99     | 0.25                      | 0.35     | 0.41     |
| 600            | 73.46                  | 74.48    | 75.38    | 0.85                      | 0.99     | 1.08     | 0.26                      | 0.38     | 0.45     |
| 700            | 92.55                  | 85.35    | 89.07    | 0.93                      | 1.08     | 1.19     | 0.28                      | 0.42     | 0.49     |
| 800            | 74.07                  | 74.10    | 73.34    | 1.00                      | 1.18     | 1.30     | 0.30                      | 0.46     | 0.54     |
| 900            | 66.00                  | 66.07    | 66.46    | 1.07                      | 1.26     | 1.41     | 0.33                      | 0.50     | 0.58     |
| 1000           | 62.06                  | 63.40    | 64.44    | 1.14                      | 1.34     | 1.50     | 0.38                      | 0.56     | 0.65     |
| 1100           | 73.60                  | 77.55    | 75.87    | 1.17                      | 1.38     | 1.55     | 0.41                      | 0.61     | 0.70     |
| 1200           | 75.93                  | 73.30    | 71.71    | 1.19                      | 1.39     | 1.56     | 0.45                      | 0.66     | 0.77     |
| 1300           | 87.59                  | 69.05    | 72.41    | 1.16                      | 1.37     | 1.54     | 0.49                      | 0.71     | 0.83     |
| 1400           | 77.35                  | 75.44    | 80.30    | 1.11                      | 1.33     | 1.49     | 0.52                      | 0.76     | 0.89     |
| 1500           | 73.60                  | 70.80    | 68.96    | 1.06                      | 1.27     | 1.42     | 0.55                      | 0.81     | 0.96     |
| 1600           | 69.10                  | 70.12    | 72.88    | 1.01                      | 1.23     | 1.37     | 0.57                      | 0.85     | 1.03     |
| 1700           | 61.63                  | 64.44    | 64.13    | 0.98                      | 1.18     | 1.31     | 0.60                      | 0.89     | 1.09     |
| 1800           | 69.56                  | 68.70    | 64.90    | 0.95                      | 1.16     | 1.29     | 0.62                      | 0.91     | 1.14     |

REV. X1

BPF-C75+

091124

Page 1 of 2



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

**Mini-Circuits®**

# Surface Mount Band Pass Filter

# BPF-C75+

## Typical Performance Data

| FREQ.<br>(MHz) | GROUP DELAY<br>(nsec) |          |          |
|----------------|-----------------------|----------|----------|
|                | @ -40° C              | @ +25° C | @ +85° C |
| 60.0           | 52.11                 | 51.57    | 51.16    |
| 61.0           | 46.56                 | 46.09    | 45.73    |
| 62.0           | 42.37                 | 42.03    | 41.74    |
| 63.0           | 39.30                 | 39.06    | 38.80    |
| 63.5           | 38.04                 | 37.86    | 37.70    |
| 64.0           | 37.01                 | 36.88    | 36.74    |
| 64.5           | 36.10                 | 35.98    | 35.88    |
| 65.0           | 35.24                 | 35.18    | 35.10    |
| 65.5           | 34.55                 | 34.46    | 34.44    |
| 66.0           | 33.91                 | 33.85    | 33.83    |
| 66.5           | 33.33                 | 33.27    | 33.25    |
| 67.0           | 32.80                 | 32.77    | 32.75    |
| 67.5           | 32.34                 | 32.32    | 32.30    |
| 68.0           | 31.96                 | 31.89    | 31.93    |
| 68.5           | 31.49                 | 31.43    | 31.43    |
| 69.0           | 31.14                 | 31.09    | 31.10    |
| 69.5           | 30.82                 | 30.79    | 30.77    |
| 70.0           | 30.49                 | 30.44    | 30.44    |
| 70.5           | 30.23                 | 30.18    | 30.14    |
| 71.0           | 29.97                 | 29.96    | 29.87    |
| 71.5           | 29.73                 | 29.67    | 29.62    |
| 72.0           | 29.50                 | 29.48    | 29.41    |
| 72.5           | 29.30                 | 29.28    | 29.21    |
| 73.0           | 29.17                 | 29.13    | 29.10    |
| 73.5           | 29.06                 | 29.03    | 28.98    |
| 74.0           | 28.97                 | 28.95    | 28.89    |
| 74.5           | 28.90                 | 28.87    | 28.81    |
| 75.0           | 28.88                 | 28.89    | 28.82    |
| 75.5           | 28.88                 | 28.90    | 28.84    |
| 76.0           | 28.95                 | 28.96    | 28.92    |
| 76.5           | 29.02                 | 29.01    | 29.00    |
| 77.0           | 29.11                 | 29.11    | 29.14    |
| 77.5           | 29.28                 | 29.31    | 29.30    |
| 78.0           | 29.44                 | 29.49    | 29.50    |
| 78.5           | 29.62                 | 29.70    | 29.69    |
| 79.0           | 29.88                 | 29.93    | 29.98    |
| 79.5           | 30.17                 | 30.21    | 30.32    |
| 80.0           | 30.46                 | 30.54    | 30.63    |
| 80.5           | 30.77                 | 30.87    | 30.95    |
| 81.0           | 31.14                 | 31.25    | 31.34    |
| 81.5           | 31.52                 | 31.63    | 31.75    |
| 82.0           | 31.91                 | 32.07    | 32.21    |
| 82.5           | 32.37                 | 32.52    | 32.65    |
| 83.0           | 32.85                 | 33.03    | 33.15    |
| 83.5           | 33.34                 | 33.56    | 33.66    |
| 84.0           | 33.92                 | 34.09    | 34.23    |
| 84.5           | 34.48                 | 34.67    | 34.83    |
| 85.0           | 35.14                 | 35.35    | 35.48    |
| 85.5           | 35.81                 | 36.04    | 36.21    |
| 86.0           | 36.60                 | 36.81    | 36.95    |
| 86.5           | 37.45                 | 37.69    | 37.87    |
| 87.0           | 38.48                 | 38.74    | 38.93    |
| 88.0           | 40.90                 | 41.24    | 41.49    |
| 89.0           | 44.24                 | 44.71    | 45.07    |
| 90.0           | 48.76                 | 49.34    | 49.81    |

REV. X1  
BPF-C75+  
091124  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



## Typical Performance Curves



REV. X1

BPF-C75+

091124

Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Outline Dimensions

HU1186



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE#  | A               | B               | C             | D              | E              | F | G              | H              | J              | K               | L | M              | N              | P | WT, GRAM |
|--------|-----------------|-----------------|---------------|----------------|----------------|---|----------------|----------------|----------------|-----------------|---|----------------|----------------|---|----------|
| HU1186 | .870<br>(22.10) | .800<br>(20.32) | .25<br>(6.35) | .100<br>(2.54) | .097<br>(2.46) | - | .060<br>(1.52) | .040<br>(1.02) | .105<br>(2.67) | .910<br>(23.11) | - | .060<br>(1.52) | .060<br>(1.52) | - | 2.85     |

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

### Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F21



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel |
|-------------------|----------------------------|----------------------|------------------|
| 32                | 32                         | 13                   | 200              |



Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661  
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010  
Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION              | DATE  | DR | AUTH |
|-----|---------|--------------------------|-------|----|------|
| OR  | M119979 | NEW RELEASE (FROM RAVON) | 11/08 | DK | HH   |
| OR  | R74463  | NEW RELEASE (FROM RAVON) | 11/08 | DK | HH   |
|     |         |                          |       |    |      |
|     |         |                          |       |    |      |

**SUGGESTED MOUNTING CONFIGURATION FOR  
HU1186 CASE STYLE, "14FL03" PIN CODE**



## NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B, DIELECTRIC THICKNESS: .030"  $\pm$  .002"; COPPER: 1/2 OZ ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, 14FL03, HU1186, BPF-C  
TB-500+ (50 OHM)

SIZE  
A

CODE IDENT  
15542

DRAWING NO:  
98-PL-294

REV:  
OR



FILE: 98PL294

SCALE: 3:1

SHEET: 1 OF 1



# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.  
Dielectric Constant=3.5, Thickness=.030 inch.

Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                 | Test/Inspection Condition                                                                                                 | Reference/Spec                                |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|
| Operating Temperature         | -40° to 85° C<br>Ambient Environment                                                                                      | Individual Model Data Sheet                   |
| Storage Temperature           | -65° to 150° C<br>Ambient Environment                                                                                     | Individual Model Data Sheet                   |
| Autoclave                     | 15 psig, 100% RH, 121°C, 96 hours                                                                                         | JESD22-A102-C, Condition C                    |
| Temperature Cycling           | -65° to 150°C, 100 cycles                                                                                                 | JESD22-A104                                   |
| Temperature Humidity          | 85°C/ 85% RH, 168 hours                                                                                                   | JESD22-113                                    |
| Solder Reflow Heat            | Sn-Pb Eutetic Process: 240°C peak<br>Pb-Free Process: 260°C peak                                                          | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours<br>Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS) | J-STD-020                                     |
| Solderability                 | 10X magnification, 95% coverage                                                                                           | JESD22-B102, Method 1: Dip and Look Test      |
| Mechanical Shock              | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                         | MIL-STD-202, Method 213, Condition A          |
| Vibration (High Frequency)    | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                       | MIL-STD-202, Method 204, Condition D          |