



Mini-Circuits

MMIC WIDEBAND

Gain Equalizer

EQY-15-24+

50Ω 6 to 20 GHz

THE BIG DEAL

- 15.7 dB Slope
- Small Package 2.5 x 2.5 mm 8L MCLP
- Wide Bandwidth, 6-20 GHz
- Excellent Return Loss, 20 dB typ.

APPLICATIONS

- Fixed Satellite
- Mobile
- Military Systems
- ELINT
- EW
- ECM



Generic photo used for illustration purposes only

CASE STYLE: JV3002

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

PRODUCT OVERVIEW

Mini-Circuits EQY-15-24+ is a MMIC gain equalizer fabricated using highly repeatable GaAs IPD MMIC process incorporating resistors, capacitors and inductors to accomplish a positive attenuation slope vs. Frequency. EQY-15-24+ has a nominal attenuation slope of 15.7dB and can be applied to compensate for the negative gain slope of amplifiers to achieve relative gain flatness for the overall system. It is packaged in a tiny 2.5x 2.5mm, 8-Lead MCLP package .

KEY FEATURES

Feature	Advantages
Positive Attenuation Slope vs. Frequency	Positive Attenuation Slope vs. Frequency
Wideband Operation, 6 to 20 GHz	Supports a wide variety of applications including wireless cellular, microwave communications, satellite, defense and aerospace, medical and optical applications.
Excellent Power Handling Capability	Enables the product to be used at the output of an amplifier.
Small Size and simple to use (2.5 mm x 2.5 mm)	As a single chip solution, the EQY-15-24+ Series occupies less board space than a lumped element approach, minimizes component count and ensures repeatable performance over wide frequency range.

*GaAs IPD (Gallium Arsenide Integrated Passive Device)



**ELECTRICAL SPECIFICATIONS¹ AT 25°C, 50Ω, UNLESS OTHERWISE NOTED.**

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		6		20	GHz
Insertion Loss	6	15.3	17.0	18.6	dB
	10	9.7	10.9	11.9	
	14	4.8	5.6	6.0	
	18	-	2.2	-	
	20	-	1.3	-	
VSWR	6 - 10	-	1.22	-	:1
	10 - 14	-	1.19	-	
	14 - 18	-	1.25	-	
	18 - 20	-	1.22	-	

1. Measured on Mini-Circuits Characterization Test Board TB-EQY-15-24+. See Characterization Test Circuit (Fig. 1)

MAXIMUM RATINGS²

Parameter	Ratings
Operating Case Temperature	-55°C to 105°C
Storage Temperature	-65°C to 150°C
RF Input Power ³	31 dBm

2. Permanent damage may occur if any of these limits are exceeded.

3. Derates linearly to 22 dBm at 105°C




Mini-Circuits

MMIC WIDEBAND

Gain Equalizer


EQY-15-24+

SIMPLIFIED SCHEMATIC



PAD DESCRIPTION

TOP VIEW



CHARACTERIZATION TEST CIRCUIT





Fig 1. Block Diagram of Test Circuit used for characterization.
Test Board TB-EQY-15-24+. Condition: Attenuation & Return
Loss Pin =0dBm

Function	Pad Number	Description
RF-IN	2	Input Pad
RF-OUT	6	Output Pad
NC	4,8	No Connection Connects to ground on TB
GND	1,3,5,7 & Paddle	Ground

PRODUCT MARKING



Marking may contain other features or characters for internal lot control




ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S3P Files) Data Set (.zip file)
Case Style	JV3002 Plastic package, exposed paddle, lead finish: Matt Tin
Tape & Reel Standard quantities available on reel	TR-F68 7" reels with 20, 50, 100, 200, 500 or 1K devices
Suggested Layout for PCB Design	PL-718
Evaluation Board	TB-EQY-15-24+ (Without Connectors) TB-EQY-15-24C+ (With Connectors)
Environmental Ratings	ENV129

ESD RATING

Human Body Model (HBM): Class 1C (Pass 1000V) in accordance with ANSI/ESD STM 5.1 - 2001 Machine.

MSL TEST FLOW CHART



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT VSWR			OUTPUT VSWR		
(MHz)	(dB)			(:1)			(:1)		
	@-55°C	@25°C	@+105°C	@-55°C	@25°C	@+105°C	@-55°C	@25°C	@+105°C
10	23.19	23.13	23.11	1.20	1.21	1.21	1.19	1.20	1.20
20	23.20	23.14	23.12	1.18	1.18	1.19	1.16	1.18	1.18
30	23.20	23.14	23.12	1.17	1.18	1.18	1.16	1.17	1.17
40	23.20	23.14	23.12	1.17	1.18	1.18	1.15	1.17	1.17
50	23.20	23.15	23.13	1.17	1.18	1.18	1.15	1.17	1.17
60	23.20	23.14	23.12	1.17	1.17	1.18	1.15	1.17	1.17
70	23.21	23.15	23.13	1.17	1.17	1.18	1.15	1.16	1.17
80	23.20	23.15	23.13	1.17	1.17	1.18	1.15	1.16	1.17
90	23.20	23.15	23.13	1.17	1.17	1.18	1.15	1.16	1.17
100	23.20	23.15	23.13	1.17	1.17	1.18	1.15	1.16	1.17
1000	23.01	22.97	22.95	1.22	1.22	1.22	1.22	1.22	1.22
2000	22.33	22.29	22.27	1.27	1.28	1.29	1.29	1.29	1.30
3000	21.31	21.26	21.23	1.27	1.27	1.28	1.28	1.27	1.29
4000	20.04	19.98	19.94	1.22	1.21	1.20	1.21	1.19	1.18
5000	18.59	18.53	18.50	1.13	1.12	1.11	1.09	1.09	1.08
6000	17.06	17.01	16.98	1.04	1.05	1.06	1.07	1.08	1.08
7000	15.55	15.52	15.48	1.18	1.19	1.18	1.20	1.19	1.18
8000	14.05	14.01	13.97	1.30	1.29	1.28	1.29	1.26	1.25
9000	12.47	12.42	12.38	1.30	1.27	1.25	1.25	1.22	1.21
10000	10.86	10.84	10.80	1.14	1.11	1.09	1.10	1.08	1.06
11000	9.36	9.35	9.32	1.06	1.08	1.09	1.08	1.09	1.10
12000	8.01	8.01	7.99	1.23	1.23	1.24	1.22	1.22	1.21
13000	6.81	6.80	6.76	1.40	1.37	1.35	1.38	1.34	1.32
14000	5.59	5.59	5.54	1.46	1.42	1.37	1.46	1.39	1.35
15000	4.38	4.41	4.39	1.30	1.28	1.24	1.28	1.25	1.22
16000	3.38	3.43	3.44	1.18	1.14	1.14	1.11	1.07	1.08
17000	2.63	2.71	2.74	1.21	1.22	1.22	1.16	1.20	1.18
18000	2.21	2.30	2.31	1.45	1.43	1.38	1.45	1.45	1.39
19000	1.80	1.82	1.83	1.39	1.25	1.18	1.48	1.35	1.29
20000	1.38	1.50	1.56	1.20	1.20	1.22	1.33	1.31	1.32
21000	1.40	1.57	1.62	1.58	1.51	1.43	1.62	1.54	1.48
22000	1.37	1.67	1.80	1.42	1.49	1.48	1.43	1.48	1.47
23000	1.70	1.99	2.25	1.64	1.59	1.68	1.58	1.51	1.60
24000	2.48	2.80	2.98	2.00	1.92	1.90	1.80	1.79	1.76
25000	3.17	3.61	3.66	2.12	2.12	1.96	2.01	2.03	1.89
26000	3.94	4.09	4.23	2.34	2.11	2.00	2.34	2.11	2.02



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com






IF/RF MICROWAVE COMPONENTS

REV. OR
EQY-15-24+
12/2/2021
Page 1 of 1



Outline Dimensions

JV3002



BOTTOM VIEW

SUGGESTED LAYOUT
FOR PCB LAND PATTERN
PATTERN TO BE WITHIN ±.002

 METALLIZATION

CASE #	A	B	C	D	E	F	G	H	J	K	L	M
JV3002	.098 (2.50)	.098 (2.50)	.035 (.90)	.010 (.25)	.007 (.18)	.047 (1.20)	.043 (1.10)	.049 (1.25)	.037 (.95)	.012 (.30)	.014 (.35)	.010 (.25)

CASE #	N	P	Q	R	S	T	U	V	W	Y	Z	WEIGHT (GRAMS)
JV3002	.014 (.35)	.118 (3.01)	.118 (3.01)	.014 (.35)	.037 (.95)	.047 (1.20)	.010 (.25)	.024 (.60)	.035 (.90)	.043 (1.10)	.012 (.30)	0.016

Dimensions are in inches (mm). Tolerances: 3 Pl. ±.002[.050]

Notes:

1. Open style, Plastic.
2. Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Matte-Tin plate.
3. Pad tolerance is non-cumulative. Minimum spacing between each pad is .004.
4. Pin numbers do not appear on unit. For reference only.

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
 minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-010217	NEW RELEASE	10/20/21	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR JV3002 CASE STYLE




NOTES:

- TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066 \pm .0007$ "; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS LINE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm .003$ ANGLES $\pm$ FRACTIONS $\pm$

INITIALS

DATE

DRAWN

ITG

10/20/21

CHECKED

GF

10/20/21

APPROVED

IL

10/20/21



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, JV3002, TB-EQY-15-24+

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-718

REV:
OR

FILE: 98PL718

SCALE: 10:1

SHEET: 1 OF 1


Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit

SEE DETAIL "A"




INDEX



DUT

DETAIL "A"
(SCALE 5:1)



SCHEMATIC DIAGRAM
(SCALE 5:1)

Function	Pad
RF-IN	2
RF-OUT	6
GND	1,3,5,7
NOT USED	4,8


Notes:

1. PCB Material: Roger R04350B or equivalent,
Dielectric constant=3.5, Thickness=0.0066 inch


 Mini-Circuits®

Evaluation Board and Circuit

SEE DETAIL "A"




INDEX



DUT

DETAIL "A"
(SCALE 5:1)



SCHEMATIC DIAGRAM
(SCALE 5:1)

Function	Pad
RF-IN	2
RF-OUT	6
GND	1,3,5,7
NOT USED	4,8

Notes:

- 2.4mm Female Connectors.
- PCB Material: Roger R04350B or equivalent,
Dielectric constant=3.5, Thickness=0.0066 inch

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Temperature Cycling	-65° C to 150°C, 500 cycles Dwell Time: 10 min	JESD22-A104E, Test Condition C
Autoclave	29.7 psia, 100% RH, 121°C, 96 Hours	JESD22-A102E, Test Condition C
HAST	150°C, 168 Hours	JESD22-A103E, Test Condition B
Solderability (Dip&Look Method)	SnAgCu Solder Pot: 245°C, Steam: 93°C, 8 Hours	JESD22-B102E, Method 1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020E, Level 1