




High Pass Filter

HFCU-1382+


50Ω 14.3 to 29 GHz

THE BIG DEAL

- Insertion Loss, 2.4 dB Typ.
- Good Rejection, 53 dB Typ.
- Good Return Loss, 14 dB Typ.
- 1812 Surface Mount Footprint
- Power Handling: 7 Watts

*Generic photo used for illustration purposes only***APPLICATIONS**

- Test & Measurement Equipment
- Radar, EW, and ECM Defense System
- 5G MIMO and Back Haul Radio

FUNCTIONAL DIAGRAM**PRODUCT OVERVIEW**

Mini-Circuits' HFCU-1382+ is a miniature low temperature co-fired ceramic (LTCC) high pass filter with a 14.3 to 29 GHz passband supporting a variety of applications. This model provides 2.4 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in an 1812 ceramic form factor which is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Wide passband, 14.7 GHz	This filter has a very wide passband from 14.3 to 29 GHz.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Small size, 1812	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Rugged Power handling, 7 Watts	Handles up to 7 Watts in a small 1812 package.



LTCC SURFACE MOUNT

High Pass Filter

HFCU-1382+

50Ω 14.3 to 29 GHz

ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Pass Band	Insertion Loss	F4-F5	14.3 - 17	—	2.3	—	dB
		F5-F6	17 - 26	—	2.4	3.1	
		F6-F7	26 - 29	—	3.0	—	
	Return Loss	F4-F5	14.3 - 17	—	12	—	dB
		F5-F6	17 - 26	—	14	—	
		F6-F7	26 - 29	—	11	—	
Stop Band	Rejection	DC-F1	DC - 8	43	53	—	dB
		F1-F2	8 - 10.8	20	32	—	
	Freq. Cut-Off ⁴	F3	13.5	—	3.0	—	dB

1. Tested in Evaluation Board P/N TB-HFCU-1382+.

2. Bi-directional, RF1 and RF2 ports can be interchanged.

3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

4. Typical variation $\pm 5\%$.ABSOLUTE MAXIMUM RATINGS⁵

Parameter	Ratings
Operating Temperature	-55 °C to +125 °C
Storage Temperature	-55 °C to +125 °C
Input Power ⁶	7W @25°C

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1.3 W at +125°C.

TYPICAL FREQUENCY RESPONSE




Figure 1. Typical Frequency Response



LTCC SURFACE MOUNT





High Pass Filter

HFCU-1382+

Mini-Circuits

50 Ω 14.3 to 29 GHz

TYPICAL PERFORMANCE GRAPHS





Mini-Circuits

LTCC SURFACE MOUNT

High Pass Filter

HFCU-1382+

50Ω 14.3 to 29 GHz

FUNCTIONAL DIAGRAM





Figure 2. HFCU-1382+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1 (Note 2)	1	Connects to RF Input Port
RF2 (Note 2)	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-708)
NC	—	No connection, not used internally. See drawing PL-708 for connection to PCB

SUGGESTED PCB LAYOUT (PL-708)




NOTES:

- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04835 Lo Pro) WITH DIELECTRIC THICKNESS .0073±.0007; COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 ■ DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

Figure 3. PL-708 Suggested PCB Layout

CASE STYLE DRAWING



Weight: .04 grams

Dimensions are in inches [mm]. Tolerances: 2Pl. ± .01; 3Pl. ± .005

Figure 4. NM1812C-5 Case Style Drawing

PRODUCT MARKING*: F518

*Marking may contain other features or characters for internal lot control.



Mini-Circuits

LTCC SURFACE MOUNT

High Pass Filter

HFCU-1382+

50Ω 14.3 to 29 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD.

[CLICK HERE](#)

Performance Data and Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	NM1812C-5 Lead Finish: Electroless Nickel-Gold
RoHs Status	Compliant
Tape and Reel	TR-F77
Suggested Layout for PCB Design	PL-708
Evaluation Board	TB-HFCU-1382+
	Gerber File
Environmental Rating	ENV6T10

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html








Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	96.29	97.88	96.75	0.02	0.04	0.05	0.02	0.05	0.05
100	89.27	91.46	91.83	0.00	0.03	0.05	0.01	0.03	0.04
300	82.25	84.84	85.50	0.03	0.06	0.09	0.01	0.04	0.07
500	78.86	81.29	81.87	0.06	0.10	0.13	0.01	0.06	0.10
700	76.60	78.71	79.19	0.07	0.12	0.15	0.01	0.07	0.10
900	74.72	76.70	77.00	0.08	0.13	0.16	0.00	0.07	0.11
1100	73.19	75.03	75.24	0.08	0.14	0.16	0.01	0.07	0.10
1300	71.99	73.67	73.91	0.08	0.14	0.17	0.02	0.06	0.09
1500	70.79	72.42	72.60	0.08	0.14	0.16	0.03	0.04	0.08
1700	69.84	71.35	71.50	0.07	0.13	0.16	0.05	0.02	0.06
2000	68.45	69.90	70.02	0.06	0.12	0.15	0.07	0.00	0.04
2500	66.50	67.82	67.94	0.01	0.08	0.11	0.13	0.05	0.01
3000	64.87	66.09	66.27	0.04	0.03	0.06	0.20	0.12	0.06
3500	63.58	64.70	64.87	0.11	0.03	0.02	0.26	0.16	0.10
4000	62.57	63.60	63.83	0.15	0.06	0.01	0.30	0.20	0.12
4500	61.83	62.65	62.78	0.17	0.07	0.01	0.31	0.19	0.11
5000	60.83	61.69	61.85	0.15	0.04	0.03	0.30	0.17	0.08
5500	60.09	60.58	60.80	0.11	0.01	0.09	0.27	0.14	0.04
6000	59.10	59.41	59.68	0.07	0.06	0.15	0.25	0.10	0.01
6500	57.87	58.33	58.33	0.03	0.11	0.21	0.23	0.07	0.05
7000	56.61	56.92	56.88	0.01	0.13	0.23	0.24	0.08	0.04
7500	54.97	55.17	55.05	0.02	0.13	0.24	0.25	0.08	0.05
8000	52.83	52.91	52.63	0.00	0.15	0.26	0.22	0.05	0.07
8500	50.54	50.54	50.33	0.02	0.18	0.29	0.20	0.03	0.10
9000	47.51	47.36	46.97	0.04	0.20	0.31	0.18	0.01	0.13
9500	44.05	43.71	43.31	0.07	0.23	0.34	0.16	0.02	0.16
10000	40.03	39.53	39.06	0.12	0.30	0.42	0.13	0.07	0.21
10800	32.33	31.54	30.93	0.26	0.50	0.67	0.01	0.26	0.44
11800	20.91	20.01	19.08	0.80	1.15	1.46	0.55	0.92	1.28
12600	11.03	10.28	9.51	1.97	2.56	3.17	1.78	2.42	3.07
13500	2.78	2.85	2.95	11.85	14.87	17.35	11.73	14.78	17.10
14300	1.69	2.00	2.25	16.14	16.39	16.38	16.16	16.25	15.99
14500	1.60	1.90	2.14	17.28	18.44	19.16	17.22	18.12	18.33
14700	1.51	1.82	2.07	20.66	22.73	23.78	20.54	21.90	21.63
14900	1.45	1.78	2.04	24.84	23.99	22.04	24.42	22.54	20.19
15100	1.44	1.79	2.07	20.19	18.52	16.95	19.81	17.83	16.15
15300	1.49	1.85	2.14	15.71	14.90	13.98	15.33	14.39	13.43
15500	1.56	1.92	2.20	13.21	12.87	12.40	12.83	12.40	11.92
15700	1.62	1.97	2.23	11.87	11.81	11.70	11.52	11.37	11.27
16000	1.64	1.96	2.20	11.41	11.67	12.03	11.01	11.19	11.58
16500	1.48	1.78	2.00	14.04	14.94	16.33	13.53	14.32	15.65
17000	1.29	1.62	1.86	24.03	28.72	33.38	22.33	24.56	25.68
17500	1.26	1.62	1.89	23.59	20.99	19.65	21.76	19.58	18.46
18000	1.31	1.67	1.93	17.93	17.79	18.13	16.77	16.71	17.06
18500	1.32	1.65	1.91	19.41	21.66	24.69	17.84	19.71	21.71
19000	1.29	1.64	1.92	33.86	34.27	25.58	24.83	25.68	23.07
19500	1.35	1.72	2.02	20.50	19.43	17.83	19.25	18.53	17.20
20000	1.44	1.79	2.06	16.14	16.96	17.62	15.45	16.31	17.12
20500	1.41	1.75	1.99	17.55	19.59	23.45	16.92	18.96	23.01
21000	1.35	1.71	1.99	26.40	28.98	26.26	24.75	27.23	25.57
21500	1.37	1.75	2.03	22.48	21.91	20.98	21.19	20.97	20.36
22000	1.40	1.78	2.05	19.30	20.39	23.34	18.36	19.51	22.50
22500	1.40	1.77	2.06	24.25	27.91	36.71	22.25	25.34	30.48
23000	1.40	1.80	2.11	31.56	26.89	22.74	26.40	24.57	21.90
23500	1.44	1.84	2.14	21.66	21.31	22.13	20.56	20.27	21.46
24000	1.44	1.84	2.14	23.26	24.98	28.11	22.32	24.24	31.26
24500	1.45	1.88	2.22	27.95	24.63	20.64	31.99	25.96	21.42
25000	1.54	1.99	2.32	18.77	17.61	17.16	19.27	17.62	17.15
26000	1.62	2.04	2.35	18.37	19.86	23.48	18.78	20.23	25.56
29000	2.13	2.69	3.07	14.91	13.48	13.80	13.76	12.54	12.80

Typical Performance Data


FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
14300	0.26	0.26	0.26
14650	0.25	0.25	0.25
15000	0.24	0.24	0.23
15350	0.22	0.22	0.22
15700	0.21	0.21	0.21
16050	0.20	0.20	0.20
16400	0.20	0.20	0.20
16750	0.20	0.20	0.20
17000	0.20	0.20	0.20
17450	0.20	0.20	0.20
17800	0.19	0.19	0.19
18150	0.19	0.19	0.19
18500	0.19	0.19	0.19
18850	0.19	0.19	0.19
19250	0.18	0.18	0.18
19600	0.18	0.18	0.18
19950	0.18	0.18	0.18
20300	0.18	0.18	0.18
20650	0.18	0.18	0.18
21050	0.18	0.18	0.18
21400	0.18	0.18	0.18
21750	0.17	0.17	0.18
22100	0.17	0.17	0.18
22450	0.17	0.18	0.18
22800	0.17	0.17	0.18
23150	0.17	0.17	0.17
23500	0.17	0.17	0.17
23850	0.17	0.17	0.18
24200	0.17	0.17	0.18
24550	0.17	0.17	0.18
24900	0.17	0.17	0.17
25250	0.17	0.17	0.17
25600	0.17	0.17	0.17
26000	0.17	0.17	0.18
26300	0.18	0.18	0.18
26650	0.18	0.18	0.18
27000	0.18	0.17	0.18
27500	0.17	0.17	0.18
28000	0.18	0.18	0.18
29000	0.18	0.18	0.18


Typical Performance Curves




Outline Dimensions

NM1812C-5



THIRD ANGLE PROJECTION		REVISIONS					
		REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
		OR	ECO-015456	NEW RELEASE	OCT 22	DDR	VC

SUGGESTED MOUNTING CONFIGURATION
FOR NM1812C-5 CASE STYLE




- NOTES:
- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04835 Lo Pro) WITH DIELECTRIC THICKNESS $.0073 \pm .0007$; COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235			
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ± 	DRAWN	DDR	20 OCT 22						
	CHECKED	GTP	20 OCT 22						
	APPROVED	RKS	20 OCT 22						
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.						PL DWG NM1812C-5 C.S 50 OHM HFHK			
		SIZE A	CODE IDENT 15542		DRAWING NO: 98-PL-708		REV: OR		
		FILE: 98-PL-708		SCALE: 9:1		SHEET: 1 OF 1			
		ASHEETA1.DWG REV:A DATE:01/12/95							

Evaluation Board and Circuit

TB-HFCU-1382+



Notes:

1. PCB Material: ROGERS (R04835 Lo Pro) OR Equivalent, Dielectric Constant= $3.48 \pm .05$
Dielectric Thickness: $.0073 \pm .0007$
2. 50 Ohm 2.92mm Female Connectors.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Test B,B1, 95% Coverage
Thermal Shock	-55° to +125°C, 15 min dwell, 250 cycles	MIL-STD-202, Method 107
Bend Test	1mm, deflection for 5 seconds Span of bending: 2.75"	--
High Temp Storage	125°C to 1000 Hrs	---