



Mini-Circuits

COAXIAL

Adapter

KMR-24F+

50Ω DC to 40 GHz Right-Angle 2.4 mm-Female to 2.92 mm-Male

THE BIG DEAL

- Ultra-Wideband, DC to 40 GHz
- Low Insertion Loss, 0.16 dB Typ.
- Excellent VSWR, 1.09:1 Typ.
- Flat response



Generic photo used for illustration purposes only

APPLICATIONS

- Interconnection of RF cable and equipment

Model No.	KMR-24F+
Case Style	DJ2442-9
Connectors	Right Angle 2.4 mm F to 2.92 mm M

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

PRODUCT OVERVIEW

Mini-Circuits' KMR-24F+ is a right-angle 2.4 mm-F to 2.92 mm-M adapter supporting a wide range of applications from DC to 40 GHz. This model provides excellent VSWR, low insertion loss, and flat response versus frequency. The KMR-24F+ features passivated stainless steel construction and gold-plated berillium copper construction center contact.

KEY FEATURES

Features	Advantages
Right-Angle adapter	Converts 2.4 F to K-connector (Right-Angle) in one unit saving space and cost
Wideband, DC to 40 GHz	Wide frequency range provides application flexibility and makes this model ideal for broadband and multi-band use.
Excellent VSWR, 1.09:1 typ.	Provides good matching for 50Ω systems and minimizes signal reflections across wide frequency range.
Low insertion loss, 0.16 dB typ.	Provides excellent signal power transmission from input to output.
Passivated stainless steel construction and gold-plated berillium copper center contact	Stands up to wear and tear in demanding environments and provides excellent reliability.
Very wide operating temperature range, -55 to +100 °C	Withstands extreme operating conditions and is suitable for use near high power componentry where heat rise is common.





ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Units
Frequency Range	-	DC	-	40	GHz
Insertion Loss	DC - 40	-	0.16	0.4	dB
VSWR	DC - 40	-	1.09	1.29	:1

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.



COAXIAL

Adapter

KMR-24F+


Mini-Circuits

50Ω DC to 40 GHz Right-Angle 2.4 mm-Female to 2.92 mm-Male

COAXIAL CONNECTIONS

Connector 1	2.4 mm -Female
Connector 2	2.92 mm -Male

OUTLINE DRAWING



Weight: 6 grams
Dimensions are in inches [mm]



COAXIAL



Adapter

KMR-24F+

50Ω DC to 40 GHz Right-Angle 2.4 mm-Female to 2.92 mm-Male

TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	
		2.4mm-Female	2.92mm-Male
10	0.01	1.01	1.01
100	0.01	1.01	1.00
500	0.03	1.01	1.02
1000	0.05	1.02	1.02
2000	0.07	1.01	1.02
3000	0.10	1.02	1.01
5000	0.14	1.08	1.08
7000	0.13	1.11	1.11
10000	0.13	1.06	1.03
15000	0.14	1.06	1.01
20000	0.17	1.07	1.03
25000	0.18	1.05	1.03
30000	0.24	1.18	1.12
33000	0.23	1.09	1.15
35000	0.25	1.10	1.09
38000	0.24	1.18	1.14
40000	0.21	1.06	1.07



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Right Angle Adapter, 2.92mm Male to 2.4mm Female KMR-24F+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	2.92mm-MALE VSWR (:1)	2.4mm-FEMALE VSWR (:1)
0.01	0.01	1.01	1.01
0.05	0.01	1.00	1.00
0.1	0.01	1.01	1.00
0.2	0.02	1.01	1.01
0.3	0.02	1.01	1.01
0.4	0.03	1.01	1.01
0.5	0.03	1.01	1.02
0.6	0.04	1.01	1.02
0.7	0.04	1.02	1.02
0.8	0.04	1.02	1.02
0.9	0.05	1.02	1.02
1.0	0.05	1.02	1.02
2.0	0.07	1.01	1.02
3.0	0.10	1.02	1.01
4.0	0.13	1.05	1.04
5.0	0.14	1.08	1.08
6.0	0.14	1.11	1.11
7.0	0.13	1.11	1.11
8.0	0.13	1.10	1.09
9.0	0.13	1.08	1.05
10.0	0.13	1.06	1.03
11.0	0.13	1.04	1.02
12.0	0.13	1.04	1.02
13.0	0.13	1.04	1.03
14.0	0.14	1.05	1.03
15.0	0.14	1.06	1.01
16.0	0.14	1.06	1.02
17.0	0.15	1.04	1.05
18.0	0.15	1.02	1.05
19.0	0.16	1.03	1.03
20.0	0.17	1.07	1.03
21.0	0.18	1.12	1.10
22.0	0.20	1.15	1.16
23.0	0.20	1.15	1.16
24.0	0.20	1.11	1.11
25.0	0.18	1.05	1.03
26.0	0.19	1.04	1.06
28.0	0.22	1.16	1.19
30.0	0.24	1.18	1.12
32.0	0.24	1.15	1.13
34.0	0.23	1.00	1.13
36.0	0.27	1.18	1.11
38.0	0.24	1.18	1.14
40.0	0.21	1.06	1.07
42.0	0.21	1.17	1.07
43.0	0.21	1.20	1.04
43.5	0.21	1.20	1.02





P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
KMR-24F+
11/6/2019
Page 1 of 1

Typical Performance Curves




Case Style

Outline Dimensions

DJ

DJ2442-9



Weight: 6 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.030 ; 3 Pl. ± 0.015

Notes:

1. Case material: Stainless Steel..
2. Finish: Passivation.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I