


Ultra High Dynamic Range

Monolithic Amplifier Die

PHA-1H-D+

50Ω 0.05 to 6 GHz



The Big Deal

- Ultra High IP3
- Broadband High Dynamic Range without external Matching Components

Product Overview

PHA-1H-D+ (RoHS compliant) is an advanced wideband amplifier die fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PHA-1H-D+ has good input and output return loss over a broad frequency range without the need for external matching components and has demonstrated excellent reliability.

Key Features

Feature	Advantages
Broad Band: 0.05 to 6.0 GHz	Broadband covering primary wireless communications bands: Cellular, PCS, LTE, WiMAX
Extremely High IP3 Versus DC power Consumption 40.4 dBm typical at 2GHz	The PHA-1H-D+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being typically 20 dB above the P 1dB point. This feature makes this amplifier ideal for use in: • Driver amplifiers for complex waveform up converter paths • Drivers in linearized transmit systems • Secondary amplifiers in ultra High Dynamic range receivers
No External Matching Components Required	Mini-Circuits' PHA-1H-D+ provides good Input and Output Return Loss of 10-23 dB up to 4 GHz without the need for any external matching components
Low Noise Figure: 2.6dB typ. up to 4 GHz 3.4dB typ. up to 6 GHz	A unique feature of the PHA-1H-D+ which separates this design from all competitors is the low noise figure performance in combination with the high IP3 resulting in high dynamic range.
Low Junction Temperature T _j =115°C at 85°C lead temperature and 135°C at 105°C lead temperature	Results in excellent reliability*

* Measured in industry standard SOT-89 package.



Ultra High Dynamic Range Monolithic Amplifier Die

PHA-1H-D+

50Ω 0.05 to 6 GHz

Product Features


- High IP3, 40.4 dBm typ. at 2.4 GHz
- Gain, 13.8 dB typ. at 2 GHz
- High Pout, P1dB 22 dBm typ. at 2 GHz
- Low noise figure, 2.2 dB @2 GHz
- No external matching components required

Typical Applications

- Base station infrastructure
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- LTE

General Description


PHA-1H-D+ (RoHS compliant) is an advanced wideband amplifier die fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PHA-1H-D+ has good input and output return loss over a broad frequency range without the need for external matching components and has low thermal resistance.



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Simplified Schematic and Pad description



Pad#	Function	Description
1	RF-IN	RF input pad. This pad requires the use of an external DC blocking capacitor chosen for the frequency of operation
3	RF-OUT & DC-IN	RF output pad and bias pad. DC voltage is present on this pad, therefore, a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection.
2,4	GND	Connections to ground. Bottom of die.

Note: 1. Bond Pad material - Gold
2. Bottom of Die - Gold plated

Bonding Pad Position



Dimensions in μm, Typical

L1	L2	L3	L4	L5	H1	H2	H3	H4	H5	Thickness	Bond pad size
86	156	453	479	750	85	114	422	444	530	750	75 X 75



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M167172
PHA-1H-D+
MCL NY
180428
Page 2 of 5

Electrical Specifications at 25°C, unless noted

Parameter	Condition (GHz)	Vd=5.0V ¹			Units
		Min.	Typ.	Max.	
Frequency range		0.05		6.0	GHz
Gain	0.05		17.7		dB
	0.8		15.9		
	2.0		13.8		
	3.0		12.1		
	4.0		10.9		
	6.0		9.6		
Input return loss	0.05		11.9		dB
	0.8		18.2		
	2.0		12.5		
	3.0		10.8		
	4.0		10.3		
	6.0		8.1		
Output return loss	0.05		14.2		dB
	0.8		22.9		
	2.0		19.7		
	3.0		17.1		
	4.0		15.5		
	6.0		13.7		
Reverse isolation	2.0		19.6		dB
Output power @ 1 dB compression	0.05		22.1		dBm
	0.8		21.8		
	2.0		22.6		
	3.0		22.2		
	4.0		22.5		
	6.0		22.0		
Output IP3	0.05		39.6		dBm
	0.8		40.6		
	2.0		40.4		
	3.0		40.8		
	4.0		41.4		
	6.0		41.0		
Noise figure	0.5		1.7		dB
	1.0		1.8		
	2.0		2.2		
	3.0		2.4		
	4.0		2.6		
	6.0		3.4		
Device operating voltage		4.8	5.0	5.2	V
Device operating current		—	132	165	mA
Device current variation vs voltage			0.057		mA/mV
Thermal resistance, junction-to-ground lead at 88°C			36.1		°C/W

1. Measured on Mini-Circuits characterization test board TB-313, DUT packaged in industry standard SOT-89 package. See characterization test circuit (Fig. 1)

Absolute Maximum Ratings²

Parameter	Ratings
Operating temperature (ground lead)	-40°C to 105°C
Operating current at 5V	210 mA
Power dissipation	1 W
Input power (CW)	24 dBm
DC voltage on RF-Out pad	6 V

2. Permanent damage may occur if any of these limits are exceeded.
Electrical maximum ratings are not intended for continuous normal operation.

Characterization Test Circuit





Fig 1. Block Diagram of Test Circuit used for characterization. (DUT, Die packaged in SOT-89 package, soldered on Mini-Circuits Characterization test board TB-313)

Gain, Return loss, Output power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm.
- Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

Assembly Diagram



Assembly and Handling Procedure

1. Storage
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD
MMIC E-PHEMT amplifier dice are susceptible to electrostatic and mechanical damage. Dice are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

additional information is available on our dash board.

*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

Human Body Model (HBM): Class 1B (pass 500V) in accordance with ANSI/ESD STM 5.1 - 2001

** Tested in industry standard SOT-89 package.

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 134.69 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.46	23.74	7.35	9.70	0.90	0.69	38.74	22.12	1.85
30	18.68	22.49	9.08	11.45	0.92	0.67	39.26	22.80	1.85
40	18.11	21.81	10.67	13.11	0.96	0.65	39.00	22.96	1.82
50	17.71	21.33	12.10	14.56	0.99	0.63	38.54	22.68	1.76
60	17.42	21.37	13.22	15.96	1.02	0.65	39.62	22.57	1.82
70	17.24	21.13	14.24	16.97	1.04	0.64	39.57	22.73	1.84
80	17.10	21.04	15.11	17.99	1.05	0.63	39.96	22.77	1.84
90	17.00	20.95	15.86	18.82	1.06	0.63	40.62	22.76	1.84
100	16.92	20.89	16.48	19.59	1.07	0.63	40.68	22.96	1.84
200	16.61	20.76	19.79	24.15	1.10	0.63	42.77	22.66	1.80
400	16.39	20.70	20.53	26.61	1.11	0.64	42.99	22.68	2.03
600	16.18	20.57	19.63	26.42	1.12	0.65	43.74	22.75	2.08
800	15.93	20.52	18.38	25.57	1.12	0.67	43.66	22.69	1.98
1000	15.63	20.43	17.17	24.39	1.13	0.69	43.25	22.55	2.07
1200	15.31	20.29	16.02	23.38	1.14	0.71	45.00	22.71	2.10
1400	14.96	20.15	15.06	22.33	1.14	0.73	44.89	22.71	2.13
1600	14.60	20.00	14.26	21.50	1.15	0.75	43.74	22.83	2.19
1800	14.24	19.85	13.58	20.56	1.15	0.77	43.96	22.65	2.25
2000	13.89	19.67	13.03	19.83	1.15	0.79	43.45	22.76	2.24
2200	13.54	19.50	12.60	19.20	1.16	0.81	43.40	22.56	2.29
2400	13.21	19.29	12.23	18.55	1.16	0.82	44.03	22.89	2.32
2600	12.87	19.13	12.04	18.03	1.16	0.84	43.68	22.98	2.37
2800	12.58	18.93	11.81	17.40	1.16	0.85	42.22	22.80	2.51
3000	12.31	18.73	11.57	16.79	1.16	0.85	43.63	22.83	2.49
3200	12.03	18.55	11.52	16.41	1.16	0.86	42.35	23.08	2.53
3400	11.75	18.30	11.31	16.19	1.15	0.87	41.75	22.90	2.60
3600	11.56	18.10	11.09	15.75	1.14	0.87	41.62	22.95	2.68
3800	11.30	17.98	11.04	15.72	1.15	0.88	41.26	22.93	2.72
4000	11.11	17.72	10.66	15.54	1.14	0.88	40.64	22.94	2.80
4200	10.93	17.54	10.41	15.43	1.13	0.89	41.08	22.97	2.90
4400	10.68	17.27	10.02	15.58	1.12	0.90	40.44	22.79	3.02
4600	10.58	17.05	9.59	15.18	1.09	0.90	40.21	22.91	3.00
4800	10.45	16.92	9.29	15.01	1.08	0.91	40.12	22.82	3.10
5000	10.33	16.79	9.00	14.92	1.06	0.92	40.31	23.02	3.21
5200	10.14	16.58	8.73	15.06	1.05	0.93	39.70	22.74	3.21
5400	10.05	16.43	8.53	14.99	1.04	0.94	40.26	22.86	3.28
5600	9.91	16.15	8.22	14.62	1.01	0.94	40.00	22.53	3.36
5800	9.79	15.85	7.99	14.48	0.99	0.94	39.70	22.38	3.42
6000	9.76	15.63	7.95	14.51	0.98	0.94	39.71	22.11	3.51
6200	9.72	15.34	7.77	14.28	0.95	0.93	39.62	22.14	3.53
6400	9.71	15.13	7.61	13.73	0.92	0.93	38.89	21.92	3.63
6600	9.74	14.84	7.53	13.70	0.90	0.91	38.81	21.65	3.70
6800	9.63	14.59	7.20	13.52	0.88	0.91	38.86	21.72	3.79
7000	9.50	14.32	6.98	13.47	0.87	0.91	38.29	21.65	3.93
7200	9.38	14.05	6.52	13.51	0.86	0.91	39.10	21.74	4.09
7400	9.11	13.94	6.06	13.19	0.85	0.92	38.08	21.56	4.20
7600	8.68	13.90	5.51	12.59	0.85	0.95	38.05	21.64	4.41
7800	8.22	13.91	4.92	11.79	0.85	0.99	38.14	21.25	4.67
8000	7.59	13.83	4.62	11.17	0.87	1.00	37.75	21.24	4.89

Note: "Test data of Die packaged in industry standard SOT-89 package"



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 120.33 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.41	23.76	7.23	9.65	0.89	0.70	37.67	21.43	1.79
30	18.64	22.40	8.93	11.35	0.91	0.67	38.68	22.13	1.84
40	18.06	21.80	10.52	12.99	0.96	0.66	38.18	22.28	1.78
50	17.65	21.39	11.96	14.48	0.99	0.64	38.19	22.02	1.73
60	17.36	21.01	13.18	15.88	1.01	0.62	39.04	21.98	1.77
70	17.17	21.02	14.07	16.84	1.03	0.63	39.03	22.07	1.81
80	17.03	20.96	14.94	17.82	1.05	0.63	39.69	22.10	1.80
90	16.93	20.89	15.70	18.68	1.06	0.63	40.38	22.13	1.79
100	16.84	20.81	16.32	19.41	1.06	0.63	39.97	22.30	1.82
200	16.52	20.66	19.62	23.93	1.10	0.63	42.60	22.02	1.78
400	16.31	20.58	20.35	26.22	1.11	0.64	46.42	22.03	1.99
600	16.10	20.53	19.52	25.91	1.12	0.65	44.65	22.14	2.06
800	15.84	20.45	18.30	25.00	1.12	0.67	42.62	22.07	1.98
1000	15.55	20.34	17.10	23.76	1.13	0.69	41.77	21.94	2.02
1200	15.22	20.21	15.97	22.75	1.13	0.71	41.16	22.11	2.08
1400	14.88	20.07	15.00	21.72	1.14	0.73	41.20	22.08	2.07
1600	14.52	19.92	14.20	20.89	1.15	0.75	40.17	22.21	2.13
1800	14.16	19.74	13.54	20.00	1.15	0.77	39.50	21.98	2.22
2000	13.81	19.60	12.98	19.31	1.15	0.79	39.53	22.08	2.18
2200	13.45	19.42	12.58	18.72	1.16	0.81	39.15	21.96	2.27
2400	13.13	19.21	12.20	18.13	1.15	0.82	39.86	22.25	2.28
2600	12.79	19.01	12.03	17.69	1.16	0.83	39.74	22.30	2.35
2800	12.49	18.82	11.79	17.13	1.16	0.84	39.01	22.13	2.48
3000	12.23	18.62	11.57	16.57	1.15	0.85	39.19	22.18	2.47
3200	11.95	18.44	11.52	16.26	1.15	0.86	39.15	22.39	2.48
3400	11.67	18.20	11.31	16.04	1.15	0.86	38.68	22.23	2.58
3600	11.48	17.99	11.10	15.66	1.14	0.87	38.55	22.30	2.59
3800	11.22	17.88	11.05	15.69	1.15	0.88	38.77	22.30	2.73
4000	11.04	17.62	10.69	15.48	1.13	0.88	38.10	22.28	2.79
4200	10.85	17.42	10.42	15.43	1.13	0.89	38.20	22.28	2.85
4400	10.60	17.17	10.05	15.53	1.12	0.90	38.08	22.13	2.99
4600	10.50	16.95	9.63	15.19	1.09	0.90	38.11	22.29	2.97
4800	10.37	16.81	9.33	15.05	1.08	0.91	37.91	22.16	3.08
5000	10.26	16.68	9.04	14.99	1.06	0.92	38.28	22.38	3.14
5200	10.07	16.47	8.78	15.12	1.06	0.93	37.73	22.08	3.18
5400	9.97	16.36	8.58	15.07	1.05	0.94	38.28	22.18	3.24
5600	9.83	16.04	8.26	14.71	1.02	0.94	37.83	21.90	3.32
5800	9.72	15.79	8.04	14.56	0.99	0.94	37.51	21.76	3.41
6000	9.69	15.54	8.00	14.63	0.98	0.93	37.45	21.48	3.48
6200	9.65	15.26	7.83	14.41	0.95	0.93	37.18	21.55	3.50
6400	9.63	15.06	7.68	13.88	0.93	0.92	36.64	21.31	3.59
6600	9.66	14.75	7.60	13.84	0.91	0.91	36.27	21.06	3.64
6800	9.55	14.53	7.27	13.62	0.89	0.91	36.42	21.11	3.75
7000	9.43	14.26	7.04	13.53	0.88	0.91	36.00	21.01	3.91
7200	9.30	14.00	6.57	13.48	0.86	0.90	36.68	21.15	4.02
7400	9.03	13.92	6.12	13.10	0.86	0.92	35.73	20.91	4.15
7600	8.60	13.87	5.57	12.43	0.86	0.94	35.80	21.04	4.34
7800	8.15	13.86	4.96	11.60	0.86	0.97	35.37	20.59	4.60
8000	7.52	13.80	4.66	10.96	0.87	0.99	35.14	20.60	4.84

Note: "Test data of Die packaged in industry standard SOT-89 package"



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)


Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 148.69 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.47	23.72	7.50	9.78	0.90	0.69	37.94	22.56	2.11
30	18.70	22.49	9.23	11.52	0.93	0.66	39.36	23.33	2.05
40	18.13	21.87	10.82	13.20	0.96	0.65	38.78	23.51	2.01
50	17.74	21.39	12.21	14.63	0.99	0.63	38.92	23.26	1.97
60	17.46	21.46	13.51	16.09	1.03	0.65	39.88	23.08	2.00
70	17.28	21.18	14.40	17.10	1.04	0.64	39.76	23.26	2.02
80	17.15	21.08	15.27	18.11	1.05	0.63	40.10	23.29	2.02
90	17.04	21.03	16.02	18.98	1.06	0.63	40.58	23.29	2.01
100	16.97	20.97	16.61	19.75	1.07	0.63	40.71	23.52	2.03
200	16.66	20.80	19.95	24.50	1.10	0.63	42.43	23.20	1.99
400	16.45	20.75	20.63	27.05	1.11	0.64	43.87	23.19	2.20
600	16.24	20.66	19.70	27.04	1.12	0.65	44.26	23.25	2.26
800	15.98	20.58	18.44	26.14	1.12	0.67	46.05	23.20	2.17
1000	15.69	20.48	17.20	24.97	1.13	0.69	44.44	23.05	2.27
1200	15.36	20.38	16.05	23.95	1.14	0.71	46.53	23.24	2.28
1400	15.02	20.21	15.07	22.87	1.14	0.73	46.18	23.21	2.32
1600	14.66	20.09	14.26	22.00	1.15	0.76	45.56	23.36	2.38
1800	14.30	19.94	13.60	21.02	1.16	0.78	45.91	23.17	2.44
2000	13.95	19.74	13.04	20.22	1.16	0.79	43.58	23.30	2.44
2200	13.59	19.59	12.61	19.51	1.16	0.81	45.19	23.11	2.50
2400	13.26	19.37	12.21	18.81	1.16	0.83	44.45	23.47	2.48
2600	12.93	19.23	12.03	18.23	1.17	0.84	43.21	23.52	2.57
2800	12.63	19.01	11.79	17.53	1.16	0.85	42.66	23.33	2.75
3000	12.36	18.80	11.56	16.89	1.16	0.86	43.57	23.36	2.69
3200	12.08	18.64	11.49	16.47	1.16	0.86	42.66	23.58	2.75
3400	11.80	18.41	11.29	16.22	1.16	0.87	41.84	23.42	2.82
3600	11.61	18.19	11.05	15.74	1.15	0.87	41.56	23.48	2.91
3800	11.35	18.10	11.02	15.71	1.16	0.88	41.45	23.45	3.00
4000	11.16	17.83	10.63	15.47	1.14	0.89	41.01	23.43	3.07
4200	10.97	17.64	10.36	15.38	1.13	0.89	41.27	23.43	3.14
4400	10.73	17.35	9.98	15.52	1.12	0.90	40.74	23.26	3.28
4600	10.62	17.14	9.54	15.12	1.09	0.91	40.63	23.41	3.28
4800	10.49	16.99	9.24	14.92	1.08	0.92	40.39	23.28	3.33
5000	10.38	16.89	8.95	14.80	1.06	0.93	40.39	23.50	3.45
5200	10.19	16.68	8.69	14.93	1.05	0.94	40.03	23.20	3.50
5400	10.10	16.52	8.48	14.86	1.04	0.94	40.41	23.34	3.61
5600	9.95	16.19	8.15	14.46	1.01	0.95	39.90	23.00	3.66
5800	9.84	15.94	7.93	14.33	0.99	0.95	39.88	22.85	3.75
6000	9.81	15.71	7.88	14.36	0.97	0.94	39.61	22.55	3.81
6200	9.77	15.39	7.71	14.13	0.94	0.93	39.67	22.61	3.84
6400	9.75	15.18	7.54	13.58	0.92	0.93	38.71	22.36	3.93
6600	9.78	14.89	7.46	13.51	0.90	0.92	38.89	22.12	4.05
6800	9.67	14.65	7.14	13.39	0.88	0.92	39.11	22.15	4.15
7000	9.55	14.36	6.91	13.35	0.86	0.92	38.60	22.07	4.29
7200	9.42	14.09	6.45	13.45	0.85	0.92	39.30	22.21	4.40
7400	9.15	13.97	6.00	13.19	0.85	0.93	38.61	21.98	4.52
7600	8.72	13.95	5.45	12.67	0.85	0.96	38.44	22.12	4.79
7800	8.26	13.92	4.86	11.91	0.84	1.00	38.71	21.70	5.06
8000	7.62	13.85	4.57	11.32	0.86	1.01	38.48	21.53	5.29

Note: "Test data of Die packaged in industry standard SOT-89 package"

Typical Performance Curves



Note: "Test data of Die packaged in industry standard SOT-89 package"



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment	20° to 35° C and 40 to 60% humidity (In Factory Shipped Package)	Individual Model Data Sheet