

Wideband, Positive Gain Slope


Monolithic Amplifier Die

AVA-183P-D+

50Ω 0.5 to 18 GHz

The Big Deal

- Ultra-wideband, 0.5 to 18 GHz
- Positive gain slope
- Single positive supply voltage



Product Overview

The AVA-183P-D+ is a InGaAs E-PHEMT based wideband, positive gain slope MMIC amplifier die. This design operates on a single 5V supply, is well matched for 50Ω. Having a positive gain slope makes the amplifier useful for compensating the negative slope of many wideband passive microwave devices and eliminating the need for equalization.

Key Features

Feature	Advantages
Positive Gain Slope vs. Frequency +0.13 dB/GHz (0.5-10 GHz) +0.25 dB/GHz (10-18 GHz)	Useful for compensating the negative slope of many wideband passive microwave devices and eliminating the need for equalization.
Positive Supply Voltage	Simplifies external circuit by eliminating need for negative voltage and sequencing.
Unpackaged Die	Enables the user to integrate the amplifier directly into hybrids.



Wideband, Positive Gain Slope

Monolithic Amplifier Die

AVA-183P-D+


50Ω 0.5 to 18 GHz

Product Features

- Wideband, 0.5 to 18 GHz
- Positive Gain Slope
- Single Positive Supply Voltage

Typical Applications

- WiFi
- WLAN
- LTE
- WiMAX
- C-band Satcom



+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

General Description


The AVA-183P-D+ is a InGaAs E-PHEMT based wideband, positive gain slope MMIC amplifier die. This design operates on a single 5V supply, is well matched for 50Ω. Having a positive gain slope makes the amplifier useful for compensating the negative slope of many wideband passive microwave devices and eliminating the need for equalization.

Simplified Schematic and Pad description



Pad#	Function
1	RF-IN
4	RF-OUT & DC-IN
2,3,5,6 & bottom of die	GND

Bonding Pad Position



Dimensions in μm, Typical

L1	L2	L3	H1	H2	H3	H4
97	1103	1200	229	379	529	998

Thickness	Die size	Pad Size 1,2,3,4,5&6
100	1200 x 998	89 x 89



Electrical Specifications¹ at 25°C and 5V, unless noted

Parameter	Condition (GHz)	Min.	Typ.	Max.	Unit
Frequency Range		0.5		18	GHz
Gain	0.5		6.8		dB
	5		7.5		
	10		8.1		
	15		9.8		
	18		10.8		
Gain Slope	0.5 - 10		0.13		dB/GHz
	10 - 18		0.25		
Input Return Loss	0.5		15		dB
	5		13		
	10		10		
	15		23		
	18		14		
Output Return Loss	0.5		11		dB
	5		8		
	10		7		
	15		9		
	18		19		
Output Power at 1dB Compression	0.5		10.9		dB
	5		10.6		
	10		11.7		
	15		12.3		
	18		11.6		
OIP3 (P _{out} = -3dBm/Tone)	0.5		22.8		dBm
	5		21.4		
	10		21.5		
	15		20.6		
	18		19.1		
Noise Figure	0.5		7.5		dBm
	5		5.3		
	10		4.8		
	15		4.6		
	18		5.0		
Device Operating Voltage(VDD)		4.75	5	5.25	V
Device Operating Current (IDD)		—	46.3	54	mA
Device Current Variation vs. Temperature ²			-168.13		μA/°C
Device Current Variation vs. Voltage ³			0.0085		mA/mV

1. Die is packaged in 3x3 mm, 12-lead MCLP package & soldered on Mini-Circuits characterization board TB-AVA-183P+. See Characterization Test Circuit (Fig. 1)

2. Current variation vs temperature=(Current at 100°C-Current at -55°C)/155°C

3. Current variation vs Voltage=(Current at 5.25V - Current at 4.75V)/(5.25V-4.75V)

Absolute Maximum Ratings⁴

Parameter	Ratings
Operating Temperature (ground)	-55°C to 100°C
Junction Temperature	161°C
Total Power Dissipation	0.46W ⁵
Input Power (CW), V _{DD} =5V ⁵	+22 dBm (5 minutes max.) +13 dBm (continuous)
DC Voltage	6V

4. Permanent damage may occur if any of these limits are exceeded.

Electrical maximum ratings are not intended for continuous normal operation.

5. Derates linearly to 0.24W at 100°C




Recommended Characterization Test Circuit

Fig 1. Characterization Test Circuit


Note: This block diagram is used for characterization. (DUT is packaged in a 3x3 mm, 12-lead MCLP and soldered on Mini-Circuits Characterization test board TB-AVA-183P+).

Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, -3 dBm/tone at output.

Assembly Diagram



Assembly and Handling Procedure

1. Storage
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD
MMIC E-PHEMT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

Additional Detailed Technical Information <i>additional information is available on our dash board.</i>									
Performance Data	Data Table								
	Swept Graphs								
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)								
Case Style	Die								
Die Ordering and packaging information	<table> <tr> <td>Quantity, Package</td><td>Model No.</td></tr> <tr> <td>Small, Gel - Pak: 5,10,50,100 KGD*</td><td>AVA-183P-DG+</td></tr> <tr> <td>Medium†, Partial wafer: KGD*<1292</td><td>AVA-183P-DP+</td></tr> <tr> <td>Large†, Full Wafer</td><td>AVA-183P-DF+</td></tr> </table> †Available upon request contact sales representative Refer to AN-60-067	Quantity, Package	Model No.	Small, Gel - Pak: 5,10,50,100 KGD*	AVA-183P-DG+	Medium†, Partial wafer: KGD*<1292	AVA-183P-DP+	Large†, Full Wafer	AVA-183P-DF+
Quantity, Package	Model No.								
Small, Gel - Pak: 5,10,50,100 KGD*	AVA-183P-DG+								
Medium†, Partial wafer: KGD*<1292	AVA-183P-DP+								
Large†, Full Wafer	AVA-183P-DF+								
Environmental Ratings	ENV80								

*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

ESD Rating**

Human Body Model (HBM): Class 1A (pass 250V) in accordance with ANSI/ESD STM 5.1 - 2001

** Tested in industry standard 3x3 mm, 12-lead MCLP package.

Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bond ing and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment	20° to 35° C and 40 to 60% humidity (In Factory Shipped Package)	Individual Model Data Sheet