

Surface Mount Bandpass Filter

BPF-BD1400+

50Ω 1200 to 1600 MHz

The Big Deal

- Wide bandwidth
- Rejection upto $2x F_c$
- Miniature shielded package



Generic photo used for illustration purposes only
CASE STYLE: TV2849

Product Overview

The BPF-BD1400+ is a 50Ω bandpass filter fabricated using SMT technology. This bandpass filter covers from 1200-1600 MHz. This filter is built with high Q capacitors and air-coil inductors for superior performance. It has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications such as radio astronomy.
Good rejection	Rejection upto $2x F_c$. This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Shielded case	Reduced interference with and from the surrounding components.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Bandpass Filter

50 Ω 1200 to 1600 MHz

BPF-BD1400+



Features

- Wide bandwidth
- Rejection upto 2x F_c
- Miniature shielded package

Generic photo used for illustration purposes only
CASE STYLE: TV2849

Applications

- Radio telescope applications
- Public cellular networks
- International mobile telecommunication
- Weather instruments / Radar / Satellite
- Transmitter / Receivers
- Harmonic rejection / Industrial applications

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	1400	—	MHz
	Insertion Loss	F1-F2	—	1.5	3.0	dB
	VSWR	F1-F2	—	1.67	2.0	:1
Stop Band, Lower	Rejection	DC-F3	40	50	—	dB
		F3-F4	20	25	—	dB
Stop Band, Upper	Rejection	F5-F6	20	25	—	dB
		F6-F7	40	60	—	dB

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1 W

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	104.35	182.16	1200	4.44
100	81.08	559.87	1220	3.91
700	53.62	80.79	1240	3.61
995	30.09	50.64	1260	3.46
1000	29.48	49.66	1280	3.35
1068	19.96	35.51	1300	3.26
1163	3.07	2.89	1320	3.21
1200	1.26	1.12	1340	3.18
1400	1.16	1.35	1360	3.16
1500	1.21	1.12	1380	3.14
1600	1.62	1.35	1400	3.12
1691	2.95	1.50	1420	3.13
1765	19.94	10.88	1440	3.15
1800	30.21	16.17	1460	3.22
1900	53.51	28.69	1480	3.32
2000	66.66	39.76	1500	3.42
2200	67.22	57.06	1520	3.52
2600	63.63	72.44	1540	3.60
2900	63.19	57.26	1560	3.71
3000	63.61	52.23	1600	4.07

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A
ECO-011411
BPF-BD1400+
EDU3590
URJ
220113
Page 2 of 3

Pad Connections


INPUT	2
OUTPUT	11
GROUND	1, 3-10, 12-18

Demo Board MCL P/N: TB-1108+
Suggested PCB Layout (PL-640)



- NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K
.433	1.299	.350	.197	.079	.140	.040	.100	.060	.157
11.00	33.00	8.89	5.00	2.02	3.56	1.02	2.54	1.52	4.00
L	M	N	P	Q	R	S	Wt.		
.098	.058	1.179	.080	.177	1.339	.473	grams		
2.50	1.48	29.95	2.03	4.51	34.02	12.02	4		

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	91.96	98.34	96.07	0.12	0.12	0.12	0.10	0.10	0.10
50	86.04	85.03	88.18	0.08	0.08	0.08	0.07	0.07	0.06
100	81.26	81.42	82.03	0.06	0.07	0.07	0.05	0.06	0.06
150	78.86	78.70	77.32	0.05	0.06	0.07	0.04	0.05	0.05
200	75.68	75.66	75.10	0.05	0.06	0.07	0.04	0.06	0.06
250	72.86	72.43	72.62	0.05	0.07	0.08	0.04	0.06	0.07
300	70.51	70.71	70.85	0.06	0.08	0.09	0.06	0.08	0.08
350	68.60	68.65	68.96	0.07	0.10	0.10	0.07	0.10	0.10
400	66.47	66.75	66.77	0.09	0.12	0.12	0.09	0.12	0.12
450	64.74	64.96	65.04	0.11	0.14	0.14	0.10	0.14	0.13
500	62.90	62.88	63.21	0.13	0.17	0.17	0.12	0.16	0.15
550	60.79	60.99	61.00	0.14	0.19	0.19	0.14	0.19	0.18
600	58.55	58.69	58.59	0.17	0.21	0.21	0.16	0.21	0.19
650	56.21	56.30	56.33	0.19	0.24	0.24	0.19	0.23	0.22
700	53.63	53.65	53.67	0.22	0.27	0.27	0.21	0.25	0.24
750	50.70	50.75	50.77	0.23	0.29	0.29	0.22	0.27	0.26
800	47.52	47.58	47.54	0.26	0.31	0.31	0.24	0.29	0.28
850	43.97	44.01	43.95	0.28	0.33	0.34	0.26	0.31	0.30
900	39.91	39.89	39.79	0.29	0.35	0.36	0.28	0.33	0.33
995	30.22	30.15	29.96	0.33	0.40	0.43	0.32	0.39	0.40
1000	29.62	29.55	29.36	0.34	0.41	0.43	0.33	0.39	0.41
1068	20.18	20.01	19.74	0.45	0.55	0.60	0.44	0.53	0.58
1100	14.65	14.43	14.15	0.68	0.81	0.89	0.66	0.78	0.87
1163	3.08	3.04	3.04	5.78	6.49	6.82	5.69	6.37	6.69
1200	1.10	1.26	1.34	28.02	28.01	28.79	25.06	24.80	24.50
1250	0.93	1.08	1.15	20.02	20.77	20.80	20.09	20.84	21.06
1300	0.86	1.01	1.08	33.13	33.44	31.06	58.35	56.04	36.34
1350	0.87	1.03	1.10	25.98	25.55	25.16	26.52	25.80	25.21
1400	0.99	1.15	1.21	17.18	17.16	17.68	16.78	16.71	17.27
1450	1.09	1.24	1.29	15.42	15.97	17.09	14.95	15.43	16.68
1500	1.04	1.21	1.30	24.47	26.84	29.66	22.70	24.13	27.30
1550	1.19	1.39	1.48	19.43	19.09	19.85	18.71	18.30	19.21
1600	1.42	1.64	1.73	16.29	16.71	17.75	15.65	15.98	17.17
1650	1.62	1.90	2.06	24.79	26.20	25.50	23.60	24.56	25.13
1680	2.08	2.47	2.68	20.82	19.68	19.70	19.99	18.92	19.70
1690	2.46	2.94	3.20	15.08	14.31	14.20	14.78	14.04	14.24
1700	3.13	3.74	4.10	10.72	10.15	9.94	10.66	10.13	10.06
1720	6.00	6.98	7.65	4.90	4.73	4.59	5.08	4.94	4.80
1740	11.10	12.34	13.18	2.32	2.38	2.39	2.55	2.65	2.60
1760	17.18	18.46	19.30	1.38	1.51	1.56	1.61	1.76	1.74
1780	23.26	24.51	25.25	1.00	1.13	1.18	1.20	1.35	1.32
1800	29.03	30.22	30.86	0.80	0.92	0.97	0.97	1.10	1.08
1820	34.47	35.58	36.09	0.69	0.80	0.84	0.82	0.95	0.92
1840	39.56	40.63	40.99	0.60	0.71	0.75	0.72	0.83	0.80
1860	44.21	45.20	45.49	0.54	0.64	0.68	0.64	0.74	0.72
1880	48.61	49.52	49.58	0.50	0.59	0.63	0.58	0.67	0.65
1900	52.63	53.43	53.36	0.46	0.55	0.58	0.53	0.62	0.60
1920	56.41	57.15	56.82	0.43	0.51	0.55	0.48	0.57	0.55
1950	61.22	61.86	60.94	0.39	0.48	0.51	0.44	0.52	0.51
2000	67.57	67.40	65.20	0.35	0.43	0.46	0.37	0.44	0.44
2100	71.19	69.31	66.24	0.27	0.35	0.39	0.27	0.35	0.36
2200	66.45	64.68	63.24	0.22	0.30	0.34	0.21	0.29	0.32
2300	61.71	61.87	61.76	0.19	0.28	0.32	0.16	0.24	0.29
2400	67.24	67.88	66.29	0.16	0.25	0.30	0.14	0.23	0.28
2500	61.40	61.96	61.47	0.14	0.24	0.29	0.14	0.23	0.27
2600	61.09	60.65	63.15	0.15	0.25	0.30	0.16	0.26	0.28
2700	56.49	55.78	54.62	0.15	0.25	0.30	0.21	0.31	0.29
2800	59.50	61.41	62.12	0.17	0.26	0.31	0.29	0.40	0.29
2900	60.17	60.55	60.38	0.18	0.29	0.33	0.41	0.52	0.30
3000	57.80	57.79	57.12	0.21	0.31	0.34	0.58	0.70	0.31

Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-40°C	@+25°C	@+85°C
1200	4.52	4.44	4.39
1210	4.19	4.13	4.10
1220	3.94	3.90	3.87
1230	3.76	3.73	3.71
1240	3.63	3.61	3.60
1250	3.54	3.53	3.51
1260	3.47	3.46	3.44
1270	3.42	3.40	3.38
1280	3.37	3.35	3.34
1290	3.32	3.31	3.29
1300	3.28	3.26	3.25
1310	3.24	3.23	3.22
1320	3.22	3.21	3.20
1330	3.20	3.19	3.18
1340	3.19	3.18	3.17
1350	3.18	3.17	3.16
1360	3.17	3.16	3.15
1370	3.16	3.16	3.14
1380	3.15	3.15	3.14
1390	3.14	3.14	3.13
1400	3.13	3.13	3.12
1410	3.13	3.12	3.13
1420	3.12	3.13	3.13
1430	3.13	3.14	3.14
1440	3.15	3.16	3.17
1450	3.18	3.19	3.20
1460	3.21	3.22	3.24
1470	3.25	3.27	3.27
1480	3.31	3.32	3.33
1490	3.36	3.37	3.37
1500	3.42	3.43	3.42
1510	3.47	3.48	3.48
1520	3.52	3.53	3.52
1530	3.56	3.57	3.57
1540	3.60	3.61	3.61
1550	3.65	3.66	3.67
1560	3.70	3.72	3.73
1570	3.75	3.78	3.80
1580	3.83	3.85	3.88
1590	3.93	3.95	3.98
1600	4.04	4.08	4.10

Typical Performance Curves




Case Style


TV

TV2849

Outline Dimensions



SUGGESTED LAYOUT FOR P.C. PATTERN



METALLIZATION
 SOLDER RESIST

CASE#	A	B	C	D	E	F	G	H	J	K	L	M
TV2849	.433 (11.00)	1.299 (33.00)	.350 (8.89)	.197 (5.00)	.079 (2.02)	.140 (3.56)	.040 (1.02)	.100 (2.54)	.060 (1.52)	.157 (4.00)	.098 (2.50)	.058 (1.48)

CASE#	N	P	Q	R	S	WT. GRAMS
TV2849	1.179 (29.95)	.080 (2.03)	.177 (4.51)	1.339 (34.02)	.473 (12.02)	4

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .005$; 3 Pl. $\pm .030$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 For RoHS Case Styles: 3-5 μ inch Gold over 120-240 μ inch Nickel plate.
 For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
 ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M174627	NEW RELEASE	JUN 19	ES	VC

Figure 1: Top view of the PCB layout for the 100W 2.45GHz PA. The layout shows a central blue area representing the substrate, with a red outline indicating the package boundary. The layout includes two RF ports, RF IN and RF OUT, and a PIN 1 connection. The layout is populated with numerous small circles representing vias or pads. Dimensions are provided for the trace width (.043±.002, 2 PLCS CD) and the space width (.028±.002, 4 PLCS CD). A note indicates the presence of 0.020 inch diameter through holes for ground.

1. TRACE WIDTH IS SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235					
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ± 		DRAWN	ES	14 JUN 19							
		CHECKED	TM	14 JUN 19							
		APPROVED	KKK	14 JUN 19							
						PL, TV2849, BPF, TB-1108+, 50 Ohm					
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.						SIZE	CODE IDENT	DRAWING NO:		REV:	
						A	15542	98-PL-640		OR	
						FILE:	98PL640	SCALE:	3:1	SHEET: 1 OF 1	
						ASHEETA1.DWG REV:A		DATE:01/12/95			



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215