

Bandpass Filter

SXBP-350+

50Ω 330 to 375 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2, 3, 4, 5, 6, 7

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	
.44	.74	.27	.200	.07	.060	
11.18	18.80	6.86	5.08	1.78	1.52	
G	H	J	K	L	M	wt.
.040	.660	.200	.470	.055	.060	grams
1.02	16.76	5.08	11.94	1.40	1.52	3.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)



- NOTE:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- high rejection
- Flat group delay @ passband
- good VSWR, 1.2:1 typ @ passband
- shielded case
- aqueous washable


Applications

- radio link
- receivers / transmitters
- harmonic rejection


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
350	330 - 375	280	435	245	520 - 2000	1.2	1.5	20

Typical Frequency Response






Functional Schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	σ			
0.5	77.48	2.27	0.24	330.0	16.58
245.0	51.21	0.45	0.22	332.0	15.81
280.0	32.44	0.51	0.29	334.0	15.15
300.0	17.62	0.71	1.01	338.0	14.32
310.0	8.62	0.78	3.07	342.0	13.74
315.0	4.82	0.59	6.57	346.0	13.33
320.0	2.74	0.32	15.40	350.0	13.10
330.0	1.89	0.19	17.22	354.0	12.98
342.0	1.69	0.20	22.55	355.0	12.96
350.0	1.69	0.19	26.48	358.0	12.91
366.0	1.87	0.19	19.67	362.0	12.89
375.0	2.09	0.18	23.06	366.0	13.20
385.0	4.07	0.24	11.76	370.0	13.78
392.0	7.99	0.31	5.74	375.0	15.23
405.0	16.28	0.29	2.56	378.0	16.30
435.0	30.23	0.18	1.21	380.0	16.90
520.0	50.91	0.07	0.55	385.0	17.12
2000.0	56.91	0.26	0.35	390.0	15.07



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Generic photo used for illustration purposes only
CASE STYLE: HF1139

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Surface Mount Band Pass Filter

SXBP-350+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	100.62	98.12	91.59	0.07	0.09	0.12	0.08	0.12	0.14
10	94.93	91.31	88.69	0.12	0.14	0.17	0.12	0.15	0.18
100	77.34	77.38	79.63	0.20	0.25	0.29	0.19	0.25	0.28
200	75.20	74.89	73.34	0.10	0.15	0.19	0.11	0.17	0.19
245	51.55	52.29	52.10	0.10	0.17	0.20	0.11	0.17	0.21
260	44.06	43.67	43.44	0.12	0.20	0.24	0.12	0.20	0.25
270	38.43	38.03	37.77	0.15	0.25	0.29	0.15	0.25	0.30
280	32.33	31.86	31.55	0.22	0.32	0.37	0.21	0.33	0.39
300	17.43	16.77	16.34	0.68	0.97	1.14	0.70	1.03	1.18
310	8.13	7.83	7.51	2.45	3.56	4.16	2.50	3.72	4.27
320	2.15	2.59	2.67	15.04	16.18	17.13	16.06	19.02	19.20
330	1.46	1.78	1.94	17.98	18.74	18.55	18.31	19.28	18.97
342	1.29	1.60	1.77	23.63	23.53	23.25	23.92	23.92	23.40
350	1.28	1.61	1.79	24.01	22.80	21.96	23.88	22.74	21.81
366	1.50	1.85	2.05	15.08	16.19	16.76	14.98	15.87	16.33
375	1.63	2.16	2.49	24.95	23.15	21.31	20.89	18.87	17.94
392	8.16	9.41	10.28	2.52	2.64	2.53	2.44	2.55	2.44
435	30.52	31.14	31.64	0.33	0.44	0.49	0.31	0.43	0.48
520	51.14	51.47	51.85	0.11	0.21	0.25	0.09	0.20	0.24
600	62.59	63.02	63.32	0.05	0.16	0.20	0.06	0.16	0.20
700	72.56	73.72	74.73	0.04	0.14	0.18	0.04	0.14	0.19
800	85.01	87.04	79.62	0.01	0.14	0.18	0.02	0.14	0.19
900	81.30	90.03	86.41	0.01	0.15	0.20	0.01	0.15	0.20
1000	91.77	89.45	88.09	0.02	0.16	0.21	0.00	0.16	0.21
1100	88.31	87.44	91.41	0.02	0.17	0.23	0.01	0.17	0.24
1200	87.37	92.25	86.91	0.02	0.19	0.25	0.01	0.18	0.25
1300	81.49	89.16	80.22	0.03	0.20	0.27	0.02	0.19	0.27
1400	93.64	89.81	92.89	0.04	0.21	0.28	0.02	0.21	0.28
1500	80.96	83.96	73.16	0.04	0.23	0.31	0.02	0.22	0.30
1600	77.70	82.79	76.90	0.05	0.24	0.32	0.04	0.23	0.32
1700	66.71	72.96	75.93	0.08	0.25	0.35	0.07	0.26	0.36
1800	72.73	69.93	74.75	0.09	0.27	0.37	0.06	0.26	0.36
1900	68.72	69.32	71.40	0.06	0.27	0.39	0.04	0.26	0.37
2000	69.79	70.45	79.18	0.10	0.29	0.39	0.06	0.29	0.39
2100	61.75	65.32	65.04	0.09	0.29	0.40	0.05	0.27	0.38
2200	41.64	49.05	52.01	0.16	0.32	0.44	0.12	0.32	0.43
2300	51.52	54.54	52.37	0.11	0.34	0.46	0.08	0.32	0.45
2400	56.05	59.08	55.96	0.10	0.32	0.44	0.05	0.30	0.43
2500	61.26	59.61	55.06	0.10	0.33	0.47	0.08	0.32	0.46
2600	55.45	56.16	51.09	0.10	0.33	0.47	0.07	0.31	0.48
2700	46.83	50.92	49.83	0.12	0.35	0.49	0.13	0.34	0.50
2800	46.95	47.69	47.88	0.15	0.37	0.49	0.09	0.37	0.51
2900	47.57	46.69	48.56	0.09	0.39	0.56	0.05	0.36	0.51
3000	43.99	45.26	46.12	0.12	0.43	0.61	0.08	0.38	0.54
3100	42.70	44.84	47.07	0.14	0.42	0.59	0.17	0.40	0.55
3200	44.82	44.00	44.21	0.15	0.42	0.60	0.09	0.43	0.59
3300	38.31	41.12	39.30	0.16	0.47	0.66	0.06	0.46	0.65
3400	42.03	38.47	36.81	0.20	0.51	0.70	0.17	0.49	0.70
3500	33.82	36.63	35.37	0.19	0.54	0.73	0.17	0.50	0.70
3600	39.72	37.02	35.75	0.22	0.58	0.75	0.19	0.57	0.76
3700	39.11	37.48	35.44	0.23	0.61	0.82	0.15	0.62	0.88
3800	39.27	34.38	35.92	0.24	0.66	0.86	0.26	0.65	0.90
3900	34.60	32.25	32.88	0.24	0.69	0.93	0.25	0.69	0.88
4000	32.10	30.53	31.55	0.33	0.73	0.98	0.36	0.70	0.95

REV. X2

SXBP-350+

101118

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

SXBP-350+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
210	3.12	1.60	2.30
220	1.13	1.21	0.65
230	1.58	1.73	1.78
240	1.88	1.73	0.52
250	1.99	1.44	1.13
260	2.35	2.29	2.18
270	2.83	3.00	3.04
280	3.71	3.87	3.92
290	5.08	5.35	5.62
300	8.19	8.75	9.19
310	16.37	17.13	17.82
320	21.93	21.34	20.88
330	16.30	15.99	15.76
332	15.58	15.34	15.17
334	15.02	14.84	14.70
336	14.59	14.44	14.35
338	14.24	14.12	14.05
340	13.97	13.86	13.81
342	13.74	13.67	13.61
344	13.54	13.48	13.46
346	13.38	13.34	13.31
348	13.24	13.22	13.19
350	13.13	13.11	13.1
352	13.04	13.02	13.04
354	12.97	12.96	12.98
356	12.91	12.91	12.96
358	12.91	12.93	12.99
360	12.91	12.96	13.05
362	12.98	13.05	13.18
364	13.05	13.21	13.37
366	13.26	13.47	13.69
368	13.54	13.82	14.12
370	13.94	14.33	14.67
372	14.46	14.93	15.33
374	15.05	15.53	15.94
375	15.7	16.2	16.59
380	17.69	17.67	17.59
390	14.9	13.77	12.92
400	8.04	7.5	7.09
420	3.44	3.38	3.29
430	2.61	2.55	2.5
440	1.98	1.89	1.89
450	1.54	1.52	1.51
460	1.42	1.48	1.42
470	1.4	1.28	1.32
480	1.21	1.16	1.12
500	0.72	0.76	0.87
520	1.03	0.8	0.84
530	0.85	0.43	0.57
540	0.55	0.58	0.58
550	0.8	0.38	0.47
560	0.58	0.53	0.51
570	0.52	0.49	0.22
580	0.18	0.38	0.49
600	0.65	0.47	0.24

REV. X2
SXBP-350+
101118
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE





OUTPUT RETURN LOSS vs. TEMPERATURE




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.015 "; 3 Pl. ± 0.01 "

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.

**NOTE:**

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025" ± .002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN DK (RAVON)	29 NOV 05
TOLERANCES ON:	CHECKED RZ (RAVON)	29 NOV 05
2 PL DECIMALS ±	APPROVED HH (RAVON)	29 NOV 05
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.




Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-230	OR
FILE:	98PL230	SCALE: 4:1	SHEET: 1 OF 1

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



TB-368



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215