

Surface Mount Directional Coupler

75Ω 6.7 dB 5 to 1250 MHz

TCD-6-122-75X+

Features

- wideband, 5 to 1250 MHz
- low mainline loss, 2.5 dB typ.
- aqueous washable
- leads for excellent solderability
- protected by US Patent 6,140,887

Applications

- DOCSIS® 3.1 Systems
- VHF/UHF
- CATV
- cellular

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5		1250	MHz
Mainline Loss ¹ (above theoretical 0.1 dB)	5-100	—	2.2	2.8	dB
	100-1000	—	2.3	2.9	
	1000-1250	—	2.8	3.5	
Nominal Coupling	5-1250	—	6.7±0.3	—	dB
Coupling Flatness(±)	5-1250	—	±0.2	±0.5	dB
Directivity	5-100	13	15	—	dB
	100-1000	10	13	—	
	1000-1250	8	12	—	
Return Loss (Input)	5-100	10	15	—	dB
	100-1000	14	16	—	
	1000-1250	13	15	—	
Return Loss (Output)	5-100	15	20	—	dB
	100-1000	15	18	—	
	1000-1250	13	18	—	
Return Loss (Coupling)	5-100	10	14	—	dB
	100-1000	13	15	—	
	1000-1250	13	16	—	
Input Power	5-500	—	—	0.3	W
	500-1250	—	—	0.5	

1. Mainline loss includes theoretical power loss 1.1dB at coupled port.



Generic photo used for illustration purposes only

CASE STYLE: AT1521

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

 Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 85°C*
Storage Temperature	-55°C to 100°C


Permanent damage may occur if any of these limits are exceeded.

* Case temperature is defined as temperature on ground leads.


Pin Connections

Function	Pin Number
INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
75Ω TERM EXTERNAL	6

Product Marking



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV. A
M156781
ED-150407
TCD-6-122-75X+
WP/CP/AM
190606
Page 1 of 2

TCD-6-122-75X+

Outline Drawing




PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.02

Demo Board MCL P/N: TB-72 Suggested PCB Layout (PL-010)






- NOTES:**
- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $0.030" \pm 0.002"$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K	wt
.150	.150	.160	.050	.040	.025	.028	.065	.190	.030	grams
3.81	3.81	4.06	1.27	1.02	0.64	0.71	1.65	4.83	0.76	0.15

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	In	Return Loss (dB) Out	Cpl
5	2.29	6.81	15.68	14.24	22.63	14.03
50	2.21	6.74	15.53	15.33	43.05	15.02
100	2.22	6.76	15.46	15.68	38.71	15.53
200	2.23	6.78	15.23	16.14	29.54	16.00
350	2.24	6.76	14.34	15.95	23.73	15.55
500	2.29	6.71	13.55	15.97	21.16	16.59
650	2.38	6.66	13.00	16.04	19.32	17.26
800	2.49	6.61	12.48	15.72	18.60	17.93
1000	2.69	6.57	12.37	15.96	18.91	18.06
1250	3.01	6.56	11.63	16.81	19.55	18.56



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Directional Coupler

TCD-6-122-75X+





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
1	3.11	7.36	14.40	10.10	11.90	10.12
2	2.61	7.01	15.13	12.30	16.07	12.22
3	2.43	6.90	15.45	13.31	18.80	13.18
4	2.35	6.84	15.60	13.87	20.90	13.71
5	2.29	6.81	15.68	14.24	22.63	14.03
10	2.21	6.74	15.69	14.91	28.56	14.62
20	2.21	6.73	15.62	15.12	34.90	14.80
30	2.21	6.74	15.58	15.18	38.36	14.86
40	2.21	6.74	15.55	15.26	40.98	14.93
50	2.21	6.74	15.53	15.33	43.05	15.02
60	2.21	6.74	15.50	15.40	44.11	15.10
70	2.21	6.75	15.46	15.48	43.66	15.16
100	2.22	6.76	15.46	15.68	38.71	15.53
150	2.22	6.77	15.42	15.96	33.23	15.96
200	2.23	6.78	15.23	16.14	29.54	16.00
250	2.23	6.77	15.02	16.09	26.98	15.94
300	2.23	6.77	14.68	16.12	25.21	15.71
350	2.24	6.76	14.34	15.95	23.73	15.55
400	2.26	6.74	14.03	15.89	22.80	15.75
450	2.27	6.73	13.73	15.85	21.58	15.91
500	2.29	6.71	13.55	15.97	21.16	16.59
550	2.32	6.70	13.34	16.00	20.21	16.73
600	2.35	6.68	13.17	16.12	19.91	17.40
650	2.38	6.66	13.00	16.04	19.32	17.26
700	2.42	6.64	12.79	16.04	19.01	17.73
750	2.45	6.62	12.67	15.86	18.82	17.57
800	2.49	6.61	12.48	15.72	18.60	17.93
850	2.54	6.59	12.41	15.61	18.71	17.95
900	2.59	6.58	12.38	15.64	18.61	18.08
950	2.64	6.57	12.31	15.77	18.87	18.16
1000	2.69	6.57	12.37	15.96	18.91	18.06
1050	2.75	6.56	12.24	16.20	19.10	18.27
1100	2.81	6.55	12.21	16.41	19.16	18.22
1150	2.87	6.54	12.03	16.57	19.26	18.52
1218	2.96	6.55	11.78	16.76	19.42	18.42
1250	3.01	6.56	11.63	16.81	19.55	18.56
1300	3.10	6.57	11.28	16.97	19.65	18.43
1400	3.31	6.62	10.70	17.51	19.76	18.00
1500	3.57	6.70	10.11	18.29	19.48	17.77

Directional Coupler

TCD-6-122-75X+


Typical Performance Curves



Outline Dimensions

AT1521

PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAMS
AT1521	.150 (3.81)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (.64)	.028 (.71)	.065 (1.65)	.190 (4.83)	.030 (.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
- Orientation Dot on Top Hat & Marking on the Substrate both refers to Pin #1 of the Unit.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F17

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		13	Standard	1000
				2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M73159	NEW RELEASE	08/00	IL	DB
A	M82377	UPDATED DRAWING	07/30/02	AV	LC
B	M102713	UPDATED NOTES	01/12/06	GF	IL

[illegible]

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" $\pm$ 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.



UNLESS OTHERWISE SPECIFIED

INITIALS

DATE _____

DIMENSIONS ARE IN INCHES

DRAWN

IL

08/03/00

TOLERANCES ON:

CHECKED

08/08/00

2 PL DECIMALS ±
3 PL DECIMALS ±

CHECKED
APPROVED

00 / 00 / 00

3 PL DECIMAL
ANGLES $\pm$
FRACTIONS $\pm$

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, mm, 75, DB714, TCD, TB-72

SIZE

CODE	IDENT
------	-------

DRAWING NO:

98-PL-010

REV:

B


FILE: 98PL010

SCALE: 10:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-72



Schematic Diagram

Notes:

1. 75 Ohm BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215