

Coaxial

Low Noise Amplifier

ZEL-0812LN

50Ω

800 to 1200 MHz

Features

- very low noise figure, 1.5 dB max.
- wideband, 800 to 1200 MHz
- rugged, shielded case

Applications

- UHF
- cellular
- PCS/GSM



Generic photo used for illustration purposes only

Case Style: EEE132

Connectors Model

SMA ZEL-0812LN

Electrical Specifications


Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		800		1200	MHz
Noise Figure	800-1200	—	—	1.5	dB
Gain	800-1200	20	—	—	dB
Gain Flatness	800-1200	—	—	±1.0	dB
Output Power at 1dB compression	800-1200	—	+8	—	dBm
Output third order intercept point	800-1200	—	+18	—	dBm
Input VSWR	800-1200	—	—	2.5	:1
Output VSWR	800-1200	—	—	2.5	:1
DC Supply Voltage		—	15	—	V
Supply Current		—	—	70	mA

Noise Figure specified at room temperature, increases to 2 dB typical at +85°C

Open load is not recommended, potentially can cause damage.

With no load derate max input power by 20 dB

Outline Drawing



Maximum Ratings

Parameter	Ratings
Operating Temperature	-54°C to 85°C
Storage Temperature	-55°C to 100°C
DC Voltage	17V
Input RF Power (no damage)	+13 dBm

Permanent damage may occur if any of these limits are exceeded.

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	wt
.90	.90	.675	.245	.45	1.34	.09	1.152	.09	.712	.22	.106	.05	grams
22.86	22.86	17.15	6.22	11.43	34.04	2.29	29.26	2.29	18.08	5.59	2.69	1.27	50.0

Notes






A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

 REV. B
 M175652
 ZEL-0812LN-S
 200512
 Page 1 of 2

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR (:1)		NOISE FIGURE (dB)	P _{OUT} at 1 dB COMPR. (dBm)
	12V	15V	16V	12V	15V	16V	IN	OUT		
800.00	24.02	25.00	25.24	10.80	10.00	9.70	1.88	1.77	1.43	14.93
829.00	23.91	24.86	25.11	10.70	10.10	10.20	1.83	1.71	1.41	14.82
869.20	23.78	24.69	24.92	10.90	10.30	10.10	1.82	1.67	1.40	14.78
911.50	23.52	24.40	24.64	10.90	10.50	10.60	1.81	1.59	1.39	14.73
953.80	23.31	24.19	24.41	11.10	10.70	10.50	1.80	1.57	1.33	14.85
994.90	23.13	24.01	24.24	11.40	10.90	10.40	1.78	1.53	1.31	14.97
1046.20	23.05	23.93	24.15	11.10	11.00	10.50	1.73	1.50	1.27	14.98
1097.40	23.14	24.02	24.27	11.00	10.70	10.50	1.65	1.46	1.23	15.25
1148.70	23.41	24.28	24.50	10.30	10.30	10.10	1.53	1.43	1.22	15.39
1200.00	23.81	24.61	24.80	9.60	9.60	9.40	1.40	1.45	1.24	15.20



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Noise Amplifier

ZEL-0812LN

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR IN (:1) 15V	VSWR OUT (:1) 15V	NOISE FIGURE (dB) 15V	Pout at 1dB Comp. (dBm) 15V
	12V	15V	16V	12V	15V	16V				
800.0	24.02	25.00	25.24	10.80	10.00	9.70	1.88	1.77	1.43	14.93
829.0	23.91	24.86	25.11	10.70	10.10	10.20	1.83	1.71	1.41	14.82
869.2	23.78	24.69	24.92	10.90	10.30	10.10	1.82	1.67	1.40	14.78
911.5	23.52	24.40	24.64	10.90	10.50	10.60	1.81	1.59	1.39	14.73
953.8	23.31	24.19	24.41	11.10	10.70	10.50	1.80	1.57	1.33	14.85
994.9	23.13	24.01	24.24	11.40	10.90	10.40	1.78	1.53	1.31	14.97
1046.2	23.05	23.93	24.15	11.10	11.00	10.50	1.73	1.50	1.27	14.98
1097.4	23.14	24.02	24.27	11.00	10.70	10.50	1.65	1.46	1.23	15.25
1148.7	23.41	24.28	24.50	10.30	10.30	10.10	1.53	1.43	1.22	15.39
1200.0	23.81	24.61	24.80	9.60	9.60	9.40	1.40	1.45	1.24	15.20

REV. X1
ZEL-0812LN
060913
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Low Noise Amplifier

Typical Performance Curves

ZEL-0812LN



Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L
EEE132	.90 (22.86)	.90 (22.86)	.675 (17.15)	.245 (6.22)	.45 (11.43)	1.34 (34.04)	.09 (2.29)	1.152 (29.26)	.09 (2.29)	.712 (18.08)	.22 (5.59)

CASE #	M	N	WT. GRAM
EEE132	.106 (2.69)	.05 (1.27)	50.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-54° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C