



USB & ETHERNET CONTROLLED

RF Switch Matrix

RC-8SPDT-A18

Mini-Circuits

50Ω DC to 18 GHz SMA-Female

THE BIG DEAL

- Eight independent mechanical SPDT switches
- 20W power rating (cold switching)
- High isolation, 85 dB typ
- High reliability

APPLICATIONS

- Fail safe / redundancy switching
- Automated test equipment
- Satcom switching

PRODUCT OVERVIEW

Mini-Circuits' RC-8SPDT-A18 contains eight independently controlled, electro mechanical SPDT switches. Each switch operates over an extremely wide bandwidth, from DC to 18 GHz with high isolation and low insertion loss. The absorptive switches are of a failsafe and break before make configuration, with a lifetime of 5 million switching cycles per switch when used within the noted specifications.

The switch box is constructed in a compact, rugged metal case (4.5 x 12.0 x 2.25") with all SMA (f) RF connectors on the front panel. The switches are controlled via USB or Ethernet, allowing control directly from a PC, or remotely over a network. Full software support is provided, including our user friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32 bit and 64 bit systems). Download the software from our website at www.minicircuits.com/softwaredownload/rfswitchcontroller.html.

KEY FEATURES

Feature	Advantages
Eight mechanical SPDT switches	Mechanical absorptive switches provide high reliability, repeatable high performance and internal termination of input signals on the disconnected paths
High power operation from DC to 18 GHz	Supports a wide range of RF test and signal routing applications up to X and Ku bands, with 40W input power.
Break-before make configuration	Prevents a momentary connection of the old and new signal paths, reducing the inconsistent transient effects that could otherwise be observed during switching
USB & Ethernet control	USB HID and Ethernet (HTTP / Telnet) interfaces provide easy compatibility with a wide range of software setups and programming environments
Full software support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box, while the comprehensive API (application programming interface) with examples and instructions allows easy automation in most programming environments



CASE STYLE: LM1852

DOWNLOAD

SOFTWARE PACKAGE

RoHS Compliant

See our website for RoHS Compliance methodologies and qualifications

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. F
ECO-021362
EDR-10927/10F1
RC-8SPDT-A18
MCL NY
240401

PAGE 1 OF 8



USB & ETHERNET CONTROLLED

RF Switch Matrix

RC-8SPDT-A18

Mini-Circuits

50Ω DC to 18 GHz SMA-Female

ELECTRICAL SPECIFICATIONS

Parameter	Conditions (GHz)	Min.	Typ.	Max.	Units
Frequency	—	DC		18	GHz
RF Insertion Loss (per switch)	DC to 1 GHz	—	0.10	0.15	dB
	1 to 8 GHz	—	0.15	0.30	
	8 to 12 GHz	—	0.25	0.40	
	12 to 18 GHz	—	0.30	0.50	
RF VSWR	DC to 1 GHz	—	1.05	—	:1
	1 to 8 GHz	—	1.20	—	
	8 to 12 GHz	—	1.20	—	
	12 to 18 GHz	—	1.25	—	
RF Isolation (per switch)	DC to 1 GHz	85	100	—	dB
	1 to 8 GHz	75	90	—	
	8 to 12 GHz	70	80	—	
	12 to 18 GHz	60	66	—	
Switching Time	—	—	15	—	ms
RF Power (cold switching) ¹	—	—	—	40	W
Rated Voltage	24V _{DC} input USB port	23	24	25	V
		—	5	—	
Rated Current (24V _{DC} input)	All switches in COM -> 2 position	—	790	1055	mA
	All switches in COM -> 1 position	—	115	165	
Rated Current (USB port)		—	10	20	
Life (per switch)	@ 100 mW (hot switching) ²	—	5	—	million switching cycles
	@ 1 W (hot switching)	—	1	—	

1. Maximum power for any connected through path as stated; maximum power into any internal termination is 1W

2. Hot switching powers above this level will degrade the switch lifetime

ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature	0°C to +40°C
Storage Temperature	-15°C to +85°C
DC Voltage max.	+26 V

3. Permanent damage may occur if any of these limits are exceeded.

CONNECTIONS

24V _{DC} IN	(2.1 mm center positive DC Socket)
RF Switch A (1, COM, 2)	(SMA female)
RF Switch B (1, COM, 2)	(SMA female)
RF Switch C (1, COM, 2)	(SMA female)
RF Switch D (1, COM, 2)	(SMA female)
RF Switch E (1, COM, 2)	(SMA female)
RF Switch F (1, COM, 2)	(SMA female)
RF Switch G (1, COM, 2)	(SMA female)
RF Switch H (1, COM, 2)	(SMA female)
USB	(USB type B receptacle)
Network (Ethernet/LAN)	(RJ45 socket)





USB & ETHERNET CONTROLLED


RF Switch Matrix

RC-8SPDT-A18


50Ω DC to 18 GHz SMA-Female

SWITCHING CONFIGURATION (PER SWITCH):

- Fail-Safe
- Absorptive (Internal terminations on ports J1-J2)



OUTLINE DRAWING (LM1852)





INSTRUCTIONS FOR MOUNTING BRACKETS:
TOOL REQUIRED: PHILLIPS HEAD SCREWDRIVER
STEP 1: REMOVE RUBBER FEET FROM THE BOTTOM OF THE UNIT. DO NOT DISCARD THE FASTENERS.
STEP 2: MOUNT THE BRACKETS WITH THE FASTENERS REMOVED IN STEP 1, USING THE COUNTER BORE HOLES IN THE BRACKET.

Weight: 2240 grams.
Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.03 inch; 3 Pl. ±.015 inch.



**TYPICAL SWITCHING PERFORMANCE**

The graphs below present the typical mechanical switching characteristic from the point of applying the internal DC voltage to the switch actuator (identified by the purple "trigger" trace). USB / Ethernet communication delays are excluded (in the order of several ms, depending on PC / network performance). The break before make process is visible in the sequence of events (the active switch path is disconnected, prior to connecting the final switch path).

Switching from COM<>1 to COM<>2 state: 6.95 ms**Switching from COM<>2 to COM<>1 state: 4.88 ms**



USB & ETHERNET CONTROLLED

RF Switch Matrix


RC-8SPDT-A18

Mini-Circuits


50Ω DC to 18 GHz SMA-Female

TYPICAL PERFORMANCE CURVES


Insertion Loss



Isolation



VSWR



Mini-Circuits



SOFTWARE SPECIFICATIONS

SOFTWARE & DOCUMENTATION DOWNLOAD:

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from www.minicircuits.com/softwaredownload/rfswitchcontroller.html
- Please contact testsolutions@minicircuits.com for support

MINIMUM SYSTEM REQUIREMENTS:

Parameter	Requirements	
Interface	USB HID & Ethernet (HTTP & Telnet)	
System Requirements	GUI	Windows 98 or later
	USB API DLL	Windows 98 or later and programming environment with ActiveX or .NET support
	USB Direct Programming	Linux, Windows 98 or later
	Ethernet	Windows, Linux or Mac computer with a network port and Ethernet TCP/IP support
Hardware	Pentium II or later with 256 MB RAM	

APPLICATION PROGRAMMING INTERFACE (API)

ETHERNET SUPPORT:

- Simple ASCII / SCPI command set for attenuator control
- Communication via HTTP or Telnet
- Supported by most common programming environments

USB SUPPORT (WINDOWS):

- ActiveX COM DLL file for creation of 32-bit programs
- .NET library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments (refer to application note AN-49-001 for summary of supported environments)

USB SUPPORT (LINUX):

- Direct USB programming using a series of USB interrupt codes

Full programming instructions and examples available for a wide range of programming environments / languages.



Mini-Circuits

USB & ETHERNET CONTROLLED


RF Switch Matrix

RC-8SPDT-A18


50Ω DC to 18 GHz SMA-Female

GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB or Ethernet
- Run GUI in "demo mode" to evaluate software without a hardware connection



- View and set switch states at the click of a button
- Configure and run timed switching sequences
- Set start-up switch state
- Configure Ethernet IP Settings



Mini-Circuits



Mini-Circuits®

USB & ETHERNET CONTROLLED

RF Switch Matrix

RC-8SPDT-A18

50Ω DC to 18 GHz SMA-Female

ORDERING INFORMATION

Please contact Mini-Circuits' Test Solutions department for price and availability: testsolutions@minicircuits.com

Model	Description
RC-8SPDT-A18	USB & Ethernet controlled SPDT switch matrix

Included Accessories	Part No.	Description
	AC/DC-24-3W1	AC/DC 24V _{DC} Grounded Power Adaptor. Operating temperature: 0°C to +40°C, I _{Max} =2.5A
See Below	CBL-3W1-XX	AC Power Cord (Select one power cord from below with each Switch Matrix box)
	USB-CBL-AB-3+	2.7 ft (0.8 m) USB Cable: USB type A(Male) to USB type B(Male)

AC Power Cords ⁵	Part No.	Description
	CBL-3W1-US	Power Cord for United States
	CBL-3W1-EU	Power Cord for Europe
	CBL-3W1-UK	Power Cord for United Kingdom
	CBL-3W1-AU	Power Cord for Australia and China
	CBL-3W1-IL	Power Cord for Israel

5. If you need a Power cord for a country not listed please contact testsolutions@minicircuits.com

OPTIONAL ACCESSORIES

USB-CBL-AB-3+	2.7 ft (0.8 m) USB Cable: USB type A(Male) to USB type B(Male)
USB-CBL-AB-7+	6.8 ft (2.1 m) USB Cable: USB type A(Male) to USB type B(Male)
USB-CBL-AB-11+	11 ft (3.4 m) USB Cable: USB type A(Male) to USB type B(Male)
CBL-RJ45-MM-5+	5 ft (1.5 m) Ethernet cable: RJ45(Male) to RJ45(Male) Cat 5E cable
BKT-272-08+	Bracket (One set of 2 each)

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Xtra Long Life USB/Ethernet RF SPDT

RC-8SPDT-A18

Typical Performance Data

TEST CONDITIONS: @Temperature = 0degC

FREQUENCY (MHz)	INSERTION LOSS ON (dB)		ISOLATION OFF (dB)		VSWR COM (:1)		VSWR COM->2 (:1)		VSWR COM->1 (:1)	
	COM-1	COM-2	COM-1	COM-2	ON	OFF	1	2	1	2
10	0.02	0.02	92.69	86.49	1.01	1.01	1.00	1.00	1.01	1.01
20	0.02	0.01	86.06	87.87	1.01	1.01	1.00	1.00	1.01	1.01
30	0.03	0.02	78.50	89.42	1.01	1.00	1.00	1.01	1.00	1.01
40	0.03	0.02	87.99	86.57	1.01	1.01	1.00	1.01	1.01	1.01
50	0.00	0.00	85.58	86.20	1.01	1.01	1.00	1.01	1.01	1.01
60	0.01	0.01	88.17	88.75	1.01	1.01	1.00	1.01	1.01	1.01
70	0.01	0.01	111.04	86.47	1.01	1.01	1.00	1.01	1.01	1.01
80	0.01	0.00	93.25	86.40	1.01	1.01	1.01	1.01	1.01	1.01
90	0.01	0.00	84.68	86.35	1.01	1.01	1.01	1.01	1.01	1.02
100	0.01	0.00	91.27	91.27	1.01	1.01	1.01	1.01	1.01	1.02
200	0.01	0.00	91.56	97.21	1.01	1.01	1.02	1.01	1.01	1.03
300	0.00	0.00	94.03	104.54	1.01	1.01	1.02	1.02	1.01	1.03
400	0.01	0.01	95.48	99.11	1.02	1.02	1.02	1.02	1.02	1.03
500	0.01	0.01	103.50	102.97	1.01	1.01	1.02	1.01	1.01	1.02
600	0.01	0.02	96.73	98.55	1.01	1.01	1.01	1.01	1.01	1.02
700	0.02	0.02	99.74	102.52	1.01	1.01	1.02	1.01	1.01	1.02
800	0.02	0.02	105.65	100.78	1.01	1.01	1.02	1.01	1.01	1.02
900	0.02	0.02	99.56	102.99	1.01	1.02	1.02	1.02	1.02	1.03
1000	0.02	0.03	105.33	97.50	1.01	1.01	1.02	1.02	1.02	1.03
1200	0.02	0.03	95.06	104.12	1.01	1.01	1.03	1.01	1.01	1.03
1400	0.02	0.03	104.83	110.41	1.02	1.01	1.03	1.01	1.01	1.03
1600	0.03	0.03	94.89	99.77	1.02	1.02	1.03	1.02	1.02	1.03
1800	0.03	0.03	103.10	103.23	1.02	1.03	1.04	1.02	1.02	1.03
2000	0.03	0.04	103.84	103.70	1.02	1.03	1.04	1.02	1.02	1.04
2200	0.03	0.04	93.08	102.31	1.02	1.02	1.05	1.02	1.02	1.04
2400	0.04	0.05	102.45	104.45	1.03	1.04	1.05	1.03	1.03	1.05
2600	0.04	0.05	111.34	96.36	1.03	1.05	1.06	1.04	1.04	1.06
2800	0.04	0.05	105.47	103.64	1.03	1.04	1.07	1.04	1.04	1.06
3000	0.05	0.05	101.65	98.86	1.03	1.04	1.08	1.04	1.04	1.07
3200	0.05	0.06	97.59	105.83	1.04	1.06	1.08	1.06	1.06	1.08
3400	0.06	0.07	99.40	102.61	1.06	1.09	1.10	1.08	1.09	1.10
3600	0.06	0.06	105.16	112.37	1.07	1.08	1.10	1.08	1.08	1.11
4000	0.07	0.07	100.12	102.42	1.10	1.13	1.12	1.12	1.12	1.13
4500	0.08	0.09	110.61	104.60	1.14	1.14	1.13	1.15	1.15	1.14
5000	0.10	0.12	101.66	99.14	1.19	1.22	1.14	1.23	1.21	1.17
5500	0.12	0.13	104.68	106.94	1.24	1.21	1.13	1.23	1.21	1.15
6000	0.12	0.14	102.68	99.55	1.26	1.23	1.13	1.27	1.23	1.17
6500	0.12	0.14	101.00	95.07	1.26	1.19	1.10	1.24	1.19	1.15
7000	0.12	0.13	97.32	97.36	1.23	1.14	1.08	1.20	1.16	1.13
7500	0.12	0.13	92.52	93.66	1.19	1.13	1.06	1.16	1.12	1.11
8000	0.12	0.13	100.57	96.16	1.17	1.08	1.06	1.13	1.09	1.11
8500	0.15	0.14	95.34	93.74	1.12	1.08	1.07	1.11	1.08	1.11
9000	0.15	0.14	94.67	91.78	1.08	1.06	1.05	1.05	1.04	1.10
9500	0.16	0.15	92.17	93.77	1.06	1.02	1.07	1.10	1.04	1.11
10000	0.17	0.17	92.10	91.45	1.07	1.05	1.08	1.06	1.02	1.11
12000	0.21	0.18	91.26	86.33	1.03	1.06	1.12	1.04	1.07	1.05
13000	0.26	0.20	87.46	84.59	1.06	1.08	1.21	1.06	1.10	1.14
14000	0.29	0.22	87.80	81.01	1.12	1.11	1.27	1.14	1.15	1.25
15000	0.36	0.28	83.73	78.00	1.27	1.25	1.31	1.25	1.25	1.32
16000	0.46	0.34	82.49	75.43	1.19	1.31	1.27	1.23	1.27	1.26
17000	0.38	0.28	81.40	72.40	1.09	1.11	1.22	1.04	1.10	1.12
18000	0.43	0.33	80.97	69.69	1.27	1.08	1.26	1.20	1.05	1.18

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Xtra Long Life USB/Ethernet RF SPDT

RC-8SPDT-A18

Typical Performance Data

TEST CONDITIONS: @Temperature = +25degC

FREQUENCY (MHz)	INSERTION LOSS ON (dB)		ISOLATION OFF (dB)		VSWR COM (:1)		VSWR COM->2 (:1)		VSWR COM->1 (:1)	
	COM-1	COM-2	COM-1	COM-2	ON	OFF	1	2	1	2
10	0.00	0.00	86.43	93.17	1.00	1.00	1.00	1.02	1.02	1.01
20	0.02	0.02	87.42	90.43	1.00	1.00	1.00	1.01	1.01	1.01
30	0.02	0.02	89.26	93.81	1.00	1.00	1.00	1.00	1.00	1.01
40	0.03	0.03	91.18	87.61	1.00	1.01	1.00	1.00	1.00	1.01
50	0.00	0.00	91.95	88.50	1.00	1.00	1.00	1.00	1.00	1.01
60	0.00	0.00	92.97	88.43	1.00	1.00	1.00	1.00	1.00	1.01
70	0.01	0.01	88.69	88.95	1.00	1.00	1.00	1.00	1.00	1.01
80	0.01	0.01	106.34	86.65	1.00	1.00	1.00	1.00	1.00	1.01
90	0.01	0.00	89.91	98.42	1.00	1.00	1.00	1.00	1.00	1.01
100	0.00	0.01	92.71	86.88	1.00	1.00	1.00	1.00	1.00	1.01
200	0.01	0.01	94.79	97.05	1.00	1.00	1.01	1.01	1.01	1.01
300	0.02	0.02	109.88	90.43	1.00	1.00	1.01	1.01	1.01	1.01
400	0.02	0.02	102.23	99.10	1.01	1.01	1.01	1.01	1.01	1.01
500	0.02	0.02	97.52	101.30	1.01	1.00	1.01	1.01	1.01	1.01
600	0.03	0.03	100.41	100.25	1.01	1.00	1.01	1.01	1.01	1.01
700	0.03	0.03	98.46	100.26	1.01	1.01	1.01	1.01	1.01	1.01
800	0.03	0.03	107.02	108.08	1.01	1.01	1.01	1.01	1.01	1.01
900	0.03	0.03	98.13	102.59	1.01	1.01	1.02	1.01	1.01	1.01
1000	0.03	0.04	106.26	108.06	1.01	1.01	1.02	1.01	1.01	1.02
1200	0.04	0.04	105.64	118.05	1.01	1.01	1.02	1.00	1.01	1.02
1400	0.04	0.04	113.89	108.14	1.01	1.01	1.03	1.00	1.01	1.02
1600	0.05	0.05	109.89	113.36	1.01	1.01	1.03	1.01	1.01	1.02
1800	0.04	0.05	101.11	105.12	1.02	1.02	1.04	1.01	1.01	1.03
2000	0.05	0.06	98.50	108.08	1.03	1.02	1.04	1.01	1.01	1.03
2200	0.05	0.06	109.01	102.61	1.04	1.02	1.05	1.02	1.02	1.04
2400	0.06	0.06	97.17	103.88	1.05	1.03	1.05	1.02	1.02	1.04
2600	0.06	0.07	102.67	99.87	1.06	1.03	1.06	1.03	1.03	1.05
2800	0.06	0.07	102.17	101.90	1.07	1.04	1.07	1.03	1.04	1.06
3000	0.06	0.07	102.72	102.95	1.08	1.04	1.08	1.04	1.04	1.06
3200	0.06	0.07	108.07	100.45	1.08	1.06	1.09	1.05	1.06	1.07
3400	0.07	0.08	101.22	103.70	1.09	1.07	1.09	1.06	1.07	1.08
3600	0.08	0.08	106.01	102.58	1.09	1.09	1.10	1.08	1.08	1.09
4000	0.09	0.09	105.56	107.81	1.10	1.11	1.11	1.11	1.11	1.10
4500	0.10	0.11	96.22	96.80	1.11	1.15	1.13	1.15	1.15	1.12
5000	0.12	0.13	98.62	100.46	1.15	1.18	1.13	1.18	1.18	1.14
5500	0.13	0.14	105.56	102.08	1.21	1.20	1.13	1.22	1.20	1.15
6000	0.14	0.16	96.57	94.10	1.26	1.20	1.12	1.23	1.21	1.15
6500	0.14	0.16	96.21	107.68	1.27	1.19	1.11	1.23	1.19	1.15
7000	0.13	0.16	99.56	100.96	1.24	1.16	1.10	1.21	1.17	1.14
7500	0.15	0.17	94.50	101.70	1.18	1.14	1.08	1.20	1.15	1.13
8000	0.14	0.16	93.06	95.68	1.12	1.13	1.07	1.17	1.13	1.12
8500	0.15	0.16	92.44	95.29	1.06	1.09	1.07	1.13	1.09	1.12
9000	0.14	0.16	92.53	92.00	1.06	1.06	1.06	1.09	1.06	1.10
9500	0.14	0.16	90.69	98.64	1.09	1.04	1.06	1.07	1.03	1.10
10000	0.14	0.16	90.46	93.90	1.10	1.02	1.07	1.06	1.03	1.10
12000	0.16	0.17	86.14	90.83	1.12	1.10	1.14	1.04	1.10	1.08
13000	0.17	0.19	82.24	89.32	1.10	1.13	1.19	1.07	1.15	1.14
14000	0.18	0.20	77.92	83.48	1.22	1.15	1.25	1.10	1.18	1.24
15000	0.21	0.22	74.68	81.86	1.33	1.19	1.27	1.14	1.19	1.30
16000	0.22	0.24	71.05	79.37	1.20	1.19	1.25	1.13	1.19	1.28
17000	0.19	0.21	67.00	78.15	1.18	1.11	1.23	1.09	1.14	1.17
18000	0.17	0.21	64.13	77.52	1.20	1.13	1.27	1.06	1.14	1.17

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Xtra Long Life USB/Ethernet RF SPDT

RC-8SPDT-A18

Typical Performance Data

TEST CONDITIONS: @Temperature = +45degC

FREQUENCY (MHz)	INSERTION LOSS ON (dB)		ISOLATION OFF (dB)		VSWR COM (:1)		VSWR COM->2 (:1)		VSWR COM->1 (:1)	
	COM-1	COM-2	COM-1	COM-2	ON	OFF	1	2	1	2
10	0.01	0.01	93.16	86.04	1.00	1.01	1.00	1.03	1.03	1.01
20	0.02	0.01	86.95	87.71	1.00	1.01	1.00	1.01	1.01	1.01
30	0.01	0.01	87.55	86.33	1.00	1.00	1.00	1.01	1.01	1.01
40	0.01	0.02	86.27	85.48	1.01	1.01	1.00	1.01	1.01	1.01
50	0.04	0.04	99.67	97.07	1.00	1.01	1.00	1.01	1.01	1.01
60	0.04	0.04	90.09	91.49	1.00	1.00	1.00	1.00	1.00	1.01
70	0.03	0.03	96.24	90.53	1.01	1.00	1.00	1.00	1.00	1.01
80	0.03	0.03	89.09	87.33	1.01	1.00	1.00	1.00	1.00	1.01
90	0.04	0.03	87.46	90.96	1.01	1.01	1.00	1.01	1.00	1.01
100	0.04	0.03	108.00	93.23	1.01	1.01	1.00	1.01	1.01	1.01
200	0.04	0.03	91.04	110.98	1.00	1.00	1.00	1.01	1.00	1.01
300	0.02	0.02	112.96	96.74	1.01	1.00	1.00	1.00	1.01	1.01
400	0.02	0.01	93.21	101.96	1.01	1.01	1.00	1.01	1.01	1.01
500	0.02	0.01	101.11	107.60	1.01	1.01	1.01	1.01	1.01	1.01
600	0.01	0.00	98.77	102.27	1.01	1.01	1.01	1.01	1.01	1.01
700	0.00	0.00	100.18	99.09	1.01	1.01	1.01	1.01	1.01	1.01
800	0.00	0.00	106.15	102.47	1.01	1.01	1.01	1.00	1.01	1.01
900	0.00	0.00	99.25	102.98	1.01	1.01	1.01	1.00	1.01	1.01
1000	0.00	0.01	99.90	105.39	1.01	1.01	1.02	1.01	1.01	1.02
1200	0.01	0.01	100.12	107.89	1.01	1.00	1.02	1.01	1.01	1.02
1400	0.01	0.02	100.50	102.06	1.01	1.01	1.02	1.00	1.01	1.02
1600	0.01	0.02	99.87	117.53	1.01	1.01	1.03	1.01	1.00	1.03
1800	0.01	0.02	102.17	97.27	1.01	1.01	1.04	1.01	1.01	1.04
2000	0.02	0.02	96.89	109.32	1.02	1.02	1.05	1.01	1.02	1.04
2200	0.02	0.03	102.64	101.47	1.02	1.02	1.05	1.01	1.01	1.04
2400	0.03	0.04	101.33	93.50	1.03	1.03	1.05	1.03	1.03	1.04
2600	0.03	0.04	106.77	100.51	1.03	1.04	1.07	1.04	1.04	1.06
2800	0.03	0.04	112.14	102.63	1.03	1.05	1.08	1.05	1.05	1.07
3000	0.03	0.04	113.00	99.01	1.04	1.06	1.08	1.05	1.05	1.07
3200	0.04	0.04	107.61	105.71	1.05	1.07	1.08	1.06	1.07	1.07
3400	0.05	0.06	107.98	114.40	1.07	1.09	1.09	1.08	1.09	1.08
3600	0.05	0.06	114.87	100.87	1.08	1.11	1.10	1.10	1.11	1.10
4000	0.06	0.07	98.83	101.56	1.11	1.13	1.11	1.11	1.13	1.10
4500	0.08	0.09	104.39	112.46	1.15	1.18	1.13	1.17	1.18	1.13
5000	0.09	0.10	97.43	101.23	1.19	1.19	1.12	1.18	1.18	1.13
5500	0.10	0.12	105.16	97.84	1.22	1.20	1.13	1.21	1.20	1.16
6000	0.10	0.12	99.05	98.10	1.24	1.19	1.12	1.21	1.19	1.15
6500	0.10	0.13	101.27	95.61	1.23	1.17	1.11	1.21	1.17	1.16
7000	0.10	0.14	95.68	94.61	1.22	1.15	1.11	1.20	1.15	1.16
7500	0.12	0.15	95.39	101.97	1.19	1.14	1.07	1.19	1.13	1.13
8000	0.12	0.15	93.75	92.47	1.16	1.14	1.08	1.20	1.14	1.15
8500	0.12	0.15	93.50	94.53	1.13	1.09	1.06	1.13	1.09	1.11
9000	0.12	0.15	95.48	90.98	1.08	1.08	1.05	1.11	1.08	1.11
9500	0.12	0.14	93.48	91.28	1.04	1.06	1.06	1.06	1.03	1.11
10000	0.13	0.15	93.06	92.02	1.03	1.06	1.05	1.03	1.05	1.09
12000	0.15	0.17	87.31	85.88	1.08	1.13	1.14	1.06	1.13	1.06
13000	0.18	0.21	86.93	83.67	1.12	1.18	1.21	1.10	1.19	1.11
14000	0.18	0.22	85.23	79.47	1.12	1.16	1.26	1.12	1.15	1.19
15000	0.17	0.22	81.58	75.73	1.11	1.07	1.24	1.07	1.06	1.24
16000	0.17	0.25	80.35	72.22	1.06	1.06	1.22	1.11	1.10	1.22
17000	0.16	0.24	78.82	68.49	1.04	1.09	1.30	1.14	1.15	1.19
18000	0.23	0.24	76.92	66.23	1.06	1.35	1.38	1.17	1.37	1.22

Notes






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Xtra Long Life USB/Ethernet RF SPDT Switch

RC-8SPDT-A18

Typical Performance Curves








Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

Xtra Long Life USB/Ethernet RF SPDT Switch

RC-8SPDT-A18

Typical Performance Curves



Notes






- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Xtra Long Life USB/Ethernet RF SPDT Switch

RC-8SPDT-A18

Typical Performance Curves



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

Case Style

LM

Outline Dimensions

LM1852



Notes:

1. Case material: Aluminum (with protective coating to prevent corrosion).
2. Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.03 inch; 3 Pl. ±.015 inch.
3. Weight: 2290 grams.
4. Marking may contain other features or characters for internal lot control.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	0° to 40° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-15° to 85°C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F class 3