

Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω

DC to 6 GHz

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA in greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

50Ω 978 to 1090 MHz

ZX75BP-1034-S+



Generic photo used for illustration purposes only

CASE STYLE: HY1238

Connectors	Model
SMA-MF	ZX75BP-1034-S+


Features

- Low Insertion loss
- High selectivity
- Good VSWR
- Connectorized package


Applications

- Traffic collision avoidance system (TCAS)
- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation system

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	1034	-	MHz
	Insertion Loss	F1-F2	-	0.8	2	dB
	VSWR	F1-F2	-	1.2	-	:1
Stop Band, Lower	Insertion Loss	DC-F3	20	30	-	dB
	VSWR	DC-F3	-	20	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	20	30	-	dB
	VSWR	F4-F5	-	20	-	:1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	5 W max.





* Passband rating, derate linearly to 3.5W at 85°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	98.10	8108.56	978	4.55
100	100.80	1484.13	984	4.43
790	37.31	77.83	989	4.33
815	30.51	68.12	992	4.28
850	20.72	46.16	996	4.22
880	11.60	20.22	1000	4.16
910	3.47	4.03	1008	4.06
920	2.00	2.42	1015	4.00
978	0.74	1.09	1020	3.95
1034	0.70	1.13	1025	3.91
1090	0.69	1.06	1030	3.88
1145	1.81	2.54	1034	3.85
1170	3.99	5.40	1040	3.83
1190	6.53	10.14	1045	3.81
1230	12.10	28.12	1050	3.80
1300	20.78	62.09	1055	3.78
1400	31.44	80.33	1060	3.77
1500	44.76	84.80	1070	3.77
1750	41.24	87.63	1080	3.80
2000	40.85	88.70	1090	3.87

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-004071
ZX75BP-1034-S+
EDU2729
URJ
201205
Page 2 of 3

Coaxial Connections

INPUT	SMA-MALE
OUTPUT	SMA-FEMALE

Outline Drawing



Outline Dimensions (^{inch}/_{mm})

A	B	C	D	E	F	G
1.20	.75	.46	1.18	.04	.17	1.00
30.48	19.05	11.68	29.97	1.02	4.32	25.40
H	J	K	L	M	N	Wt.
.50	.35	.18	.21	2.05	.106	grams
12.70	8.89	4.57	5.28	52.07	2.69	35.0

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	94.58	98.10	107.88	0.00	0.00	0.00	0.00	0.00	0.00
10	104.24	112.04	98.12	0.00	0.00	0.00	0.00	0.01	0.00
50	105.84	92.38	96.83	0.01	0.01	0.01	0.02	0.02	0.02
100	98.36	100.80	91.70	0.01	0.01	0.02	0.02	0.03	0.04
150	88.18	87.76	92.27	0.00	0.01	0.02	0.03	0.05	0.06
200	82.74	81.99	81.55	0.00	0.02	0.03	0.05	0.09	0.10
250	76.59	77.24	77.37	0.01	0.03	0.04	0.10	0.14	0.16
300	71.77	72.57	72.29	0.01	0.04	0.05	0.14	0.18	0.21
350	68.40	68.75	68.70	0.02	0.05	0.06	0.20	0.25	0.28
400	65.22	65.73	65.73	0.03	0.06	0.08	0.24	0.31	0.34
450	62.47	62.96	62.97	0.04	0.07	0.10	0.29	0.37	0.40
500	60.29	60.72	60.61	0.05	0.09	0.11	0.34	0.42	0.47
550	58.38	58.80	58.87	0.06	0.10	0.13	0.39	0.48	0.53
600	57.21	57.58	57.68	0.08	0.12	0.15	0.43	0.53	0.59
650	57.52	58.08	58.18	0.10	0.14	0.18	0.47	0.58	0.64
700	66.42	68.43	69.52	0.12	0.16	0.21	0.50	0.62	0.69
750	49.94	49.43	49.05	0.15	0.19	0.24	0.52	0.65	0.73
790	37.65	37.31	37.01	0.17	0.22	0.27	0.54	0.67	0.76
800	34.92	34.58	34.28	0.18	0.24	0.29	0.54	0.68	0.77
810	32.20	31.87	31.56	0.19	0.25	0.30	0.54	0.69	0.78
815	30.84	30.51	30.19	0.20	0.26	0.31	0.55	0.69	0.79
820	29.48	29.15	28.83	0.21	0.27	0.32	0.55	0.69	0.79
850	21.08	20.72	20.37	0.30	0.38	0.44	0.60	0.76	0.86
855	19.61	19.25	18.90	0.32	0.41	0.49	0.63	0.79	0.90
860	18.13	17.76	17.40	0.36	0.46	0.54	0.66	0.82	0.93
875	13.55	13.16	12.81	0.57	0.71	0.82	0.84	1.04	1.18
880	11.99	11.60	11.27	0.70	0.86	0.99	0.96	1.19	1.34
890	8.91	8.54	8.25	1.15	1.39	1.58	1.39	1.68	1.89
900	6.01	5.72	5.51	2.05	2.44	2.72	2.28	2.71	2.99
910	3.62	3.47	3.37	3.78	4.40	4.82	4.02	4.65	5.05
915	2.71	2.63	2.60	5.10	5.85	6.33	5.34	6.10	6.54
950	0.67	0.83	0.94	24.39	26.74	27.32	25.67	27.18	25.94
978	0.58	0.74	0.84	28.55	27.25	26.57	26.43	25.61	25.01
1034	0.54	0.70	0.78	23.90	24.01	25.83	26.13	26.55	29.21
1090	0.53	0.69	0.80	29.92	30.43	30.17	27.23	26.61	25.38
1100	0.55	0.72	0.83	23.84	23.67	23.32	22.04	21.55	20.86
1125	0.80	1.01	1.15	12.98	12.76	12.48	12.67	12.35	12.03
1150	1.84	2.13	2.34	6.31	6.21	6.07	6.47	6.35	6.22
1170	3.64	3.99	4.25	3.25	3.26	3.21	3.56	3.58	3.56
1200	7.54	7.92	8.19	1.19	1.27	1.31	1.62	1.75	1.83
1250	14.45	14.76	14.99	0.35	0.44	0.50	0.82	1.01	1.14
1275	17.58	17.88	18.08	0.25	0.34	0.39	0.73	0.93	1.06
1300	20.50	20.78	20.96	0.19	0.28	0.34	0.68	0.89	1.02
1350	25.93	26.19	26.35	0.16	0.23	0.29	0.64	0.85	0.98
1390	30.13	30.38	30.52	0.15	0.22	0.27	0.63	0.84	0.97
1400	31.19	31.44	31.58	0.15	0.22	0.27	0.63	0.84	0.96
1425	33.96	34.19	34.33	0.15	0.21	0.26	0.62	0.83	0.95
1450	36.97	37.16	37.30	0.15	0.21	0.26	0.62	0.83	0.94
1475	40.40	40.55	40.69	0.15	0.21	0.26	0.62	0.82	0.94
1500	44.68	44.76	44.89	0.15	0.20	0.25	0.62	0.82	0.93
1525	51.07	50.81	50.95	0.15	0.21	0.26	0.62	0.81	0.93
1550	68.90	66.18	66.10	0.15	0.21	0.26	0.61	0.81	0.92
1575	55.12	56.30	56.41	0.15	0.20	0.25	0.61	0.81	0.91
1600	49.24	49.94	50.12	0.15	0.20	0.25	0.62	0.81	0.91
1625	46.20	46.83	46.95	0.14	0.20	0.25	0.62	0.81	0.91
1650	44.28	44.85	44.97	0.15	0.21	0.26	0.63	0.81	0.90
1700	41.97	42.49	42.61	0.14	0.20	0.25	0.66	0.83	0.92
1800	40.04	40.54	40.61	0.13	0.20	0.25	0.71	0.87	0.96
1900	39.71	40.22	40.27	0.13	0.20	0.25	0.79	0.94	1.04
2000	40.31	40.85	40.90	0.12	0.20	0.26	0.87	1.05	1.16


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
978	4.60	4.55	4.51
980	4.55	4.50	4.46
982	4.51	4.47	4.43
984	4.47	4.43	4.39
986	4.43	4.39	4.35
988	4.39	4.35	4.31
990	4.35	4.31	4.28
992	4.32	4.28	4.25
994	4.29	4.25	4.22
996	4.26	4.22	4.19
998	4.23	4.20	4.17
1000	4.20	4.16	4.14
1002	4.17	4.14	4.11
1004	4.15	4.11	4.08
1006	4.12	4.09	4.07
1008	4.10	4.06	4.05
1010	4.08	4.05	4.03
1012	4.06	4.03	4.01
1014	4.04	4.01	3.99
1016	4.02	3.99	3.97
1018	4.00	3.97	3.95
1020	3.98	3.95	3.94
1022	3.96	3.93	3.92
1024	3.94	3.92	3.91
1026	3.93	3.90	3.89
1028	3.91	3.89	3.88
1030	3.90	3.88	3.87
1032	3.89	3.86	3.86
1034	3.88	3.85	3.84
1036	3.86	3.85	3.83
1038	3.85	3.83	3.82
1040	3.85	3.83	3.82
1042	3.84	3.82	3.81
1044	3.83	3.81	3.80
1046	3.82	3.81	3.80
1048	3.82	3.80	3.79
1050	3.81	3.80	3.79
1052	3.81	3.79	3.78
1054	3.80	3.78	3.77
1056	3.80	3.78	3.77
1058	3.79	3.78	3.77
1060	3.79	3.77	3.77
1062	3.79	3.78	3.77
1064	3.78	3.77	3.76
1066	3.79	3.77	3.77
1068	3.79	3.78	3.77
1070	3.79	3.77	3.77
1072	3.79	3.78	3.77
1074	3.80	3.79	3.79
1076	3.80	3.79	3.79
1078	3.80	3.80	3.79
1079	3.81	3.80	3.80
1080	3.81	3.80	3.80
1081	3.82	3.81	3.81
1082	3.82	3.82	3.82
1083	3.83	3.82	3.82
1084	3.82	3.82	3.82
1085	3.84	3.83	3.83
1088	3.85	3.84	3.86
1090	3.87	3.87	3.87

Typical Performance Curves



Typical Performance Curves




Case Style

HY

Outline Dimensions

HY1238



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT GRAMS
HY1238	1.20 (30.48)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.17 (4.32)	1.00 (25.40)	.50 (12.70)	.35 (8.89)	.18 (4.57)	.21 (5.28)	2.05 (52.07)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A