


Outline Dimensions



* OVERALL CONNECTOR OR CABLE & BOOT DIMENSION
(CONNECTOR SHAPE MAY VARY)

GM1133 SERIES
SMA FEMALE (CONN-1)
SMA MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					FEET	METERS	
GM1133-1	1.00	.30	.51 (12.95)	-	.42 (10.67)	.312 (7.92)	.06	.02	51
GM1133-1.5	1.50	.46					.06	.02	60
GM1133-1.64	1.64	.50					.06	.02	63
GM1133-2	2.00	.61					.06	.02	70
GM1133-3	3.00	.91					.09	.03	90
GM1133-3.28	3.28	1.00					.10	.03	95
GM1133-4	4.00	1.22					.12	.04	109
GM1133-5	5.00	1.52					.15	.05	129
GM1133-6	6.00	1.83					.18	.05	148
GM1133-6.56	6.56	2.00					.20	.06	159
GM1133-10	10.00	3.05					.30	.09	226
GM1133-16.4	16.40	5.00					.49	.15	351
GM1133-25	25.00	7.62					.75	.23	519
GM1133-32.8	32.80	10.00					.98	.30	671
GM1133-65.6	65.60	20.00					1.97	.60	1310

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

- Flexible Coaxial Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified