



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
UR2632	.900 (22.86)	1.600 (40.64)	.580 (14.73)	.140 (3.56)	1.320 (33.53)	.150 (3.81)	.080 (2.03)	.160 (4.06)	.178 (4.52)	.130 (3.30)	.090 (2.29)	.940 (23.88)	.680 (17.27)

CASE#	P	Q	R	S	T	U	V	W	WT.GRAM
UR2632	.600 (15.24)	.580 (14.73)	1.640 (41.66)	1.324 (33.64)	1.280 (32.51)	1.244 (31.61)	.110 (2.79)	.070 (1.78)	22.2

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13microns) Gold over 120-240 μ inch (3.05-6.10microns) Nickel plate.
All models, (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS