


Outline Dimensions

VS2537



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
VS2537	.750 (19.05)	.500 (12.70)	.210 (5.33)	.139 (3.53)	.070 (1.78)	.150 (3.81)	.060 (1.52)	.100 (2.54)	.157 (3.99)	.218 (5.54)	.167 (4.24)	.080 (2.03)

CASE#	N	P	Q	R	S	T	U	V	W	WT.GRAMS
VS2537	.790 (20.06)	.542 (13.77)	.385 (9.78)	.203 (5.16)	.540 (13.72)	.152 (3.86)	.237 (6.02)	.630 (16.00)	.380 (9.65)	2.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
 - For RoHS Case Styles: 3-5 μ inch Gold over 120-240 μ inch Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS