

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
100	0.12	32.3	31.7
200	0.17	30.6	29.9
300	0.21	40.0	38.9
400	0.24	33.9	33.6
500	0.28	29.3	28.9
600	0.30	33.7	33.3
700	0.33	39.4	39.3
800	0.35	29.2	29.1
900	0.38	30.1	30.1
1000	0.40	47.9	52.0
1100	0.42	30.4	30.1
1200	0.45	27.8	27.8
1300	0.46	33.7	34.4
1400	0.47	36.0	35.3
1500	0.50	27.9	28.0
1600	0.52	29.0	29.4
1800	0.55	30.6	30.4
2000	0.58	33.5	34.3
2500	0.65	33.6	33.5
3000	0.72	31.3	31.7
3500	0.75	32.1	29.1
4000	0.82	31.9	37.7
4500	0.88	31.8	27.6
5000	0.92	36.7	36.0
5500	1.00	28.7	26.1
6000	1.02	34.7	30.8
6500	1.06	39.2	38.5
7000	1.10	30.9	28.7
7500	1.13	36.9	31.1
8000	1.17	38.6	36.0
8500	1.19	30.3	28.4
9000	1.21	38.7	31.1
9500	1.31	26.3	30.1
10000	1.34	31.7	28.7
10500	1.36	36.7	31.5
11000	1.41	25.9	30.4
11500	1.50	30.9	30.0
12000	1.45	25.4	39.4
12500	1.54	29.6	26.7
13000	1.40	28.2	28.1
13500	1.63	22.7	23.7
14000	1.67	39.8	27.0
14500	1.73	26.7	22.4
15000	1.70	29.7	30.0
15500	1.75	27.9	23.6
16000	1.71	37.4	27.5
16500	1.78	25.0	21.2
17000	1.80	26.0	24.1
17500	1.84	25.2	22.0
18000	1.73	24.2	33.0