

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
100	0.13	27.9	27.6
200	0.20	25.9	25.8
300	0.23	33.6	34.4
400	0.27	32.4	32.7
500	0.30	25.8	25.8
600	0.33	28.9	29.1
700	0.36	39.6	40.2
800	0.38	26.5	26.7
900	0.42	26.1	26.2
1000	0.44	35.7	36.1
1100	0.46	29.6	29.9
1200	0.49	25.6	25.7
1300	0.51	29.8	29.9
1400	0.51	36.6	36.9
1500	0.54	26.8	27.0
1600	0.57	26.7	26.7
1800	0.59	29.9	30.5
2000	0.64	31.3	30.4
2500	0.70	31.6	31.9
3000	0.78	29.1	27.4
3500	0.81	40.2	37.0
4000	0.89	32.2	29.9
4500	0.96	39.4	34.6
5000	1.01	36.0	32.2
5500	1.08	27.3	23.8
6000	1.10	44.7	38.1
6500	1.16	33.3	28.7
7000	1.20	33.3	31.9
7500	1.24	32.0	28.8
8000	1.29	35.5	37.7
8500	1.32	33.5	31.6
9000	1.35	35.2	35.9
9500	1.43	27.8	30.8
10000	1.44	31.2	28.1
10500	1.44	25.0	28.4
11000	1.53	25.0	26.0
11500	1.62	24.3	27.8
12000	1.52	22.5	26.1
12500	1.72	23.1	25.9
13000	1.60	20.3	23.6
13500	1.86	23.2	25.0
14000	1.79	23.7	24.7
14500	1.60	24.9	26.9
15000	1.88	28.4	26.6
15500	1.86	28.2	28.7
16000	1.92	25.5	25.5
16500	1.94	25.8	24.1
17000	1.92	28.9	28.7
17500	2.00	27.1	24.1
18000	1.89	24.8	23.8