

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
100	0.06	34.3	34.0
200	0.09	28.9	28.6
300	0.12	26.8	26.7
400	0.14	26.8	26.8
500	0.16	28.8	28.8
600	0.17	34.2	34.5
700	0.18	42.5	42.6
800	0.19	32.4	32.2
900	0.21	28.2	28.0
1000	0.22	26.8	26.7
1100	0.24	27.4	27.3
1200	0.25	29.9	29.8
1300	0.26	35.3	34.9
1400	0.25	37.8	36.5
1500	0.26	32.1	31.7
1600	0.29	29.3	29.2
1800	0.31	30.0	29.4
2000	0.32	34.8	32.3
2500	0.34	30.3	29.1
3000	0.37	32.5	33.0
3500	0.39	32.6	28.6
4000	0.44	28.5	24.5
4500	0.45	37.8	33.0
5000	0.48	41.2	33.7
5500	0.55	33.2	26.2
6000	0.52	30.5	26.8
6500	0.57	36.9	37.6
7000	0.59	32.6	35.1
7500	0.61	36.0	37.8
8000	0.63	38.8	36.6
8500	0.65	31.6	35.1
9000	0.67	38.8	31.5
9500	0.71	31.5	27.8
10000	0.73	24.5	28.2
10500	0.75	33.3	26.4
11000	0.77	23.2	22.2
11500	0.80	20.7	21.8
12000	0.77	22.0	43.7
12500	0.88	24.2	23.2
13000	0.81	19.1	19.0
13500	0.86	22.7	23.1
14000	0.95	23.2	37.6
14500	0.67	21.9	21.3
15000	0.87	21.0	20.9
15500	0.92	29.4	22.9
16000	1.03	27.1	31.9
16500	0.92	28.3	24.3
17000	1.05	31.0	23.4
17500	0.97	22.4	23.9
18000	0.87	21.9	20.2