

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
100.0	0.04	38.3	38.6
150.0	0.05	36.4	36.2
200.0	0.06	35.4	35.2
250.0	0.07	35.4	35.4
300.0	0.08	36.0	35.7
350.0	0.08	37.5	37.1
400.0	0.09	40.0	39.8
450.0	0.09	45.6	44.1
550.0	0.11	49.5	49.6
600.0	0.11	42.4	42.2
650.0	0.12	39.4	39.5
700.0	0.12	38.0	37.9
750.0	0.13	37.4	36.9
800.0	0.14	37.7	37.4
850.0	0.14	38.8	38.2
900.0	0.14	41.1	40.0
950.0	0.15	44.1	43.2
1000.0	0.16	50.9	49.1
1200.0	0.17	37.7	40.3
1400.0	0.19	37.6	38.0
1600.0	0.20	44.1	53.8
1800.0	0.21	36.2	39.0
2000.0	0.23	38.9	39.4
2200.0	0.24	41.2	49.4
2400.0	0.25	34.3	35.9
2600.0	0.26	37.8	37.7
2800.0	0.27	36.8	43.4
3000.0	0.28	32.1	33.7
3500.0	0.31	31.7	33.7
4000.0	0.33	36.3	43.7
4500.0	0.35	37.4	43.5
5000.0	0.37	32.0	31.6
5020.0	0.37	33.2	32.7
5500.0	0.39	30.7	29.8
6000.0	0.41	28.7	28.9
6500.0	0.42	31.6	37.4
7000.0	0.43	32.7	41.2
7500.0	0.45	29.5	30.8
8000.0	0.47	26.9	26.0
8500.0	0.49	29.3	27.8
9000.0	0.51	38.9	37.1
9500.0	0.53	38.4	44.8
10000.0	0.54	31.3	29.6
10500.0	0.57	26.4	24.8
11000.0	0.57	24.3	24.4
11500.0	0.58	27.6	26.5
12000.0	0.60	30.9	32.1
12500.0	0.61	30.2	37.8
13000.0	0.64	25.5	25.0
13500.0	0.71	22.8	22.9
14000.0	0.75	21.3	21.2
14500.0	0.77	23.9	20.5
15000.0	0.78	24.4	28.1
15500.0	0.76	25.4	40.0
16000.0	0.77	24.5	24.9
16500.0	0.80	23.0	23.1
17000.0	0.82	22.5	23.1
17500.0	0.83	20.3	18.7
18000.0	0.84	19.0	18.7