

Bandpass Filter

SXBP-150+

50Ω 140 to 160 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2, 3, 4, 5, 6, 7

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	
.44	.74	.27	.200	.07	.060	
11.18	18.80	6.86	5.08	1.78	1.52	
G	H	J	K	L	M	wt.
.040	.660	.200	.470	.055	.060	grams
1.02	16.76	5.08	11.94	1.40	1.52	3.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)




- NOTE:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- high rejection
- good VSWR, 1.3:1 typ @ passband
- aqueous washable

Applications

- radio link
- receivers / transmitters
- professional mobile radio / public access mobile radio (PMR/ PAMR)



Generic photo used for illustration purposes only

CASE STYLE: HF1139


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
150	140 - 160	120	190	100	250 - 2400	1.3	1.8	20

Typical Frequency Response






Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	σ			
1.0	83.96	1.58	0.37	135.0	47.94
50.0	78.09	1.11	0.31	138.0	43.87
100.0	54.50	0.68	0.17	139.0	40.79
120.0	29.52	0.89	0.40	140.0	37.89
130.0	11.22	1.23	2.35	141.0	35.78
135.0	3.38	0.59	16.16	142.0	34.12
140.0	1.99	0.06	18.26	144.0	31.61
150.0	1.69	0.01	28.35	146.0	29.70
160.0	2.05	0.04	17.98	147.5	29.05
165.0	3.19	0.36	9.45	148.0	28.76
170.0	8.77	0.99	2.53	150.0	27.97
175.0	15.71	0.87	1.21	152.0	27.42
184.0	25.51	0.60	0.64	154.0	27.86
190.0	30.53	0.49	0.49	155.0	27.58
250.0	56.82	0.34	0.18	156.0	27.72
1000.0	88.44	3.18	0.15	158.0	27.64
2000.0	61.58	0.28	0.28	160.0	28.49
2400.0	55.81	0.21	0.29	165.0	36.48



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Band Pass Filter

SXBP-150+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
10	84.18	83.43	83.48	0.35	0.42	0.52	0.35	0.44	0.52
20	83.30	87.61	80.16	0.34	0.42	0.49	0.36	0.43	0.50
30	80.48	78.08	80.42	0.33	0.39	0.45	0.33	0.40	0.45
40	79.75	79.38	78.55	0.30	0.34	0.39	0.31	0.36	0.39
50	78.07	78.81	78.82	0.27	0.30	0.34	0.27	0.31	0.33
60	79.63	83.54	77.29	0.22	0.26	0.29	0.23	0.27	0.30
70	89.89	87.38	85.23	0.18	0.22	0.26	0.18	0.23	0.26
80	80.32	76.48	80.04	0.16	0.19	0.23	0.15	0.20	0.24
90	66.90	66.87	66.45	0.13	0.17	0.22	0.13	0.18	0.22
100	55.98	55.83	55.66	0.13	0.18	0.21	0.13	0.18	0.21
120	31.53	31.21	30.88	0.27	0.36	0.42	0.26	0.34	0.40
130	13.90	13.47	13.05	1.28	1.59	1.86	1.17	1.48	1.73
135	4.40	4.41	4.38	6.88	8.15	9.35	6.58	7.79	8.94
140	1.86	2.15	2.35	24.98	24.50	24.31	23.69	22.70	22.02
150	1.51	1.79	1.99	23.51	23.96	24.16	21.82	22.73	23.56
160	1.74	2.07	2.33	16.91	16.94	17.16	17.53	17.72	18.06
165	2.31	2.90	3.42	16.13	14.07	12.52	19.43	16.51	14.46
170	6.89	7.93	8.78	3.57	3.42	3.28	3.88	3.74	3.60
175	14.04	14.95	15.69	1.32	1.43	1.48	1.44	1.55	1.60
184	24.44	25.06	25.60	0.60	0.69	0.76	0.63	0.75	0.81
190	29.70	30.23	30.66	0.44	0.52	0.59	0.46	0.57	0.62
250	56.46	56.83	57.35	0.13	0.18	0.23	0.12	0.20	0.23
300	67.73	67.48	68.13	0.06	0.13	0.17	0.06	0.13	0.17
400	79.14	87.21	84.70	0.02	0.08	0.12	0.02	0.09	0.13
500	87.49	86.08	97.36	0.01	0.07	0.12	0.00	0.08	0.13
600	89.91	90.03	97.76	0.00	0.09	0.14	0.01	0.08	0.14
700	85.89	93.28	89.56	0.01	0.09	0.16	0.00	0.10	0.17
800	86.21	97.45	96.86	0.01	0.10	0.17	0.02	0.13	0.20
900	96.07	91.22	88.25	0.01	0.13	0.20	0.02	0.14	0.20
1000	87.75	94.95	84.53	0.00	0.13	0.21	0.01	0.14	0.21
1200	87.93	86.14	94.72	0.01	0.17	0.24	0.03	0.19	0.26
1300	85.08	90.84	83.18	0.03	0.19	0.27	0.05	0.22	0.31
1400	76.59	75.32	78.31	0.03	0.20	0.29	0.05	0.22	0.32
1500	70.41	71.02	69.89	0.03	0.20	0.31	0.05	0.22	0.32
1600	65.48	68.34	69.32	0.04	0.22	0.32	0.07	0.26	0.35
1700	65.33	64.44	74.31	0.05	0.25	0.36	0.09	0.27	0.38
1800	71.27	82.74	62.99	0.05	0.26	0.39	0.09	0.26	0.38
2000	73.25	61.52	65.50	0.08	0.28	0.40	0.08	0.31	0.43
2200	59.89	55.42	59.16	0.09	0.30	0.45	0.09	0.33	0.45
2300	56.97	61.78	58.36	0.09	0.32	0.45	0.11	0.34	0.48
2400	50.91	53.73	50.10	0.10	0.31	0.48	0.13	0.33	0.50
2500	50.71	51.53	49.97	0.13	0.34	0.51	0.10	0.37	0.51
2600	50.52	50.70	49.23	0.14	0.36	0.54	0.13	0.37	0.53
2700	50.06	50.40	52.80	0.09	0.35	0.51	0.13	0.37	0.55
2800	47.88	48.19	48.33	0.15	0.40	0.57	0.13	0.39	0.57
3000	42.07	47.58	43.81	0.11	0.40	0.59	0.15	0.45	0.64
3200	38.78	40.15	40.32	0.18	0.47	0.64	0.16	0.44	0.68
3300	37.42	39.21	38.11	0.15	0.46	0.65	0.20	0.56	0.75
3400	38.42	38.43	38.33	0.17	0.52	0.75	0.37	0.71	1.07
3500	35.19	36.58	36.62	0.21	0.62	0.88	0.73	1.49	1.95
3600	35.48	38.56	35.18	0.39	0.91	1.37	1.45	1.23	1.20
3700	38.48	37.11	35.81	1.29	1.41	1.29	0.40	0.75	1.04
3800	38.02	33.00	35.78	0.39	0.75	0.94	0.45	0.67	1.15
4000	30.42	27.95	30.00	0.28	0.70	0.95	0.35	0.89	1.09

REV. X2

SXBP-150+

101118

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

SXBP-150+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
80	15.92	2.43	28.52
85	1.08	2.02	9.30
90	3.96	2.79	1.63
95	1.45	5.61	2.04
100	3.12	2.81	4.79
105	4.27	4.93	4.69
108	4.95	4.37	4.26
110	5.30	4.65	4.80
115	5.71	6.30	6.31
118	7.07	7.56	7.66
120	8.23	8.51	8.72
125	12.48	13.06	13.67
128	17.78	18.80	19.75
130	23.75	25.14	26.41
135	45.61	45.75	45.87
138	45.68	44.43	43.38
140	40.13	39.06	38.25
141	37.47	36.65	36.04
142	35.30	34.71	34.23
143	33.63	33.20	32.85
144	32.34	32.04	31.77
145	31.26	31.03	30.81
146	30.44	30.22	30.07
147	29.73	29.59	29.45
148	29.14	29.05	28.99
149	28.66	28.60	28.57
150	28.32	28.30	28.26
151	28.06	28.05	28.09
152	27.86	27.90	27.97
153	27.79	27.82	27.85
154	27.72	27.77	27.83
155	27.69	27.75	27.86
156	27.75	27.86	27.94
157	27.86	27.99	28.14
158	28.03	28.23	28.47
159	28.41	28.71	29.09
160	29.02	29.48	29.96
165	36.30	36.58	36.66
168	36.72	35.31	33.96
170	31.87	29.87	28.23
175	16.95	16.04	15.17
178	11.97	11.51	11.06
180	9.82	9.42	9.11
185	6.48	6.28	6.30
188	5.30	5.18	5.11
190	4.64	4.69	4.61
195	3.51	3.52	3.54
198	3.03	3.06	3.11
200	2.88	2.86	2.78
205	2.39	2.44	2.45
300	1.32	1.07	1.47
305	0.57	0.97	0.43
400	3.16	1.18	9.44

REV. X2
SXBP-150+
101118
Page 2 of 2




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Typical Performance Curves




Outline Dimensions



 METALLIZATION
 SOLDER RESIST

PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.015 "; 3 Pl. ± 0.01 "

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.



NOTE:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: $.025 \pm .002$ ". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN DK (RAVON)	29 NOV 05
TOLERANCES ON:	CHECKED RZ (RAVON)	29 NOV 05
2 PL DECIMALS ±	APPROVED HH (RAVON)	29 NOV 05
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-230	OR
FILE:	98PL230	SCALE: 4:1	SHEET: 1 OF 1

Evaluation Board and Circuit



TB-368



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215