

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.06	45.7	41.7
200.0	0.09	43.8	44.7
400.0	0.13	37.6	39.2
600.0	0.16	35.5	35.9
800.0	0.18	39.5	35.1
900.0	0.19	46.0	40.6
1000.0	0.21	48.8	36.5
1200.0	0.23	37.6	37.2
1400.0	0.25	34.0	39.9
1600.0	0.27	35.4	45.5
1800.0	0.28	46.2	43.4
2000.0	0.30	39.6	40.2
2200.0	0.32	32.5	34.9
2400.0	0.33	33.9	32.7
2600.0	0.35	38.6	33.1
2800.0	0.36	38.2	35.0
3000.0	0.37	34.2	39.1
3200.0	0.39	33.1	40.4
3400.0	0.40	34.3	44.1
3600.0	0.41	37.3	40.2
3800.0	0.43	38.1	35.1
4000.0	0.45	32.9	29.1
4200.0	0.45	30.0	29.2
4400.0	0.47	31.5	28.5
4600.0	0.48	32.4	27.8
4800.0	0.49	29.6	29.7
5000.0	0.50	27.0	30.5
5500.0	0.53	27.0	25.2
6000.0	0.56	25.6	25.0
6500.0	0.60	23.3	23.2
7000.0	0.63	24.3	22.3
7500.0	0.65	24.7	21.5
8000.0	0.67	23.5	22.3
8500.0	0.69	25.0	21.5
9000.0	0.70	27.5	24.2
9500.0	0.72	25.7	26.4
10000.0	0.73	32.4	31.0
10500.0	0.76	35.2	35.7
11000.0	0.83	34.5	35.1
11500.0	0.85	27.8	31.8
12000.0	0.90	27.8	20.9
12500.0	0.90	27.5	20.8