

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
10.0	0.00	49.0	48.9
50.0	0.01	47.7	48.6
100.0	0.02	43.2	42.3
150.0	0.03	40.4	40.3
200.0	0.03	38.6	38.0
250.0	0.03	37.3	37.0
300.0	0.04	36.5	36.3
350.0	0.04	36.3	35.9
400.0	0.04	36.6	36.2
450.0	0.04	37.5	37.2
500.0	0.05	38.9	38.7
550.0	0.05	41.2	41.4
600.0	0.05	45.2	46.5
650.0	0.06	48.9	64.1
700.0	0.06	46.5	48.6
750.0	0.06	42.2	42.3
800.0	0.06	39.2	38.9
850.0	0.06	37.3	37.0
900.0	0.07	35.9	35.5
950.0	0.07	35.3	34.9
1000.0	0.07	35.1	34.6
1200.0	0.08	39.5	40.0
1400.0	0.08	42.7	43.0
1600.0	0.09	34.7	34.2
1800.0	0.10	35.2	35.2
2000.0	0.10	42.4	45.6
2200.0	0.11	39.9	39.2
2400.0	0.12	36.8	36.4
2600.0	0.12	40.6	42.9
2800.0	0.12	51.1	46.9
3000.0	0.13	40.9	39.4
3600.0	0.14	44.0	41.9
4000.0	0.15	44.8	48.5
4600.0	0.16	43.5	45.3
5000.0	0.17	34.0	33.0
5600.0	0.19	34.1	32.8
6000.0	0.20	39.3	40.1
6600.0	0.21	32.9	32.9
7000.0	0.22	29.8	28.9
7600.0	0.23	33.1	30.9
8000.0	0.24	30.1	28.8
8600.0	0.25	29.1	28.1
9000.0	0.26	33.2	31.0
9600.0	0.27	32.6	31.1
10000.0	0.28	31.0	30.7
10600.0	0.29	31.1	32.3
11000.0	0.31	27.3	27.6
11600.0	0.32	26.4	26.9
12000.0	0.33	28.3	33.8
12600.0	0.33	30.4	30.7
13000.0	0.34	29.8	27.1
13600.0	0.36	29.0	28.0
14000.0	0.37	31.1	32.1
14600.0	0.40	28.2	26.8
15000.0	0.41	28.8	32.6
15600.0	0.43	32.2	33.3
16000.0	0.47	24.6	23.9
16600.0	0.49	26.2	27.6
17000.0	0.50	30.7	34.2
17600.0	0.49	29.7	29.8
18000.0	0.49	22.9	23.5