

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.02	49.5	48.1
200.0	0.03	46.5	40.7
400.0	0.05	42.4	36.4
500.0	0.06	43.4	37.6
600.0	0.06	49.1	39.8
800.0	0.07	44.7	34.3
900.0	0.08	40.4	32.9
1000.0	0.09	39.4	33.9
1200.0	0.09	47.2	39.2
1400.0	0.10	42.5	33.6
1600.0	0.11	40.3	39.6
2000.0	0.12	40.1	35.0
2200.0	0.12	42.3	37.5
2400.0	0.13	50.0	32.0
2600.0	0.14	41.2	37.1
2800.0	0.15	46.6	30.3
3000.0	0.16	44.1	31.5
3200.0	0.15	39.0	32.6
3400.0	0.17	42.0	28.7
3600.0	0.17	37.0	35.2
3800.0	0.17	32.6	26.4
4000.0	0.16	35.7	27.0
4200.0	0.18	32.1	25.4
4400.0	0.18	29.3	21.7
4600.0	0.19	33.3	23.8
4800.0	0.18	28.6	20.7
5000.0	0.23	27.8	20.6
5200.0	0.20	29.9	21.9
5400.0	0.22	27.0	20.1
5600.0	0.23	28.1	22.4
5800.0	0.23	29.5	22.2
6000.0	0.25	26.6	21.7
6200.0	0.23	27.5	26.1
6400.0	0.25	27.9	23.8
6600.0	0.25	25.5	28.6
6800.0	0.24	29.7	26.6
7000.0	0.26	26.0	27.7
7400.0	0.25	27.2	29.9
7600.0	0.26	23.6	30.0
7800.0	0.27	24.8	22.3
8000.0	0.28	28.3	23.7
8200.0	0.26	25.7	22.3
8400.0	0.27	26.1	19.3
8600.0	0.28	25.2	19.4
8800.0	0.30	26.3	18.9
9000.0	0.30	28.4	18.6
9200.0	0.31	26.7	18.7
9400.0	0.34	26.1	18.3
9600.0	0.29	27.8	18.9
9800.0	0.31	27.4	20.5
10000.0	0.30	29.0	20.1
10200.0	0.30	29.0	20.1
10400.0	0.31	27.5	22.4
10600.0	0.33	31.1	21.2
11000.0	0.33	26.6	22.7
11200.0	0.36	24.3	22.5
12400.0	0.32	22.0	20.2
12500.0	0.31	20.9	18.9