

Surface Mount Bandpass Filter

SXBP-202+

50Ω 198 to 206 MHz



Generic photo used for illustration purposes only
CASE STYLE: HF1317

The Big Deal

- Flat group delay, (0.6 ns typical)
- Narrow band, (3.96% fractional Bandwidth)
- High Wideband rejection,
40 dB from 290-2000 MHz
- Miniature shielded package

Product Overview

The SXBP-202+ is a flat group delay bandpass filter fabricated using SMT technology. Covering 202 MHz $\pm$ 4 MHz, these units offer good matching within the passband and high rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Flat group delay characteristics	This model has a group delay flatness of 0.6 ns typical which in reducing the signal distortion
High rejection (40 dB)	Achieving 40 dB rejection over the wide stopband range 290-2000 MHz will be used for suppressing harmonics.
Small size, 0.44" x 0.74" x 0.19"	The surface mount package enables the SXBP-202+ to be used in compact designs.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Surface Mount Bandpass Filter

50 Ω 198 to 206 MHz

SXBP-202+



Generic photo used for illustration purposes only
CASE STYLE: HF1317

Features

- Flat group delay over passband, (0.6 ns typical)
- High rejection 40 dB
- Miniature shielded package
- Aqueous washable

Applications

- Test equipments
- Receivers / transmitters
- Harmonic rejection
- Military

Electrical Specifications at 25°C


Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	—	202	—	MHz
	Insertion Loss	F1-F2	198-206	—	3.4	5	dB
	VSWR	F1-F2	198-206	—	1.9	2.3	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-160	20	32	—	dB
	VSWR	DC-F3	DC-160	—	33	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	250-2700	20	31	—	dB
	VSWR	F4-F5	250-2700	—	27	—	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.4W max.

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	75.13	59.91	198.00	23.00
75	59.39	56.04	198.50	22.82
160	32.09	34.75	199.00	22.76
171	16.22	12.09	199.50	22.71
176	8.14	4.38	200.00	22.67
180	4.73	2.37	200.50	22.66
198	3.16	1.62	201.00	22.63
202	3.18	1.67	201.75	22.60
206	3.33	1.61	202.00	22.57
216	6.29	2.41	202.25	22.55
223	12.50	6.21	202.75	22.60
236	24.29	17.39	203.25	22.60
250	33.82	29.96	203.50	22.62
300	56.65	72.39	203.75	22.69
500	71.14	133.63	204.00	22.74
1000	74.29	96.51	204.50	22.83
1500	64.70	62.05	204.75	22.84
2000	50.37	57.91	205.00	22.86
2500	38.18	48.26	205.50	22.92
2700	34.48	46.96	206.00	23.03

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.C
M174392
SXBP-202+
EDU1490
URJ
200303
Page 2 of 3

Pad Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7


Demo Board MCL P/N: TB-368
Suggested PCB Layout (PL-230)



- NOTE:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	
.440	.740	.190	.200	.070	.060	
11.18	18.80	4.83	5.08	1.78	1.52	
G	H	J	K	L	M	Wt.
.040	.660	.200	.470	.055	.060	grams
1.02	16.76	5.08	11.94	1.40	1.52	3.0

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1.0	90.64	91.52	93.08	0.22	0.29	0.35	0.21	0.29	0.35
5.0	79.61	80.97	82.62	0.23	0.31	0.37	0.24	0.31	0.37
10.0	75.82	75.77	75.48	0.27	0.33	0.39	0.27	0.34	0.38
50.0	67.34	67.12	66.62	0.33	0.36	0.40	0.33	0.37	0.41
100.0	65.91	66.34	66.05	0.20	0.24	0.26	0.20	0.24	0.26
110.0	66.00	66.66	67.01	0.19	0.23	0.25	0.20	0.23	0.25
120.0	70.55	69.99	70.70	0.18	0.22	0.24	0.19	0.22	0.26
130.0	77.86	76.45	73.98	0.19	0.23	0.25	0.19	0.23	0.26
140.0	57.48	56.91	56.45	0.21	0.26	0.29	0.21	0.25	0.29
150.0	45.84	45.36	44.93	0.26	0.32	0.36	0.26	0.31	0.36
160.0	34.51	33.94	33.53	0.39	0.49	0.56	0.38	0.48	0.56
171.0	19.93	19.41	18.96	1.01	1.27	1.48	0.98	1.24	1.42
176.0	12.09	11.76	11.47	2.34	2.89	3.34	2.26	2.80	3.22
180.0	6.31	6.42	6.47	6.33	7.39	8.21	6.15	7.21	8.02
188.0	2.71	3.13	3.39	19.09	19.36	19.71	18.06	18.18	18.41
198.0	2.24	2.64	2.89	29.15	29.26	28.65	21.92	22.53	23.22
198.8	2.23	2.62	2.88	27.84	28.19	27.77	22.34	23.11	23.83
199.0	2.23	2.63	2.89	27.50	27.85	27.47	22.50	23.33	24.04
199.8	2.22	2.62	2.89	26.57	26.96	26.64	23.00	23.92	24.68
200.0	2.22	2.62	2.88	26.32	26.68	26.37	23.18	24.14	24.89
200.5	2.23	2.62	2.89	25.89	26.21	25.89	23.58	24.59	25.29
200.8	2.23	2.62	2.89	25.70	25.96	25.67	23.82	24.84	25.47
201.0	2.22	2.62	2.89	25.50	25.75	25.42	24.05	25.08	25.65
201.5	2.22	2.62	2.88	25.19	25.36	25.00	24.54	25.53	25.93
201.8	2.22	2.62	2.89	25.04	25.17	24.81	24.78	25.73	26.07
202.0	2.22	2.62	2.89	24.92	25.01	24.62	25.04	25.94	26.15
202.5	2.23	2.64	2.91	24.69	24.67	24.27	25.59	26.31	26.24
202.8	2.23	2.64	2.92	24.60	24.54	24.11	25.85	26.46	26.26
203.0	2.23	2.63	2.91	24.49	24.37	23.96	26.09	26.56	26.24
203.5	2.23	2.65	2.93	24.29	24.12	23.69	26.61	26.75	26.15
203.8	2.24	2.65	2.93	24.20	23.98	23.56	26.81	26.76	26.06
204.0	2.24	2.66	2.94	24.10	23.88	23.45	27.00	26.78	25.96
204.5	2.24	2.67	2.95	23.94	23.69	23.28	27.30	26.71	25.72
204.8	2.26	2.68	2.96	23.86	23.59	23.21	27.36	26.64	25.59
205.0	2.26	2.68	2.97	23.81	23.52	23.14	27.42	26.54	25.46
205.5	2.27	2.70	3.00	23.67	23.44	23.09	27.36	26.29	25.17
205.8	2.28	2.71	3.00	23.60	23.40	23.08	27.31	26.16	25.06
206.0	2.29	2.71	3.01	23.56	23.38	23.08	27.21	26.02	24.94
216.0	3.34	4.14	4.72	14.49	12.70	11.49	13.99	12.33	11.28
220.0	5.54	6.61	7.39	6.43	5.97	5.61	6.49	6.03	5.68
223.0	8.26	9.36	10.17	3.67	3.61	3.52	3.77	3.70	3.60
230.0	15.50	16.36	17.00	1.44	1.57	1.62	1.52	1.65	1.71
240.0	24.25	24.82	25.25	0.72	0.83	0.89	0.76	0.87	0.94
250.0	30.95	31.34	31.64	0.48	0.57	0.62	0.51	0.60	0.65
300.0	50.68	50.87	50.94	0.19	0.23	0.26	0.19	0.25	0.28
400.0	68.99	69.18	69.70	0.08	0.11	0.13	0.09	0.13	0.16
500.0	79.91	81.39	79.71	0.04	0.09	0.11	0.05	0.10	0.12
600.0	101.93	88.41	85.99	0.03	0.08	0.11	0.05	0.09	0.11
800.0	90.00	93.34	103.75	0.03	0.09	0.12	0.05	0.11	0.13
1000.0	85.85	89.51	92.29	0.03	0.11	0.13	0.04	0.11	0.15
1500.0	79.57	77.75	84.58	0.08	0.17	0.20	0.12	0.20	0.23
2000.0	68.52	65.91	65.98	0.10	0.19	0.24	0.11	0.20	0.25
2200.0	62.39	61.26	61.63	0.14	0.23	0.30	0.13	0.23	0.30
2500.0	60.99	59.73	59.45	0.18	0.31	0.39	0.16	0.30	0.36
2700.0	54.63	52.36	52.45	0.21	0.35	0.43	0.17	0.32	0.40
2750.0	45.72	45.34	51.72	0.23	0.38	0.44	0.19	0.34	0.40


Typical Performance Data

FREQ.	OUTPUT RETURN LOSS		
(MHz)	(nsec)		
	@-40°C	@+25°C	@+85°C
198.0	23.17	23.08	23.03
198.3	23.08	23.07	22.95
198.5	22.97	22.85	22.86
198.8	22.95	22.89	22.88
199.0	23.01	22.88	22.86
199.3	22.86	22.78	22.82
199.5	22.88	22.79	22.84
199.8	22.74	22.71	22.76
200.0	22.72	22.78	22.75
200.3	22.73	22.67	22.70
200.5	22.65	22.64	22.68
200.8	22.73	22.76	22.77
201.0	22.59	22.61	22.57
201.3	22.65	22.71	22.72
201.5	22.69	22.66	22.68
201.8	22.59	22.63	22.65
202.0	22.64	22.66	22.58
202.3	22.61	22.63	22.63
202.5	22.55	22.60	22.59
202.8	22.61	22.62	22.64
203.0	22.51	22.59	22.61
203.3	22.55	22.63	22.71
203.5	22.64	22.63	22.71
203.8	22.62	22.70	22.67
204.0	22.68	22.72	22.78
204.3	22.60	22.69	22.78
204.5	22.65	22.67	22.73
204.8	22.70	22.81	22.84
205.0	22.71	22.80	22.86
205.3	22.77	22.79	22.95
205.5	22.82	22.92	22.94
205.8	22.79	22.89	22.99
206.0	22.82	22.97	23.09


Typical Performance Curves



Typical Performance Curves



Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.



NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025" ± .002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES


TOLERANCES ON:

2 PL DECIMALS ± .005

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-230

REV:
OR

FILE: 98PL230


SCALE: 4:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-368



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215