










## Typical Performance Curves




## Typical Performance Curves


OUTPUT IP3 vs. FREQUENCY & TEMPERATURE  
OUTPUT POWER = -5 dBm, VDD = +5V




OUTPUT IP3 vs. FREQUENCY & DEVICE VOLTAGE  
OUTPUT POWER = -5 dBm, Temperature = +25°C




P1dB vs. FREQUENCY & TEMPERATURE  
VDD = +5V




P1dB vs. FREQUENCY & DEVICE VOLTAGE  
Temperature = +25°C



NOISE FIGURE vs. FREQUENCY & TEMPERATURE  
VDD = +5V



NOISE FIGURE vs. FREQUENCY & DEVICE VOLTAGE  
Temperature = +25°C



GAIN VARIATIONS VS FREQUENCY & TEMPERATURE  
INPUT POWER = -25 dBm, VDD = +5V

