

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
500	42.66	1191.08	224.71
550	41.97	745.57	221.30
600	41.34	750.55	191.01
650	40.80	779.72	261.72
695	40.37	619.61	170.03
700	40.32	651.00	160.47
750	39.92	779.60	181.91
800	39.54	629.67	143.67
850	39.26	633.01	114.99
900	39.10	698.21	223.39
950	38.94	650.87	157.08
1000	38.89	899.24	165.35
1100	39.09	1437.07	160.43
1300	41.48	1162.63	479.49
1400	45.03	521.66	1673.10
1500	54.31	320.55	853.42
1600	43.63	192.32	7469.57
1700	35.27	131.41	350.24
1800	29.34	87.63	161.96
1910	23.80	52.95	82.74
2000	19.22	31.39	47.47
2200	8.86	6.04	7.51
2400	3.29	1.33	1.60
2410	3.27	1.37	1.60
2420	3.25	1.42	1.60
2430	3.25	1.45	1.60
2440	3.25	1.49	1.60
2450	3.25	1.50	1.59
2460	3.27	1.52	1.58
2470	3.29	1.53	1.56
2480	3.32	1.53	1.53
2490	3.35	1.53	1.51
2500	3.40	1.53	1.48
2600	4.89	2.13	2.03
2800	13.99	11.80	12.84
3000	24.36	32.26	40.79
3200	37.06	56.69	66.49
3400	35.15	80.85	110.93
3600	30.74	104.48	145.73
3800	28.58	126.13	154.17
4000	27.18	150.74	381.82
4200	26.19	162.80	350.91
4400	25.38	164.66	252.02
4600	24.67	154.86	241.41
4800	24.02	138.29	193.10
4820	23.95	134.74	196.35
4840	23.89	134.03	185.48
4860	23.82	133.60	169.67
4880	23.76	130.70	152.38
4900	23.71	126.40	148.98
4920	23.65	125.53	153.98
4940	23.57	124.94	158.78
4960	23.50	122.85	161.77
4980	23.43	123.67	154.37
5000	23.38	120.74	142.17
5500	21.73	74.03	84.56
6000	20.45	45.73	44.94
6500	20.06	35.31	34.54
7000	20.87	39.02	35.67
7200	21.49	44.04	39.86
7250	21.66	45.97	41.46
7300	21.86	47.80	42.17
7350	22.04	49.93	44.26
7400	22.25	52.46	45.48
7450	22.45	55.16	48.08
7500	22.67	58.78	50.95
7600	23.10	65.17	58.49
7700	23.54	72.76	64.99
7800	23.97	83.38	72.66
7900	24.39	94.57	79.52
8000	24.77	107.96	86.59