


Digital Step Attenuator


Typical Performance Curves

DAT-31R5A-PN+


Thru Loss




Step Attenuation (0.5dB)




Step Attenuation (1dB)




Step Attenuation (2dB)




Step Attenuation (4dB)




Step Attenuation (8dB)



Step Attenuation (16dB)











Step Attenuation (31.5dB)



Digital Step Attenuator

Typical Performance Curves

DAT-31R5A-PN+




Digital Step Attenuator


Typical Performance Curves

DAT-31R5A-PN+


Output Return Loss (0dB)




Output Return Loss (0.5dB)




Output Return Loss (1dB)




Output Return Loss (2dB)




Output Return Loss (4dB)



Output Return Loss (8dB)



Output Return Loss (16dB)



Output Return Loss (31.5dB)

