



THE BIG DEAL

- Low Insertion Loss, 0.3dB Typ.
- Return Loss, 10dB Typ.
- 0603 Surface Mount Footprint
- Versatile "Place Holder" for Mini-Circuits LTCC Filters
- Power Handling: 7.5W



Generic photo used for illustration purposes only

APPLICATIONS

- Test and Measurement Equipment
- Communication, EW, Radar, and ECM Defense Systems
- 5G MIMO and Back Haul Radio Systems
- Satellite Communications

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

TPCW-183+ is a miniature low temperature co-fired ceramic (LTCC) 50 Ohm transmission line, with low insertion loss through 18GHz that supports a variety of applications. This model provides 0.3dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in a tiny 0603 ceramic form factor with inspectable wrap-around terminations, the transmission line is ideal for dense signal chain PCB layouts, where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Footprint Compatible "Thru-Line"	Enables system designers the flexibility to plan to add LTCC filters to the PCB layout at a later stage in the design process, after system test results are available. Compatible with Mini-Circuits low pass filters (LFCW series), with identical case style and pad connections.
LTCC Construction	The use of LTCC technology allows for repeatable performance in a rugged ceramic package, well suited for tough environments such as high humidity and temperature extremes. See Mini-Circuits Environmental Rating ENV06T11 for more information.
Tiny Size, 0603	0603 package allows for space to be saved in dense circuit board layouts, while also minimizing the effects of parasitics.
Wrap-around Terminations	Provides excellent solderability and easy visual inspection.
Rugged Power Handling, 7.5W	Handles up to 7.5 Watts in a small 0603 package.



LTCC SURFACE MOUNT

Thru-Line

TPCW-183+

Mini-Circuits

50Ω DC to 18 GHz

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Pass Band	Insertion Loss	DC-F1	DC - 10	—	0.2	0.7	dB
		F1-F2	10 - 15	—	0.3	0.9	
		F2-F3	15 - 18	—	1.1	—	
	Return Loss	DC-F1	DC - 10	—	16	—	dB
		F1-F2	10 - 15	—	10	—	
		F2-F3	15 - 18	—	9	—	
	Group Delay	DC-F3	DC - 18	—	155	—	psec

1. Tested on Evaluation Board P/N TB-TPCW-183+

2. Bi-directional RF1 and RF2 ports can be interchanged


ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁴	7.5W @ 25°C

3. Permanent damage may occur if any of these limits are exceeded.

4. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 2.6W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C





LTCC SURFACE MOUNT




Thru-Line

TPCW-183+

Mini-Circuits

50Ω DC to 18 GHz

TYPICAL PERFORMANCE GRAPHS





Mini-Circuits

LTCC SURFACE MOUNT

Thru-Line

TPCW-183+

50Ω DC to 18 GHz

FUNCTIONAL DIAGRAM





Figure 1. TPCW-183+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1 ²	1	Connects to RF Input Port
RF2 ²	3	Connects to RF Output Port
GROUND	4,2	Connects to Ground on PCB, (See drawing PL-650)
NC	—	No connection, not used internally. See drawing PL-650 for connection to PCB

SUGGESTED PCB LAYOUT (PL-650)




NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4835 Lo Pro) WITH DIELECTRIC THICKNESS .0107±.0010. COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Figure 2. Suggested PCB Layout PL-650

CASE STYLE DRAWING



Weight: .005 grams.

Dimensions are in inches (mm). Tolerances: 3Pl. ± .004

PRODUCT MARKING*: WH

*Marking may contain other features or characters for internal lot control.



LTCC SURFACE MOUNT

Thru-Line

TPCW-183+

Mini-Circuits

50Ω DC to 18 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD. [CLICK HERE](#)

Performance Data and Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	JC0603C-1 Lead Finish: Nickel-Tin
RoHS Status	Compliant
Tape and Reel	TR-F75
Suggested Layout for PCB Design	PL-650
Evaluation Board	TB-TPCW-183+
	Gerber File
Environmental Rating	ENV06T11

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html








Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(GHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
0.01	0.03	0.03	0.04	59.53	53.23	52.37	62.42	54.49	52.15
0.10	0.04	0.04	0.05	55.84	51.26	46.43	55.98	51.47	47.77
0.20	0.05	0.04	0.06	49.68	48.16	45.04	50.43	48.70	45.54
0.25	0.05	0.04	0.06	47.31	47.18	44.89	48.22	47.84	45.25
0.30	0.05	0.04	0.06	45.71	46.44	44.57	46.58	47.20	45.04
0.35	0.05	0.04	0.06	45.04	45.81	44.06	45.51	46.71	44.82
0.40	0.05	0.04	0.06	45.06	45.29	43.48	45.03	46.28	44.53
0.50	0.05	0.04	0.07	45.38	44.42	42.52	45.19	45.60	44.05
0.55	0.05	0.04	0.07	45.13	43.97	42.14	45.47	45.35	43.93
0.60	0.05	0.04	0.07	44.71	43.51	41.83	45.72	45.12	43.86
0.65	0.05	0.05	0.07	44.17	42.97	41.51	45.93	44.89	43.77
0.70	0.06	0.05	0.07	43.71	42.47	41.22	46.14	44.63	43.67
0.75	0.06	0.05	0.07	43.31	41.99	40.91	46.27	44.33	43.49
0.80	0.06	0.05	0.08	42.94	41.52	40.57	46.49	44.06	43.38
0.85	0.06	0.05	0.08	42.60	41.08	40.21	46.68	43.77	43.25
0.90	0.07	0.06	0.08	42.36	40.71	39.90	46.93	43.50	43.19
0.95	0.07	0.06	0.09	42.17	40.34	39.61	47.21	43.23	43.14
1.00	0.07	0.06	0.09	42.06	40.02	39.37	47.49	42.96	43.10
1.05	0.07	0.06	0.09	41.93	39.72	39.16	47.76	42.68	43.03
1.10	0.08	0.07	0.09	41.68	39.36	38.91	47.96	42.38	42.91
1.15	0.08	0.07	0.10	41.36	39.01	38.68	47.99	42.06	42.73
1.20	0.08	0.07	0.10	40.94	38.68	38.46	47.78	41.70	42.47
2.00	0.09	0.08	0.11	36.05	34.95	35.47	38.11	36.45	37.15
2.50	0.11	0.10	0.14	33.72	33.73	34.07	34.09	34.23	34.32
3.00	0.12	0.11	0.14	32.65	33.35	33.34	32.14	32.88	32.57
3.50	0.12	0.12	0.15	32.83	33.88	33.03	31.47	32.48	31.66
4.00	0.14	0.13	0.17	33.98	35.46	33.18	31.57	32.89	31.48
4.50	0.13	0.13	0.17	36.55	37.65	33.55	32.52	33.67	31.72
5.00	0.14	0.14	0.17	39.05	38.78	34.18	33.58	34.44	32.58
5.50	0.14	0.14	0.17	38.53	37.46	34.15	34.39	34.85	33.50
6.00	0.14	0.14	0.17	35.90	35.72	33.08	34.65	35.23	33.77
6.50	0.14	0.14	0.18	34.41	34.32	31.64	35.50	35.86	33.33
7.00	0.15	0.14	0.18	32.87	32.17	29.36	35.74	34.46	31.08
7.50	0.16	0.16	0.20	30.42	28.64	26.75	32.78	30.01	27.95
8.00	0.19	0.18	0.23	27.14	25.07	24.19	28.19	25.67	24.83
8.50	0.22	0.23	0.27	23.75	22.02	21.59	24.19	22.27	21.87
9.00	0.27	0.28	0.32	21.09	19.68	19.43	21.28	19.80	19.57
9.50	0.31	0.33	0.38	19.09	18.01	17.82	19.21	18.11	17.93
10.00	0.36	0.37	0.42	17.57	16.94	16.67	17.66	17.03	16.78
10.50	0.39	0.39	0.45	16.71	16.45	16.08	16.78	16.54	16.19
11.00	0.40	0.39	0.44	16.34	16.47	16.02	16.43	16.59	16.16
11.50	0.38	0.36	0.42	16.44	16.92	16.42	16.58	17.11	16.61
12.00	0.35	0.33	0.38	16.97	17.84	17.27	17.13	18.09	17.51
12.50	0.32	0.30	0.35	18.06	19.18	18.64	18.08	19.35	18.79
13.00	0.28	0.27	0.32	19.56	20.75	20.22	19.26	20.57	20.11
13.50	0.28	0.28	0.33	21.15	21.99	21.54	20.30	21.23	21.06
14.00	0.29	0.30	0.35	21.99	22.08	21.70	20.49	20.97	21.06
14.50	0.34	0.35	0.40	20.85	20.76	20.37	19.65	19.88	20.08
14.53	0.34	0.35	0.40	20.76	20.67	20.29	19.60	19.82	20.04
14.55	0.34	0.36	0.41	20.67	20.58	20.19	19.54	19.75	19.97
14.58	0.34	0.36	0.41	20.57	20.49	20.10	19.48	19.66	19.90
15.00	0.40	0.42	0.47	18.82	18.79	18.45	18.30	18.45	18.73
15.50	0.48	0.50	0.56	16.67	16.67	16.44	16.80	16.91	17.20
15.53	0.48	0.50	0.56	16.57	16.58	16.36	16.72	16.82	17.13
16.00	0.58	0.60	0.67	14.58	14.70	14.51	15.20	15.28	15.51
16.50	0.69	0.72	0.79	12.80	12.89	12.77	13.64	13.63	13.86
16.55	0.71	0.73	0.81	12.63	12.73	12.61	13.47	13.47	13.68
17.00	0.83	0.86	0.94	11.20	11.33	11.21	12.11	12.10	12.25
17.50	1.00	1.04	1.13	9.91	10.05	9.91	10.80	10.81	10.88
18.00	1.14	1.18	1.28	8.94	9.07	8.94	9.76	9.80	9.83

Typical Performance Data

FREQ.	GROUP DELAY		
(GHz)	(psec)		
	@-55°C	@+25°C	@+125°C
0.01	162.68	155.89	165.66
0.50	152.33	152.55	154.71
1.00	152.13	152.17	154.27
1.50	151.96	151.98	154.13
2.00	151.93	151.93	154.10
2.50	151.85	151.84	154.02
3.00	152.00	152.01	154.16
3.50	152.13	152.10	154.23
4.00	152.29	152.25	154.31
4.50	152.64	152.50	154.57
5.00	152.72	152.62	154.64
5.50	152.82	152.70	154.73
6.00	153.02	152.94	154.98
6.50	153.23	153.11	155.19
7.00	153.49	153.40	155.47
7.50	153.75	153.71	155.76
8.00	154.12	153.96	156.04
8.50	154.17	153.92	156.01
9.00	154.21	153.88	155.96
9.50	154.12	153.68	155.76
10.00	153.92	153.45	155.51
10.50	153.83	153.50	155.44
11.00	153.87	153.78	155.68
11.50	154.08	154.15	156.08
12.00	154.73	154.95	156.90
12.50	155.74	155.81	157.99
13.00	156.80	156.92	159.03
13.50	157.35	157.43	159.58
14.00	158.71	158.05	160.40
14.50	158.99	158.79	161.03
15.00	159.55	159.39	161.54
15.53	160.04	159.98	162.10
15.55	160.07	159.99	162.12
16.00	160.33	160.56	162.69
16.50	160.84	160.74	162.89
16.53	160.78	160.66	162.84
16.55	160.78	160.63	162.87
16.58	160.81	160.69	162.88
17.00	160.55	160.49	162.81
17.50	159.75	159.87	161.88
18.00	159.61	159.15	161.22



Typical Performance Curves



Outline Dimensions

JC0603C-1

PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
JC0603C-1	.063 (1.60)	.031 (0.80)	.024 (0.60)	.018 (0.45)	.028 (0.70)	.006 (0.15)	.012 (0.30)	.100 (2.54)	.071 (1.80)	.032 (0.80)	.028 (0.70)

CASE #	M*	N	P	Q	R	WT. GRAMS
JC0603C-1	.012 (0.30)	.049 (1.24)	.026 (0.65)	.016 (0.40)	.014 (0.35)	.005

Dimensions are in inches (mm). Tolerances: 3 Pl. $\pm .004$

Notes:

1. Open style, ceramic base.
2. Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
- 3.* - Line width should be designed to match 50 OHMS characteristic impedance, depending on PCB material & thickness.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F74

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles

GE0805C-1
GE0805C-1AP
JV1210C-1
GU2939




ILLUSTRATION 2

Applicable Case Styles

JV1210C
JV1210C-2
JV1210C-3
JV1210C-4
JV1210C-5
JV1210C-6
JV1210C-11




ILLUSTRATION 3

Applicable Case Styles

JC0603C-8
JV1210C-7
JV1210C-8
JV1210C-9
JV1210C-10
JV1210C-13
GE0805C-13

Tape Width, mm	Device Cavity Pitch, mm	Real Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	2000
				4000

Note: Small reel availability varies by model. Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

THIRD ANGLE PROJECTION		REVISIONS				
	REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
	OR	M175765	NEW RELEASE	AUG 19	DDR	VC
	A	M175661	DESIGN CHANGED	NOV 19	DDR	VC

SUGGESTED MOUNTING CONFIGURATION
FOR JC0603C-1 CASE STYLE



NOTES:


- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04835 Lo Pro) WITH DIELECTRIC THICKNESS $.0107 \pm .0010$. COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235	
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	DDR	05 AUG 19	PL, JC0603C-1, TB-1114+			
	CHECKED	RV	05 AUG 19				
	APPROVED	RKS	05 AUG 19				
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS. ASHEETA1.DWG REV:A DATE:01/12/95							
SIZE A		CODE IDENT 15542		DRAWING NO: 98-PL-650		REV: A	
FILE: 98PL650		SCALE: 16:1		SHEET: 1 OF 1			

Evaluation Board and Circuit

TB-TPCW-183+



Notes:

1. PCB Material: ROGERS (R04835 Lo Pro) OR Equivalent, Dielectric Constant= $3.48 \pm .05$

Dielectric Thickness: $.0107 \pm .0010$

2. 50 Ohm 2.92mm Female Connectors.

3. Connectors on the test board shall not be subjected to temperature greater than 200°C to avoid permanent damage to the connectors.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Test B,B1, 95% Coverage
Thermal Shock	-40° to +125°C, 15 min dwell, 100 cycles	MIL-STD-202, Method 107
Bend Test	1mm, deflection for 5 seconds Span of bending: 2.75"	--
High Temp Storage	125°C to 1000 Hrs	---