

MMIC Amplifier

ERA-21SM+

Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions
or to view GRAPHS.**

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 40mA, Vd = 3.50V @Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.66	18.86	39.58	32.42	1.12	0.62	28.75	12.28	3.32
100	14.69	18.89	41.22	31.61	1.12	0.62	28.72	12.46	3.44
200	14.63	18.89	37.68	30.57	1.12	0.61	28.85	12.36	3.29
400	14.50	18.83	33.45	28.09	1.12	0.61	28.33	12.13	3.37
600	14.35	18.81	30.60	25.84	1.13	0.60	28.10	12.37	3.34
800	14.18	18.76	28.90	24.14	1.14	0.59	28.17	12.01	3.46
1000	14.01	18.76	26.30	22.79	1.15	0.58	28.52	11.78	3.40
1200	13.85	18.76	24.44	21.62	1.16	0.57	28.51	11.78	3.48
1400	13.69	18.75	22.98	20.75	1.17	0.56	28.21	12.03	3.49
1600	13.52	18.79	21.63	19.98	1.18	0.55	28.23	11.65	3.52
1800	13.34	18.80	20.58	19.47	1.19	0.54	28.19	11.65	3.53
2000	13.18	18.81	19.90	19.22	1.21	0.53	27.85	11.88	3.45
2200	12.99	18.84	18.95	18.92	1.22	0.52	27.49	12.01	3.57
2400	12.81	18.86	18.20	18.77	1.24	0.51	27.25	11.75	3.58
2600	12.62	18.92	17.64	18.70	1.26	0.50	27.19	11.36	3.55
2800	12.42	18.92	16.77	18.51	1.27	0.49	27.00	11.53	3.57
3000	12.21	19.00	16.52	18.55	1.30	0.47	26.67	11.87	3.41
3200	12.01	19.06	15.69	18.39	1.32	0.46	26.35	11.60	3.44
3400	11.81	19.07	15.26	18.24	1.34	0.45	26.13	10.94	3.60
3600	11.58	19.15	14.86	17.93	1.37	0.44	25.82	11.17	3.67
3800	11.39	19.24	14.30	17.70	1.39	0.43	25.79	11.64	3.70
4000	11.20	19.27	13.67	17.11	1.41	0.42	25.28	11.39	3.67
4200	10.96	19.37	13.32	16.93	1.45	0.41	25.18	10.76	3.66
4400	10.77	19.43	12.70	16.51	1.47	0.40	25.20	10.93	3.77
4600	10.55	19.51	12.27	16.00	1.50	0.39	24.87	11.53	3.97
4800	10.38	19.59	11.71	15.69	1.52	0.39	24.58	11.20	3.99
5000	10.14	19.68	11.06	15.44	1.55	0.38	24.14	10.29	4.16
5200	9.90	19.72	10.85	15.21	1.59	0.37	24.14	10.15	4.08
5400	9.73	19.82	10.38	15.17	1.61	0.36	23.75	10.83	4.14
5600	9.49	19.90	9.93	14.97	1.64	0.35	23.28	10.65	4.20
5800	9.26	20.06	9.83	14.98	1.70	0.34	23.31	10.16	4.28
6000	9.08	20.11	9.49	15.21	1.72	0.33	23.27	9.54	4.20
6200	8.87	20.14	9.31	15.48	1.75	0.32	22.77	10.03	4.28
6400	8.76	20.21	9.28	15.99	1.78	0.31	22.62	10.35	4.54
6600	8.52	20.24	8.95	16.12	1.81	0.30	22.55	10.00	4.63
6800	8.39	20.37	8.99	16.57	1.86	0.29	22.26	9.14	4.75
7000	8.27	20.44	8.83	17.16	1.89	0.29	22.18	9.55	4.71
7200	8.14	20.49	8.71	17.58	1.92	0.28	21.91	9.78	4.76
7600	7.97	20.66	8.32	18.37	1.97	0.27	21.56	8.60	5.16
8000	7.91	21.02	7.94	19.15	2.03	0.26	20.85	9.06	5.29

REV. X1
ERA-21SM+
090319
Page 1 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 32mA, Vd = 3.43V @Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.38	18.67	29.70	63.88	1.12	0.61	25.00	9.96	3.29
100	14.42	18.67	30.39	51.24	1.12	0.61	24.95	10.43	3.38
200	14.37	18.68	30.42	43.31	1.12	0.61	25.08	10.19	3.28
400	14.23	18.63	30.23	35.34	1.13	0.60	24.71	9.89	3.34
600	14.09	18.58	30.29	31.01	1.13	0.60	24.61	10.36	3.32
800	13.93	18.55	30.30	28.15	1.14	0.59	24.67	10.02	3.45
1000	13.76	18.55	27.75	25.98	1.15	0.58	25.13	9.93	3.38
1200	13.60	18.54	25.86	24.30	1.16	0.57	25.45	9.79	3.45
1400	13.47	18.53	24.18	23.07	1.17	0.56	25.17	10.17	3.46
1600	13.29	18.57	22.59	22.05	1.18	0.55	25.39	9.85	3.49
1800	13.12	18.58	21.44	21.33	1.20	0.54	25.61	9.91	3.48
2000	12.96	18.60	20.49	20.98	1.21	0.53	25.44	10.03	3.42
2200	12.79	18.62	19.46	20.58	1.22	0.52	25.11	10.24	3.50
2400	12.61	18.65	18.62	20.33	1.24	0.51	25.08	10.02	3.52
2600	12.41	18.69	17.96	20.23	1.26	0.50	25.28	9.79	3.53
2800	12.22	18.72	16.95	19.95	1.27	0.49	25.29	9.95	3.52
3000	12.02	18.80	16.64	19.90	1.30	0.47	24.98	10.36	3.33
3200	11.82	18.86	15.75	19.70	1.32	0.46	24.74	10.22	3.40
3400	11.63	18.89	15.27	19.46	1.34	0.45	24.85	9.84	3.55
3600	11.39	18.98	14.86	19.08	1.37	0.44	24.75	9.97	3.62
3800	11.21	19.06	14.24	18.77	1.40	0.43	24.57	10.35	3.63
4000	11.02	19.12	13.63	18.11	1.42	0.42	24.27	10.35	3.61
4200	10.79	19.23	13.23	17.84	1.45	0.40	24.24	9.88	3.61
4400	10.59	19.31	12.59	17.41	1.48	0.40	24.44	9.93	3.72
4600	10.38	19.38	12.16	16.86	1.51	0.39	24.12	10.48	3.88
4800	10.19	19.48	11.59	16.53	1.53	0.38	23.78	10.37	3.88
5000	9.96	19.58	10.96	16.25	1.56	0.37	23.49	9.61	4.06
5200	9.73	19.65	10.71	16.03	1.60	0.36	23.42	9.39	3.98
5400	9.55	19.74	10.25	16.02	1.62	0.35	23.08	10.04	4.03
5600	9.30	19.84	9.78	15.82	1.66	0.34	22.73	10.01	4.12
5800	9.08	19.98	9.67	15.87	1.71	0.33	22.68	9.54	4.20
6000	8.89	20.08	9.35	16.16	1.74	0.32	22.66	8.87	4.09
6200	8.69	20.12	9.15	16.48	1.78	0.31	22.29	9.47	4.17
6400	8.56	20.22	9.10	17.08	1.81	0.30	22.16	9.74	4.43
6600	8.33	20.27	8.78	17.26	1.85	0.29	22.07	9.35	4.55
6800	8.19	20.40	8.81	17.79	1.90	0.28	21.84	8.58	4.62
7000	8.06	20.48	8.63	18.50	1.93	0.27	21.74	8.96	4.57
7200	7.93	20.55	8.51	19.02	1.96	0.27	21.49	9.20	4.61
7600	7.76	20.77	8.11	19.97	2.02	0.26	21.23	8.02	5.00
8000	7.67	21.17	7.71	20.92	2.09	0.24	20.42	8.49	5.12

REV. X1
ERA-21SM+
090319
Page 2 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I_{cc} = 48mA, V_d = 3.57V @Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.81	18.99	41.00	28.39	1.12	0.62	31.49	13.62	3.37
100	14.86	19.03	42.49	27.80	1.12	0.62	31.49	13.61	3.49
200	14.79	19.03	39.95	27.17	1.12	0.61	31.59	13.67	3.33
400	14.67	18.96	32.71	25.48	1.12	0.61	30.81	13.47	3.40
600	14.49	18.93	29.22	23.72	1.13	0.60	30.34	13.56	3.35
800	14.32	18.89	27.33	22.42	1.14	0.59	30.21	13.07	3.51
1000	14.15	18.90	25.07	21.30	1.15	0.58	30.20	12.61	3.45
1200	13.99	18.89	23.40	20.32	1.16	0.57	29.85	12.81	3.52
1400	13.84	18.89	22.09	19.59	1.17	0.57	29.47	13.03	3.55
1600	13.66	18.90	20.94	18.96	1.18	0.56	29.18	12.45	3.58
1800	13.48	18.95	19.99	18.52	1.19	0.54	28.92	12.37	3.59
2000	13.32	18.95	19.37	18.34	1.21	0.53	28.34	12.78	3.52
2200	13.13	18.97	18.51	18.08	1.22	0.52	28.01	12.94	3.62
2400	12.94	18.99	17.89	17.96	1.24	0.51	27.74	12.40	3.63
2600	12.74	19.03	17.43	17.93	1.25	0.50	27.52	11.87	3.60
2800	12.55	19.05	16.57	17.77	1.27	0.49	27.19	12.06	3.64
3000	12.34	19.12	16.38	17.82	1.30	0.48	26.92	12.47	3.45
3200	12.13	19.17	15.58	17.72	1.32	0.46	26.62	12.04	3.52
3400	11.94	19.18	15.21	17.58	1.34	0.46	26.24	11.26	3.66
3600	11.70	19.26	14.87	17.31	1.37	0.44	25.88	11.62	3.77
3800	11.51	19.34	14.30	17.10	1.39	0.43	25.89	12.18	3.76
4000	11.33	19.37	13.69	16.58	1.41	0.43	25.44	11.76	3.74
4200	11.08	19.46	13.34	16.38	1.44	0.41	25.33	11.08	3.74
4400	10.90	19.52	12.77	16.02	1.47	0.41	25.32	11.33	3.87
4600	10.66	19.58	12.33	15.51	1.49	0.40	24.93	11.98	4.04
4800	10.49	19.64	11.77	15.24	1.52	0.39	24.57	11.54	4.11
5000	10.26	19.73	11.16	14.97	1.54	0.38	24.22	10.59	4.25
5200	10.02	19.78	10.90	14.73	1.58	0.37	24.14	10.41	4.19
5400	9.86	19.83	10.47	14.68	1.59	0.37	23.74	11.17	4.22
5600	9.61	19.94	10.00	14.45	1.63	0.36	23.27	10.97	4.33
5800	9.38	20.06	9.90	14.46	1.68	0.35	23.33	10.39	4.43
6000	9.22	20.13	9.61	14.64	1.71	0.34	23.27	9.84	4.34
6200	9.01	20.14	9.43	14.86	1.73	0.33	22.83	10.39	4.41
6400	8.89	20.20	9.40	15.30	1.76	0.32	22.65	10.66	4.68
6600	8.66	20.23	9.07	15.41	1.79	0.31	22.76	10.32	4.78
6800	8.53	20.31	9.13	15.76	1.83	0.30	22.38	9.52	4.89
7000	8.39	20.39	8.98	16.29	1.87	0.30	22.24	9.87	4.85
7200	8.27	20.41	8.86	16.66	1.89	0.29	21.98	10.12	4.91
7600	8.12	20.56	8.48	17.35	1.93	0.28	21.67	8.90	5.28
8000	8.06	20.89	8.11	18.04	1.98	0.27	20.82	9.41	5.45

REV. X1
ERA-21SM+
090319
Page 3 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 40mA, Vd = 3.68V @Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.63	18.85	34.77	36.29	1.12	0.61	29.60	12.43	2.93
100	14.69	18.86	33.26	35.93	1.12	0.62	29.57	12.72	2.99
200	14.65	18.82	33.37	34.13	1.12	0.62	29.73	12.61	2.88
400	14.51	18.77	32.51	31.00	1.12	0.61	29.30	12.40	2.91
600	14.37	18.73	31.58	27.64	1.13	0.61	29.17	12.68	2.87
800	14.21	18.69	30.72	25.36	1.13	0.60	29.26	12.38	2.98
1000	14.06	18.68	27.59	23.75	1.14	0.59	29.70	12.26	2.92
1200	13.91	18.65	25.57	22.31	1.15	0.58	29.85	12.18	2.95
1400	13.76	18.67	23.79	21.24	1.16	0.57	29.51	12.43	2.99
1600	13.59	18.70	22.17	20.42	1.17	0.56	29.62	12.15	3.02
1800	13.44	18.68	20.78	19.66	1.18	0.56	29.67	12.18	3.02
2000	13.27	18.72	20.40	19.54	1.19	0.54	29.28	12.35	2.93
2200	13.09	18.73	19.35	19.26	1.21	0.53	28.90	12.48	3.00
2400	12.92	18.75	18.61	19.04	1.22	0.52	28.75	12.28	3.02
2600	12.74	18.78	17.87	18.93	1.24	0.51	28.77	12.10	3.03
2800	12.55	18.80	17.13	18.84	1.25	0.50	28.59	12.22	3.03
3000	12.34	18.89	16.74	18.80	1.28	0.49	28.30	12.50	2.87
3200	12.13	18.97	15.96	18.56	1.30	0.47	28.16	12.30	2.93
3400	11.98	18.92	15.44	18.48	1.31	0.47	27.99	11.90	3.01
3600	11.74	19.02	15.07	18.17	1.34	0.45	27.78	12.08	3.12
3800	11.54	19.13	14.47	17.84	1.37	0.44	27.78	12.38	3.07
4000	11.38	19.14	13.81	17.25	1.38	0.44	27.24	12.25	3.11
4200	11.10	19.31	13.64	16.90	1.43	0.42	27.38	11.82	3.05
4400	10.98	19.29	12.89	16.55	1.43	0.42	27.31	12.01	3.19
4600	10.70	19.38	12.37	15.86	1.47	0.41	27.15	12.47	3.31
4800	10.58	19.44	11.85	15.69	1.48	0.40	26.60	12.19	3.37
5000	10.36	19.51	11.13	15.28	1.50	0.39	26.44	11.49	3.53
5200	10.07	19.56	10.90	14.86	1.54	0.38	26.48	11.34	3.48
5400	9.96	19.60	10.35	14.92	1.55	0.38	25.93	11.89	3.46
5600	9.73	19.63	9.75	14.63	1.56	0.37	25.50	11.67	3.54
5800	9.54	19.86	9.82	14.86	1.63	0.36	25.49	11.24	3.60
6000	9.41	20.05	9.82	15.15	1.67	0.34	25.54	10.85	3.61
6200	9.17	19.96	9.44	15.18	1.68	0.34	25.18	11.24	3.60
6400	8.98	19.92	9.34	15.34	1.70	0.33	25.12	11.37	3.86
6600	8.79	19.94	8.94	15.59	1.71	0.32	25.07	11.12	3.85
6800	8.72	20.04	9.00	16.10	1.75	0.31	24.77	10.56	3.95
7000	8.60	20.26	9.12	16.72	1.82	0.30	24.86	10.81	3.94
7200	8.48	20.30	8.93	17.15	1.84	0.30	24.47	10.89	4.06
7600	8.26	20.37	8.27	17.72	1.85	0.29	23.97	9.89	4.34
8000	8.27	20.80	8.00	18.59	1.92	0.28	23.45	10.24	4.57

REV. X1
ERA-21SM+
090319
Page 4 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 32mA, Vd = 3.61V @Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.40	18.60	28.55	44.51	1.12	0.62	25.55	9.86	2.90
100	14.45	18.67	28.39	44.92	1.12	0.62	25.49	10.43	2.93
200	14.41	18.65	28.51	43.02	1.12	0.61	25.67	10.16	2.84
400	14.28	18.59	28.78	39.32	1.12	0.61	25.37	9.78	2.90
600	14.14	18.53	29.71	33.37	1.13	0.60	25.32	10.41	2.86
800	14.00	18.49	30.91	29.42	1.14	0.60	25.40	10.06	2.97
1000	13.84	18.48	28.55	26.90	1.14	0.59	25.88	10.02	2.90
1200	13.69	18.48	26.93	24.86	1.15	0.58	26.27	9.83	2.93
1400	13.54	18.47	24.92	23.39	1.16	0.57	25.95	10.28	2.96
1600	13.38	18.50	23.09	22.28	1.17	0.56	26.29	9.94	2.99
1800	13.24	18.50	21.49	21.32	1.18	0.55	26.56	10.10	2.98
2000	13.08	18.53	20.98	21.12	1.20	0.54	26.29	10.17	2.88
2200	12.90	18.54	19.88	20.75	1.21	0.53	25.97	10.41	2.97
2400	12.73	18.57	18.94	20.46	1.22	0.52	25.94	10.18	2.98
2600	12.56	18.60	18.15	20.29	1.24	0.51	26.24	10.03	2.97
2800	12.37	18.64	17.32	20.13	1.25	0.50	26.32	10.18	2.98
3000	12.17	18.72	16.88	20.07	1.28	0.48	26.11	10.64	2.82
3200	11.97	18.80	16.07	19.73	1.30	0.47	25.90	10.55	2.87
3400	11.81	18.76	15.49	19.63	1.31	0.46	26.09	10.26	2.98
3600	11.58	18.87	15.04	19.24	1.34	0.45	26.06	10.41	3.06
3800	11.39	18.98	14.47	18.81	1.37	0.44	26.05	10.72	3.02
4000	11.22	18.99	13.76	18.14	1.38	0.43	25.61	10.82	3.04
4200	10.94	19.17	13.58	17.71	1.43	0.41	25.69	10.54	3.00
4400	10.80	19.17	12.80	17.34	1.44	0.41	25.96	10.56	3.10
4600	10.54	19.27	12.31	16.59	1.47	0.40	25.77	11.06	3.22
4800	10.43	19.34	11.75	16.41	1.49	0.39	25.42	10.98	3.30
5000	10.20	19.39	11.06	16.00	1.51	0.39	25.14	10.48	3.43
5200	9.91	19.46	10.83	15.57	1.55	0.38	25.20	10.35	3.40
5400	9.81	19.51	10.25	15.65	1.55	0.37	24.90	10.86	3.42
5600	9.57	19.58	9.64	15.37	1.57	0.36	24.44	10.81	3.46
5800	9.37	19.82	9.71	15.62	1.64	0.35	24.44	10.41	3.53
6000	9.23	20.02	9.67	15.96	1.69	0.33	24.44	10.01	3.47
6200	9.00	19.95	9.30	16.04	1.70	0.33	24.19	10.44	3.51
6400	8.81	19.90	9.20	16.23	1.72	0.32	24.08	10.60	3.76
6600	8.63	19.95	8.80	16.54	1.74	0.31	23.91	10.27	3.75
6800	8.54	20.07	8.83	17.16	1.77	0.30	23.78	9.72	3.86
7000	8.41	20.30	8.92	17.87	1.85	0.29	23.66	10.06	3.86
7200	8.30	20.36	8.74	18.36	1.87	0.28	23.50	10.15	3.93
7600	8.08	20.46	8.10	19.04	1.89	0.28	23.20	9.16	4.22
8000	8.08	20.92	7.80	20.04	1.96	0.26	22.56	9.51	4.41

REV. X1
ERA-21SM+
090319
Page 5 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 48mA, Vd = 3.75V @Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.79	18.94	48.32	31.05	1.12	0.62	32.63	13.97	3.00
100	14.83	18.96	38.77	30.74	1.11	0.62	32.47	14.13	3.06
200	14.79	18.95	38.94	29.83	1.12	0.62	32.60	14.09	2.88
400	14.67	18.90	34.63	27.83	1.12	0.61	32.08	13.89	2.97
600	14.51	18.83	31.17	25.34	1.12	0.61	31.70	14.01	2.89
800	14.35	18.81	29.23	23.57	1.13	0.60	31.73	13.64	3.01
1000	14.19	18.80	26.50	22.24	1.14	0.59	31.92	13.38	2.95
1200	14.03	18.79	24.54	21.05	1.15	0.58	31.64	13.43	3.00
1400	13.89	18.78	22.93	20.15	1.16	0.58	31.26	13.64	3.02
1600	13.71	18.81	21.48	19.43	1.17	0.56	31.02	13.24	3.05
1800	13.56	18.83	20.19	18.76	1.18	0.56	30.68	13.22	3.06
2000	13.38	18.85	19.89	18.69	1.19	0.54	30.18	13.51	2.98
2200	13.22	18.83	18.95	18.45	1.20	0.54	29.92	13.61	3.08
2400	13.04	18.86	18.29	18.27	1.22	0.53	29.72	13.26	3.08
2600	12.86	18.89	17.62	18.17	1.23	0.51	29.51	12.90	3.08
2800	12.66	18.93	16.94	18.12	1.25	0.50	29.09	13.04	3.08
3000	12.45	19.00	16.62	18.13	1.28	0.49	29.00	13.35	2.92
3200	12.23	19.08	15.86	17.92	1.30	0.47	28.72	13.01	2.97
3400	12.08	19.02	15.36	17.84	1.31	0.47	28.51	12.37	3.08
3600	11.86	19.12	15.02	17.60	1.34	0.46	28.19	12.68	3.16
3800	11.64	19.21	14.47	17.30	1.36	0.44	28.12	13.15	3.14
4000	11.48	19.22	13.83	16.75	1.38	0.44	27.77	12.82	3.17
4200	11.20	19.38	13.63	16.43	1.43	0.42	27.59	12.26	3.09
4400	11.07	19.37	12.91	16.10	1.43	0.42	27.63	12.53	3.24
4600	10.81	19.46	12.41	15.43	1.46	0.41	27.29	13.06	3.36
4800	10.69	19.50	11.89	15.27	1.47	0.40	27.07	12.67	3.44
5000	10.47	19.56	11.18	14.85	1.50	0.40	26.64	11.85	3.59
5200	10.18	19.63	10.95	14.45	1.53	0.39	26.53	11.71	3.56
5400	10.07	19.64	10.42	14.47	1.54	0.38	26.06	12.33	3.52
5600	9.84	19.68	9.81	14.17	1.55	0.38	25.60	12.05	3.65
5800	9.64	19.91	9.90	14.36	1.62	0.36	25.81	11.61	3.71
6000	9.50	20.06	9.90	14.64	1.66	0.35	25.81	11.25	3.72
6200	9.27	19.97	9.54	14.64	1.67	0.34	25.42	11.65	3.69
6400	9.08	19.91	9.42	14.75	1.68	0.34	25.12	11.76	3.96
6600	8.90	19.92	9.03	14.97	1.70	0.33	25.26	11.54	3.97
6800	8.83	20.03	9.13	15.43	1.73	0.32	25.05	10.99	4.07
7000	8.71	20.23	9.21	16.00	1.79	0.31	24.97	11.24	4.07
7200	8.59	20.26	9.04	16.39	1.81	0.31	24.52	11.27	4.17
7600	8.39	20.31	8.42	16.86	1.83	0.30	24.35	10.31	4.52
8000	8.40	20.69	8.15	17.63	1.88	0.29	23.56	10.72	4.73

REV. X1
ERA-21SM+
090319
Page 6 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 40mA, Vd = 3.38V @Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.60	18.83	38.84	32.43	1.12	0.61	28.43	12.18	3.66
100	14.63	18.87	43.91	31.24	1.12	0.61	28.39	12.23	3.80
200	14.57	18.87	37.01	30.16	1.12	0.61	28.41	12.15	3.65
400	14.43	18.82	33.53	27.65	1.13	0.60	27.86	11.89	3.71
600	14.26	18.79	30.09	25.61	1.14	0.59	27.48	12.07	3.71
800	14.10	18.76	28.70	24.16	1.14	0.59	27.43	11.66	3.85
1000	13.92	18.75	26.35	22.99	1.15	0.58	27.59	11.31	3.79
1200	13.75	18.77	24.54	21.92	1.17	0.57	27.42	11.39	3.87
1400	13.59	18.77	23.28	21.05	1.18	0.56	27.08	11.68	3.91
1600	13.41	18.78	21.79	20.34	1.19	0.55	26.94	11.19	3.94
1800	13.23	18.78	20.69	19.78	1.20	0.54	26.78	11.09	3.94
2000	13.07	18.81	19.79	19.45	1.22	0.53	26.31	11.41	3.88
2200	12.87	18.83	18.85	19.16	1.23	0.52	25.94	11.60	3.97
2400	12.69	18.87	18.20	19.01	1.25	0.50	25.70	11.16	4.01
2600	12.48	18.93	17.61	18.87	1.27	0.49	25.50	10.69	4.00
2800	12.28	18.95	16.67	18.59	1.29	0.48	25.18	10.84	4.01
3000	12.06	19.02	16.49	18.62	1.31	0.46	24.84	11.22	3.84
3200	11.84	19.11	15.68	18.35	1.34	0.45	24.58	10.83	3.90
3400	11.66	19.09	15.18	18.17	1.36	0.44	24.26	10.12	4.07
3600	11.39	19.22	14.84	17.85	1.40	0.43	23.87	10.36	4.14
3800	11.19	19.32	14.24	17.62	1.43	0.42	23.86	10.89	4.21
4000	11.00	19.34	13.59	17.09	1.44	0.41	23.36	10.54	4.14
4200	10.76	19.41	13.06	16.80	1.48	0.40	23.21	9.78	4.15
4400	10.55	19.51	12.55	16.50	1.51	0.39	23.18	9.97	4.29
4600	10.26	19.60	12.09	15.84	1.55	0.38	22.82	10.69	4.50
4800	10.14	19.67	11.63	15.84	1.57	0.37	22.42	10.32	4.54
5000	9.89	19.79	11.11	15.67	1.60	0.36	22.14	9.31	4.68
5200	9.62	19.82	10.87	15.39	1.64	0.35	22.05	9.06	4.58
5400	9.44	19.93	10.44	15.39	1.67	0.34	21.58	9.87	4.67
5600	9.20	19.91	9.80	15.18	1.68	0.34	21.15	9.78	4.80
5800	9.02	20.18	9.97	15.55	1.76	0.32	21.20	9.17	4.87
6000	8.85	20.38	9.62	15.92	1.81	0.31	21.03	8.40	4.72
6200	8.63	20.34	9.44	16.16	1.83	0.30	20.58	9.05	4.88
6400	8.38	20.31	9.25	16.16	1.87	0.30	20.43	9.45	5.14
6600	8.34	20.73	9.16	17.32	1.95	0.28	20.39	8.96	5.27
6800	8.23	20.72	8.97	18.04	1.96	0.27	20.06	8.03	5.36
7000	8.09	20.82	8.75	18.81	2.00	0.26	19.95	8.49	5.33
7200	7.91	20.82	8.71	19.20	2.03	0.26	19.79	8.81	5.35
7600	7.67	20.96	8.35	20.03	2.09	0.25	19.30	7.44	5.79
8000	7.54	21.35	8.00	21.04	2.18	0.23	18.55	8.02	5.88

REV. X1
ERA-21SM+
090319
Page 7 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 32mA, Vd = 3.31V @Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.29	18.59	29.69	53.24	1.12	0.61	24.84	9.99	3.61
100	14.35	18.64	31.46	52.08	1.12	0.61	24.80	10.37	3.72
200	14.28	18.64	30.81	44.41	1.13	0.61	24.90	10.20	3.63
400	14.15	18.59	30.43	35.14	1.13	0.60	24.45	9.86	3.69
600	14.00	18.54	29.91	31.07	1.14	0.59	24.27	10.32	3.69
800	13.82	18.52	29.95	28.45	1.15	0.58	24.28	9.97	3.82
1000	13.65	18.51	27.58	26.54	1.16	0.57	24.66	9.81	3.74
1200	13.50	18.50	25.88	24.88	1.17	0.56	24.88	9.71	3.81
1400	13.35	18.54	24.38	23.65	1.18	0.55	24.54	10.07	3.87
1600	13.17	18.54	22.73	22.63	1.19	0.54	24.69	9.74	3.87
1800	13.00	18.55	21.55	21.87	1.20	0.53	24.77	9.75	3.87
2000	12.83	18.59	20.40	21.38	1.22	0.52	24.64	9.89	3.79
2200	12.66	18.60	19.34	20.97	1.23	0.51	24.28	10.10	3.89
2400	12.47	18.65	18.52	20.69	1.25	0.50	24.20	9.89	3.92
2600	12.25	18.70	17.83	20.49	1.27	0.49	24.23	9.49	3.92
2800	12.06	18.74	16.84	20.11	1.29	0.48	24.15	9.66	3.91
3000	11.86	18.82	16.54	20.09	1.32	0.46	23.81	10.12	3.74
3200	11.64	18.90	15.71	19.70	1.34	0.45	23.53	9.92	3.81
3400	11.45	18.91	15.17	19.50	1.36	0.44	23.48	9.33	3.97
3600	11.19	19.03	14.81	19.03	1.40	0.42	23.19	9.47	4.05
3800	11.01	19.13	14.20	18.76	1.43	0.41	23.09	9.96	4.09
4000	10.81	19.17	13.50	18.13	1.45	0.41	22.67	9.85	4.03
4200	10.56	19.24	12.97	17.80	1.48	0.40	22.59	9.18	4.05
4400	10.36	19.37	12.45	17.44	1.51	0.38	22.64	9.27	4.18
4600	10.07	19.45	12.00	16.74	1.55	0.37	22.35	9.95	4.38
4800	9.94	19.57	11.52	16.75	1.58	0.37	21.99	9.72	4.38
5000	9.70	19.68	10.96	16.57	1.61	0.36	21.66	8.81	4.56
5200	9.44	19.73	10.72	16.26	1.65	0.35	21.58	8.52	4.45
5400	9.25	19.81	10.30	16.28	1.68	0.34	21.20	9.29	4.55
5600	9.01	19.85	9.65	16.07	1.70	0.33	20.78	9.22	4.66
5800	8.83	20.15	9.80	16.50	1.79	0.31	20.81	8.70	4.71
6000	8.66	20.36	9.45	16.98	1.84	0.30	20.62	7.85	4.57
6200	8.44	20.33	9.27	17.28	1.86	0.29	20.32	8.52	4.71
6400	8.17	20.29	9.06	17.31	1.89	0.28	20.11	8.97	4.98
6600	8.13	20.74	8.96	18.62	1.99	0.27	20.08	8.45	5.11
6800	8.01	20.79	8.76	19.56	2.00	0.26	19.74	7.36	5.19
7000	7.87	20.87	8.54	20.50	2.04	0.25	19.71	7.96	5.15
7200	7.69	20.90	8.48	20.96	2.08	0.24	19.43	8.25	5.17
7600	7.43	21.07	8.12	22.01	2.15	0.23	19.05	6.76	5.65
8000	7.30	21.52	7.75	23.35	2.25	0.22	18.25	7.48	5.68

REV. X1
ERA-21SM+
090319
Page 8 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



MMIC Amplifier

ERA-21SM+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 48mA, Vd = 3.44V @Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	14.77	18.95	38.84	28.03	1.12	0.62	31.27	13.29	3.71
100	14.80	19.01	40.24	27.33	1.12	0.62	31.30	13.08	3.88
200	14.75	19.02	36.52	26.64	1.12	0.61	31.02	13.21	3.70
400	14.60	18.96	31.89	24.98	1.13	0.61	30.01	13.08	3.77
600	14.44	18.94	28.57	23.44	1.13	0.60	29.27	13.07	3.75
800	14.25	18.90	27.02	22.31	1.14	0.59	28.85	12.47	3.89
1000	14.08	18.90	25.10	21.40	1.15	0.58	28.56	11.94	3.85
1200	13.90	18.91	23.51	20.52	1.16	0.57	27.90	12.20	3.93
1400	13.74	18.91	22.31	19.83	1.17	0.56	27.51	12.42	3.97
1600	13.54	18.93	21.03	19.20	1.19	0.55	27.13	11.69	4.01
1800	13.37	18.94	20.07	18.75	1.20	0.54	26.86	11.54	4.02
2000	13.20	18.97	19.31	18.47	1.22	0.53	26.16	12.05	3.94
2200	13.01	18.97	18.51	18.24	1.23	0.52	25.80	12.24	4.05
2400	12.80	19.01	17.86	18.11	1.25	0.50	25.50	11.57	4.07
2600	12.61	19.06	17.39	18.03	1.27	0.49	25.20	10.98	4.07
2800	12.40	19.09	16.50	17.81	1.29	0.48	24.77	11.24	4.08
3000	12.18	19.15	16.37	17.86	1.31	0.47	24.51	11.57	3.91
3200	11.95	19.24	15.59	17.63	1.34	0.45	24.21	11.04	3.98
3400	11.76	19.22	15.11	17.50	1.36	0.45	23.90	10.27	4.14
3600	11.51	19.34	14.79	17.19	1.39	0.43	23.43	10.60	4.24
3800	11.30	19.42	14.28	17.01	1.42	0.42	23.41	11.22	4.27
4000	11.11	19.45	13.60	16.51	1.44	0.41	22.99	10.77	4.23
4200	10.87	19.51	13.11	16.25	1.47	0.40	22.81	9.97	4.27
4400	10.66	19.60	12.60	15.97	1.50	0.39	22.74	10.27	4.37
4600	10.38	19.69	12.14	15.36	1.54	0.38	22.42	10.97	4.61
4800	10.23	19.76	11.69	15.35	1.56	0.38	22.05	10.52	4.64
5000	10.01	19.85	11.18	15.17	1.60	0.37	21.73	9.50	4.81
5200	9.74	19.87	10.94	14.87	1.63	0.36	21.62	9.24	4.70
5400	9.55	19.96	10.53	14.86	1.66	0.35	21.18	10.14	4.80
5600	9.32	19.98	9.88	14.62	1.68	0.35	20.80	9.98	4.90
5800	9.14	20.22	10.07	14.96	1.75	0.33	20.84	9.38	4.99
6000	8.98	20.40	9.73	15.30	1.80	0.32	20.73	8.54	4.87
6200	8.75	20.34	9.54	15.48	1.82	0.31	20.33	9.27	4.96
6400	8.49	20.28	9.35	15.46	1.84	0.30	20.13	9.68	5.27
6600	8.49	20.71	9.31	16.52	1.93	0.29	20.10	9.19	5.43
6800	8.37	20.70	9.13	17.11	1.94	0.28	19.69	8.23	5.49
7000	8.23	20.76	8.90	17.77	1.96	0.27	19.70	8.77	5.50
7200	8.06	20.76	8.87	18.12	2.00	0.27	19.43	9.06	5.52
7600	7.82	20.88	8.53	18.85	2.05	0.26	18.98	7.68	5.95
8000	7.70	21.23	8.15	19.62	2.13	0.25	18.27	8.28	6.07

REV. X1
ERA-21SM+
090319
Page 9 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


GAIN vs. TEMPERATURE




GAIN vs. CURRENT




ISOLATION vs. TEMPERATURE




ISOLATION vs. CURRENT




INPUT RETURN LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. CURRENT



OUTPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. CURRENT



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Typical Performance Curves


OUTPUT IP3 vs. TEMPERATURE

INPUT POWER = -20dBm, CURRENT = 40mA




OUTPUT IP3 vs. CURRENT

INPUT POWER = -20dBm, Temperature = +25°C




OUTPUT POWER at 1dB Compression vs. TEMPERATURE

CURRENT = 40mA




OUTPUT POWER at 1dB Compression vs. CURRENT

Temperature = +25°C



Noise Figure vs. TEMPERATURE

CURRENT = 40mA



Noise Figure vs. CURRENT

Temperature = +25°C

