

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
100	0.06	43.1	42.6
200	0.08	39.6	39.2
300	0.10	41.6	41.1
400	0.12	53.0	54.2
500	0.14	43.3	41.3
600	0.15	40.6	39.0
700	0.16	43.6	43.1
800	0.17	50.3	52.4
900	0.18	45.0	42.3
1000	0.19	44.5	41.2
1100	0.20	50.6	47.5
1250	0.21	48.8	44.0
1500	0.23	50.9	49.9
1750	0.26	50.3	39.4
2000	0.27	52.5	45.4
2001	0.27	52.5	45.3
2250	0.28	40.2	38.3
2500	0.30	41.7	36.5
2750	0.31	41.2	39.6
3000	0.32	34.8	32.3
3250	0.34	39.7	37.3
3500	0.38	37.1	34.4
3750	0.37	32.4	30.1
4000	0.36	39.5	44.5
4250	0.40	34.7	30.9
4500	0.42	30.7	29.1
5000	0.42	31.5	28.5
5500	0.42	41.5	39.9
6000	0.47	28.3	28.6
6500	0.53	28.6	28.2
7000	0.48	40.4	32.5
7500	0.51	29.0	28.2
8000	0.52	29.2	29.7
8500	0.53	33.4	31.6
9000	0.56	25.6	25.3
9500	0.55	28.8	32.4
10000	0.58	30.9	31.6
10500	0.58	26.2	26.5
11000	0.63	28.3	29.7
11500	0.68	30.5	31.1
12000	0.52	29.7	29.3
12500	0.65	33.5	31.6
13000	0.70	25.6	26.5
13500	0.66	29.3	25.2
14000	0.77	30.8	24.6
14500	0.81	23.1	22.8
15000	0.70	27.6	25.2
15500	0.70	26.6	21.8
16000	0.78	21.7	19.9
16500	0.83	23.1	22.3
17000	0.83	28.7	24.2
17500	0.84	27.4	21.5
18000	0.76	21.5	20.1