

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.03	49.9	53.4
200	0.04	44.6	45.3
300	0.05	41.8	41.3
400	0.06	39.1	39.5
500	0.07	38.8	40.0
600	0.08	40.5	40.7
700	0.08	43.1	41.1
800	0.09	50.6	43.2
900	0.10	45.1	50.2
1000	0.11	38.6	44.9
1100	0.10	35.8	38.1
1250	0.12	35.3	34.7
1500	0.13	42.2	43.5
1750	0.14	37.2	37.0
2000	0.14	40.0	40.1
2001	0.15	39.8	40.0
2250	0.15	41.6	44.2
2500	0.16	41.8	42.3
2750	0.17	37.4	43.4
3000	0.18	34.5	37.2
3250	0.19	42.4	52.6
3500	0.20	30.3	32.6
3750	0.22	37.8	36.1
4000	0.21	32.4	34.2
4250	0.23	30.7	30.5
4500	0.24	40.2	44.5
5000	0.25	35.3	36.0
5500	0.26	31.6	32.8
6000	0.29	33.1	34.8
6500	0.29	38.9	41.4
7000	0.30	29.6	29.3
7500	0.33	24.6	24.8
8000	0.33	26.7	27.3
8500	0.33	38.0	34.4
9000	0.33	34.7	29.3
9500	0.35	31.6	28.4
10000	0.36	40.9	37.1
10500	0.36	27.0	28.9
11000	0.37	27.7	25.7
11500	0.38	29.6	27.0
12000	0.40	49.2	52.2
12500	0.43	24.1	25.6
13000	0.37	22.7	21.8
13500	0.46	22.5	24.3
14000	0.44	23.7	31.3
14500	0.42	30.1	46.5
15000	0.44	33.8	26.8
15500	0.44	29.5	29.8
16000	0.44	38.8	32.9
16500	0.44	37.3	32.8
17000	0.44	34.0	32.3
17500	0.51	28.0	27.0
18000	0.57	22.6	23.0