

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.06	29.9	29.7
200	0.08	35.8	35.4
300	0.11	30.8	30.9
400	0.13	32.4	33.3
500	0.15	33.8	33.8
600	0.17	29.9	30.7
700	0.18	41.5	39.2
800	0.20	28.7	29.4
900	0.21	42.2	52.8
1000	0.23	28.7	28.8
1100	0.24	32.2	34.5
1250	0.25	43.6	52.0
1500	0.29	27.5	27.4
1750	0.31	38.5	37.3
2000	0.34	29.2	29.1
2001	0.34	29.1	29.0
2250	0.36	34.8	34.2
2500	0.38	33.3	35.0
2750	0.40	34.3	32.3
3000	0.41	31.5	31.1
3250	0.44	36.1	33.3
3500	0.46	38.5	39.5
3750	0.49	39.2	37.9
4000	0.49	38.5	36.1
4250	0.51	48.2	52.5
4500	0.54	34.5	33.4
5000	0.57	35.6	34.1
5500	0.60	35.8	35.5
6000	0.66	33.1	32.3
6500	0.67	35.0	33.2
7000	0.70	31.8	30.6
7500	0.74	30.5	28.1
8000	0.77	26.6	25.6
8500	0.79	26.6	25.4
9000	0.81	28.5	26.2
9500	0.84	29.6	29.1
10000	0.87	34.1	29.8
10500	0.88	30.7	37.5
11000	0.91	24.8	27.0
11500	0.95	26.1	28.3
12000	0.98	25.8	26.4
12500	1.00	39.3	36.5
13000	0.96	27.5	25.3
13500	1.05	42.6	32.4
14000	1.05	31.0	36.6
14500	1.06	39.6	43.2
15000	1.05	28.3	31.7
15500	1.11	28.8	38.7
16000	1.13	36.6	37.7
16500	1.14	30.2	31.3
17000	1.16	29.2	30.0
17500	1.23	28.8	27.5
18000	1.29	25.9	26.2