

# Frequency Synthesizer

# KSN-2346A+

## Typical Performance Data

FREQ. (MHz)	POWER OUTPUT (dBm)			HARMONICS (dBc)						VCO CURRENT (mA)			PLL CURENT (mA)		
				F2			F3								
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
2286	-0.15	-0.13	-0.15	-33.48	-31.72	-31.73	-45.15	-48.70	-48.58	23.07	24.25	25.03	9.95	12.41	14.51
2295	-0.20	-0.23	-0.19	-34.25	-31.16	-31.52	-46.84	-48.67	-49.75	23.05	24.23	25.01	9.91	12.36	14.46
2310	-0.21	-0.17	-0.22	-31.85	-30.05	-29.50	-49.01	-52.38	-52.30	23.03	24.22	24.99	9.92	12.37	14.46
2325	-0.22	-0.18	-0.29	-29.78	-28.86	-29.48	-54.42	-53.66	-52.29	22.98	24.19	24.95	9.92	12.38	14.48
2340	-0.30	-0.27	-0.34	-26.90	-26.61	-27.98	-55.95	-56.06	-52.78	22.90	24.12	24.89	9.93	12.39	14.49
2346	-0.31	-0.29	-0.36	-26.09	-25.72	-27.63	-58.88	-57.31	-53.86	22.88	24.10	24.85	9.99	12.44	14.55

FREQ. (MHz)	PHASE NOISE (dBc/Hz) @ OFFSETS														
	-45°C					+25°C					+85°C				
	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz
2286	-83.57	-84.00	-88.50	-124.23	-146.82	-84.86	-87.03	-89.47	-122.84	-144.68	-82.95	-88.05	-88.16	-121.17	-142.81
2295	-84.94	-86.57	-89.33	-123.73	-146.44	-86.32	-87.87	-88.79	-122.63	-144.35	-81.91	-85.95	-87.68	-120.91	-142.72
2310	-81.73	-86.14	-88.41	-123.26	-146.28	-85.86	-86.30	-89.14	-122.68	-144.49	-81.37	-85.13	-87.07	-120.76	-142.80
2325	-82.31	-86.59	-88.51	-123.14	-145.80	-85.16	-85.90	-87.49	-122.08	-144.19	-85.12	-84.89	-86.39	-120.39	-142.07
2340	-84.14	-86.28	-88.06	-122.40	-145.12	-83.48	-86.43	-86.47	-121.51	-143.89	-81.99	-86.33	-86.65	-120.18	-142.08
2346	-83.06	-85.24	-86.87	-122.34	-145.13	-85.59	-85.28	-87.00	-121.55	-143.72	-83.98	-86.34	-86.72	-119.99	-141.32

## Typical Performance Data

COMPARISON SPURIOUS ORDER  n	COMPARISON SPURIOUS @Fcarrier 2286MHz± (n*Fcomparison) (dBc) NOTE 1			COMPARISON SPURIOUS @Fcarrier 2316MHz± (n*Fcomparison) (dBc) NOTE 1			COMPARISON SPURIOUS @Fcarrier 2346MHz± (n*Fcomparison) (dBc) NOTE 1		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5	-123.87	-110.95	-102.84	-103.40	-114.80	-114.22	-101.62	-109.45	-103.02
-4	-107.19	-103.79	-102.93	-108.95	-115.60	-103.42	-104.85	-111.60	-102.05
-3	-104.94	-101.32	-100.61	-106.71	-118.82	-102.27	-103.17	-107.74	-101.18
-2	-96.60	-98.32	-95.78	-107.04	-111.53	-96.02	-106.72	-108.16	-94.86
-1	-90.49	-92.26	-91.26	-100.77	-104.97	-89.76	-99.00	-102.58	-89.41
0 <sup>note 2</sup>	-	-	-	-	-	-	-	-	-
+1	-88.83	-92.62	-90.66	-96.43	-99.88	-89.54	-94.43	-98.82	-88.76
+2	-95.34	-97.79	-95.01	-100.90	-104.68	-94.78	-104.13	-109.22	-93.51
+3	-99.87	-101.07	-100.85	-102.12	-116.50	-100.96	-107.67	-107.94	-99.74
+4	-105.26	-104.65	-104.33	-106.85	-117.19	-102.66	-107.22	-112.01	-100.31
+5	-107.88	-105.48	-103.18	-104.68	-106.32	-108.57	-101.22	-113.46	-104.21

Note 1: Comparison frequency 1000 kHz

Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER  n	REFERENCE SPURIOUS @Fcarrier 2286MHz± (n*Reference) (dBc) NOTE 3			REFERENCE SPURIOUS @Fcarrier 2316MHz± (n*Reference) (dBc) NOTE 3			REFERENCE SPURIOUS @Fcarrier 2346MHz± (n*Reference) (dBc) NOTE 3		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5	-115.10	-126.60	-116.04	-117.31	-114.85	-119.26	-116.91	-117.03	-119.52
-4	-116.83	-123.42	-117.54	-120.37	-118.83	-116.87	-120.32	-116.24	-124.91
-3	-115.57	-122.81	-115.09	-119.28	-117.07	-115.10	-115.94	-114.59	-117.35
-2	-111.77	-113.45	-113.50	-112.72	-112.98	-118.55	-110.09	-113.67	-118.43
-1	-109.04	-108.01	-113.27	-109.38	-117.43	-117.04	-98.95	-106.22	-112.71
0 <sup>note 4</sup>	-	-	-	-	-	-	-	-	-
+1	-106.52	-106.39	-114.45	-112.11	-120.00	-122.20	-106.69	-112.16	-116.50
+2	-110.48	-111.83	-117.44	-112.53	-119.86	-116.72	-109.84	-112.19	-117.96
+3	-116.78	-117.87	-116.02	-116.56	-116.24	-117.86	-113.59	-113.02	-113.79
+4	-117.88	-123.24	-121.64	-122.15	-123.29	-116.84	-118.74	-116.43	-118.53
+5	-117.56	-123.72	-118.34	-116.34	-117.79	-117.49	-115.40	-114.86	-117.56

Note 3: Reference frequency 15 MHz

Note 4: All spurs are referenced to carrier signal (n=0).