

Coaxial Bandpass Filter

ZABP-184-S+

50Ω 154.32 to 214.32 MHz



Generic photo used for illustration purposes only
CASE STYLE: UU1842

The Big Deal

- Broad bandwidth
- High Rejection
- Good VSWR
- Connectorized package

Product Overview

ZABP-184-S+ is a 50Ω bandpass filter with a rugged connectorized package covering the passband of 154.32 to 214.32 MHz. The bandpass filter offers good matching within the passband and provides high rejection. This filter has miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages
High rejection	ZABP-184-S+ has sharper transition and rejects spurious signals in the stopband.
Good VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

50Ω 154.32 to 214.32 MHz

ZABP-184-S+



Generic photo used for illustration purposes only

CASE STYLE: UU1842

Connectors	Model
SMA-MF	ZABP-184-S+

Features

- Broad bandwidth
- High rejection
- Good VSWR
- Connectorized package

Applications

- Digital television
- Biomedical telemetry device
- Wireless microphone
- Test equipment

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	184	-	MHz
	Insertion Loss	F1-F2	154.32 - 214.32	1.9	3.0	dB
	VSWR	F1-F2	154.32 - 214.32	1.4	1.9	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 139	20	30	dB
	VSWR	DC-F3	DC - 139	-	20	:1
Stop Band, Upper	Insertion Loss	F4-F5	242 - 750	20	27	dB
		F5-F6	750 - 1400	60	79	dB
		F6-F7	1400 - 2500	50	60	dB
		F7-F8	2500 - 3500	-	20	dB
	VSWR	F4-F8	242 - 3500	-	20	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	2 W max.

Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1.00	77.69	4919.23	154.32	29.65
50.00	44.89	654.25	155.00	27.68
139.00	33.31	31.85	160.00	21.55
140.00	28.58	27.95	162.00	19.85
142.00	20.74	19.78	164.00	18.49
149.00	3.05	1.69	166.00	17.39
151.00	2.10	1.07	168.00	16.54
154.32	1.66	1.18	170.00	15.89
184.00	1.21	1.07	175.00	14.85
214.32	1.84	1.36	180.00	14.29
218.00	2.02	1.20	182.00	14.12
223.00	3.04	1.68	184.00	13.99
236.00	20.19	26.47	185.00	13.93
242.00	30.89	45.12	190.00	13.80
750.00	93.71	144.40	192.00	13.83
1400.00	84.23	130.59	195.00	13.99
2500.00	61.97	42.16	200.00	14.57
2800.00	57.36	38.76	205.00	15.54
3000.00	53.32	36.50	210.00	16.92
3500.00	45.78	26.26	214.32	19.09

Functional Schematic







Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Coaxial Connections

PORT - 1	SMA-MALE
PORT - 2	SMA-FEMALE

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E
2.300	2.250	.750	2.175	2.125
58.42	57.15	19.05	55.25	53.98
F	G	H	J	wt.
.125	.125	.312	1.125	grams
3.18	3.18	7.93	28.58	124

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1.00	77.37	76.49	77.03	0.00	0.01	0.00	0.32	0.41	0.47
10.00	58.22	58.19	58.21	0.01	0.02	0.02	0.45	0.54	0.61
50.00	44.50	44.60	44.63	0.03	0.04	0.04	0.77	0.87	0.95
100.00	41.50	41.59	41.66	0.09	0.11	0.11	0.74	0.84	0.90
130.00	39.30	39.10	38.87	0.26	0.31	0.33	0.60	0.70	0.77
139.00	32.61	31.73	31.13	0.54	0.64	0.71	0.84	0.98	1.07
140.00	27.78	27.06	26.56	0.61	0.73	0.82	0.92	1.08	1.18
142.00	19.90	19.34	18.93	0.87	1.06	1.19	1.22	1.42	1.56
145.00	10.24	9.90	9.64	2.11	2.55	2.90	2.61	3.00	3.29
148.00	3.88	3.93	3.96	7.36	8.40	9.24	8.06	8.71	9.12
149.00	2.86	3.01	3.10	10.81	12.04	13.01	11.41	11.85	12.03
150.00	2.26	2.46	2.59	15.17	16.38	17.16	15.13	14.95	14.65
151.00	1.92	2.14	2.28	19.99	20.23	19.94	18.19	17.18	16.42
154.32	1.48	1.68	1.82	21.25	19.66	18.53	21.83	20.96	20.21
160.00	1.25	1.42	1.53	18.42	18.01	17.66	26.10	26.64	27.21
170.00	1.14	1.28	1.37	17.61	18.19	18.66	16.53	16.78	17.05
184.00	1.07	1.23	1.33	24.91	23.63	22.59	26.74	28.20	29.98
190.00	1.14	1.31	1.41	18.69	18.21	18.00	20.38	20.39	20.75
200.00	1.23	1.41	1.53	18.73	18.14	18.05	18.00	17.38	17.26
210.00	1.41	1.63	1.78	17.96	17.40	17.04	20.75	20.33	20.00
214.32	1.57	1.81	1.97	16.86	16.69	16.65	21.30	21.99	22.27
218.00	1.72	1.98	2.17	20.06	20.25	20.82	25.75	27.72	28.33
220.00	1.85	2.15	2.37	26.63	25.34	24.79	28.87	27.40	24.97
223.00	2.41	2.82	3.15	14.19	13.23	12.33	15.33	14.81	14.09
225.00	3.36	3.89	4.34	8.30	7.82	7.32	10.07	10.00	9.72
230.00	8.85	9.60	10.25	2.12	2.10	2.03	4.20	4.57	4.77
236.00	18.26	19.06	19.74	0.66	0.71	0.72	2.70	3.09	3.35
237.00	19.91	20.70	21.39	0.58	0.63	0.64	2.60	2.99	3.24
242.00	28.55	29.42	30.19	0.37	0.41	0.42	2.31	2.65	2.87
243.00	30.44	31.34	32.14	0.35	0.38	0.40	2.26	2.59	2.82
250.00	50.24	51.46	52.33	0.25	0.28	0.29	2.06	2.34	2.52
260.00	43.45	43.71	43.82	0.19	0.22	0.22	1.88	2.11	2.26
275.00	44.94	45.40	45.73	0.16	0.18	0.18	1.74	1.94	2.05
300.00	56.61	57.04	57.36	0.14	0.15	0.15	1.75	1.98	2.12
325.00	66.42	66.38	66.77	0.13	0.15	0.14	2.35	2.82	3.13
350.00	60.18	60.72	61.39	0.13	0.15	0.14	6.49	8.44	10.28
400.00	65.32	65.66	66.32	0.13	0.15	0.15	2.17	2.35	2.41
500.00	75.15	75.17	75.29	0.13	0.16	0.16	0.77	0.90	0.98
750.00	91.72	101.07	98.36	0.14	0.18	0.19	0.37	0.48	0.53
1000.00	84.78	83.04	85.64	0.11	0.16	0.17	0.27	0.38	0.42
1400.00	83.89	83.05	87.32	0.08	0.15	0.17	0.28	0.38	0.43
1500.00	76.73	76.00	76.08	0.08	0.15	0.18	0.28	0.39	0.43
1750.00	71.67	70.74	71.68	0.10	0.18	0.21	0.29	0.40	0.47
2000.00	67.29	67.20	66.98	0.15	0.23	0.27	0.28	0.41	0.48
2100.00	65.89	65.59	65.92	0.17	0.25	0.30	0.27	0.40	0.48
2200.00	64.62	64.34	64.63	0.19	0.29	0.33	0.27	0.40	0.48
2250.00	63.82	63.63	63.89	0.20	0.30	0.34	0.26	0.40	0.48
2300.00	63.12	62.84	63.18	0.22	0.31	0.36	0.26	0.40	0.48
2500.00	61.01	60.78	61.04	0.27	0.37	0.42	0.25	0.39	0.47
2600.00	60.00	59.60	59.73	0.31	0.42	0.47	0.25	0.39	0.46
2750.00	57.62	57.49	57.38	0.38	0.48	0.53	0.25	0.39	0.46
2800.00	57.15	56.77	56.58	0.34	0.45	0.52	0.25	0.39	0.46
3000.00	53.78	53.28	52.77	0.35	0.50	0.59	0.25	0.41	0.48
3200.00	48.59	47.70	46.61	0.42	0.67	0.87	0.28	0.45	0.53
3300.00	44.09	42.61	40.76	0.64	1.21	1.98	0.30	0.47	0.56
3400.00	35.59	34.68	35.42	3.52	10.89	8.44	0.31	0.49	0.60
3500.00	37.82	40.23	41.34	2.30	1.75	1.55	0.32	0.52	0.65
3750.00	43.89	43.43	44.48	0.35	0.52	0.62	0.69	0.99	1.15
3900.00	40.72	37.56	39.97	0.40	0.66	0.79	0.90	1.22	1.28
4000.00	34.05	32.43	30.48	0.76	1.14	1.57	1.45	1.68	1.83

Typical Performance Data


FREQ. (MHz)	GROUP DELAY		
	(ns)		
	@-40°C	@+25°C	@+85°C
154.32	29.16	28.54	28.09
155.00	27.24	26.74	26.37
156.00	25.70	25.28	24.97
157.00	24.43	24.07	23.81
158.00	23.25	22.95	22.73
159.00	22.12	21.87	21.68
160.00	21.10	20.89	20.74
161.00	20.21	20.03	19.91
162.00	19.43	19.28	19.19
163.00	18.73	18.61	18.53
164.00	18.11	18.02	17.95
165.00	17.56	17.49	17.44
166.00	17.08	17.02	16.99
167.00	16.66	16.62	16.59
168.00	16.29	16.26	16.24
169.00	15.96	15.94	15.93
170.00	15.68	15.66	15.66
171.00	15.42	15.42	15.42
172.00	15.21	15.20	15.21
173.00	15.01	15.01	15.01
174.00	14.84	14.85	14.85
175.00	14.69	14.69	14.69
176.00	14.55	14.56	14.56
177.00	14.43	14.43	14.43
178.00	14.32	14.31	14.32
179.00	14.21	14.21	14.21
180.00	14.11	14.11	14.11
181.00	14.02	14.01	14.01
182.00	13.93	13.93	13.93
183.00	13.85	13.85	13.85
184.00	13.77	13.78	13.78
185.00	13.70	13.72	13.72
186.00	13.64	13.66	13.66
187.00	13.60	13.61	13.63
188.00	13.56	13.58	13.60
189.00	13.53	13.54	13.57
190.00	13.51	13.53	13.57
191.00	13.52	13.54	13.58
192.00	13.52	13.55	13.60
193.00	13.56	13.59	13.64
194.00	13.60	13.64	13.69
195.00	13.66	13.71	13.77
196.00	13.74	13.80	13.86
197.00	13.84	13.90	13.96
198.00	13.95	14.01	14.09
199.00	14.09	14.15	14.22
200.00	14.23	14.30	14.37
201.00	14.39	14.46	14.55
202.00	14.57	14.64	14.72
203.00	14.76	14.84	14.92
204.00	14.96	15.05	15.13
205.00	15.18	15.26	15.36
206.00	15.41	15.50	15.59
207.00	15.65	15.74	15.85
208.00	15.91	16.01	16.12
209.00	16.19	16.31	16.43
210.00	16.50	16.62	16.75
211.00	16.83	16.97	17.12
212.00	17.18	17.35	17.50
214.32	18.41	18.64	18.87

Typical Performance Curves



Outline Dimensions

UU1842



CASE#	A	B	C	D	E	F	G	H	J	WT.GRAMS
UU1842	2.300 (58.42)	2.250 (57.15)	0.750 (19.05)	2.175 (55.25)	2.125 (53.98)	0.125 (3.18)	0.125 (3.18)	0.312 (7.93)	1.125 (28.58)	124

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I