

Coaxial Bias-Tee

75Ω Wideband 10 to 3000 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	30 dBm max.
Voltage at DC port	30 V max.
Input Current	200 mA
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

RF	2 (N-female)
RF & DC	1 (N-male)
DC	(feed-through pin)
GROUND	GROUND


Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H
1.25	1.25	.95	.63	.47	1.00	.125	1.000
31.75	31.75	24.13	16.00	11.94	25.40	3.18	25.40
J	K	L	M	N	P	wt	
.13	.13	.50	.40	.80	.56	grams	
3.18	3.18	12.70	10.16	20.32	14.22	117.0	

Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 10 to 3000 MHz
- low insertion loss, 0.15 dB typ.
- feed through terminal per DC port
- excellent VSWR, 1.13:1 typ.

Applications

- biasing amplifiers
- biasing of laser diodes
- biasing of active antennas
- test accessory

ZFBT-33-75-FT+



Generic photo used for illustration purposes only

CASE STYLE: K1486

Connectors Model

N-Type ZFBT-33-75-FT+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		3000	MHz
Insertion Loss ¹	10-100	—	0.15	0.5	dB
	100-1500	—	0.15	0.6	
	1500-3000	—	0.2	0.8	
VSWR ¹	10-100	—	1.25	1.5	:1
	100-1500	—	1.13	1.35	
	1500-3000	—	1.13	1.35	
DC Resistance, DC to RF and DC port	10 - 3000	—	1.0	—	ohms

1. Specifications and typical performance are relevant to input RF power up to +20dBm and DC Current up to 200mA.


Typical Performance Data

Frequency (MHz)	INSERTION LOSS (dB)	VSWR (:1)	
		RF	RF&DC
10.00	0.12	1.26	1.26
50.00	0.03	1.04	1.04
100.00	0.03	1.01	1.01
400.00	0.10	1.04	1.04
500.00	0.10	1.06	1.06
800.00	0.12	1.09	1.11
1000.00	0.20	1.13	1.14
1400.00	0.24	1.20	1.17
1500.00	0.23	1.20	1.18
1800.00	0.17	1.16	1.21
2000.00	0.12	1.19	1.21
2400.00	0.22	1.20	1.17
2500.00	0.28	1.17	1.17
2800.00	0.37	1.11	1.16
3000.00	0.34	1.14	1.15

ZFBT-33-75-FT+
INSERTION LOSS





ZFBT-33-75-FT+
VSWR



Typical Performance Data


FREQ	INSERTION LOSS	VSWR	
		RF	RF & DC
(MHz)	(dB)	(:1)	
10.0	0.12	1.26	1.26
50.0	0.03	1.04	1.04
100.0	0.03	1.01	1.01
150.0	0.04	1.01	1.01
200.0	0.06	1.03	1.02
300.0	0.14	1.02	1.02
400.0	0.10	1.04	1.04
500.0	0.10	1.06	1.06
600.0	0.10	1.08	1.07
700.0	0.10	1.08	1.09
800.0	0.12	1.09	1.11
900.0	0.16	1.11	1.12
1000.0	0.20	1.13	1.14
1100.0	0.23	1.16	1.14
1200.0	0.26	1.18	1.15
1300.0	0.26	1.19	1.16
1400.0	0.24	1.20	1.17
1500.0	0.23	1.20	1.18
1600.0	0.20	1.18	1.19
1650.0	0.19	1.17	1.19
1700.0	0.16	1.16	1.20
1750.0	0.15	1.16	1.20
1800.0	0.17	1.16	1.21
1850.0	0.14	1.17	1.20
1900.0	0.15	1.17	1.21
1950.0	0.15	1.17	1.20
2000.0	0.12	1.19	1.21
2050.0	0.12	1.19	1.19
2100.0	0.12	1.21	1.20
2150.0	0.10	1.21	1.19
2200.0	0.09	1.23	1.20
2250.0	0.13	1.22	1.18
2300.0	0.12	1.22	1.19
2350.0	0.17	1.20	1.17
2400.0	0.22	1.20	1.17
2450.0	0.25	1.17	1.16
2500.0	0.28	1.17	1.17
2550.0	0.37	1.15	1.16
2600.0	0.30	1.15	1.17
2650.0	0.43	1.12	1.15
2700.0	0.37	1.12	1.16
2750.0	0.38	1.11	1.15
2800.0	0.37	1.11	1.16
2850.0	0.36	1.11	1.14
2900.0	0.34	1.12	1.15
2950.0	0.33	1.13	1.14
3000.0	0.34	1.14	1.15

Typical Performance Curves



K1486

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
K1486	1.25 (31.75)	1.25 (31.75)	.95 (24.13)	.63 (16.00)	.47 (11.94)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	.13 (3.18)	.13 (3.18)	.50 (12.70)	.40 (10.16)	.80 (20.32)

CASE#	P	Q	WT. GRAMS
K1486	.56 (14.22)	--	117.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I