

High IP3

# Low Noise Amplifier

ZRL-400+

50Ω

150 to 400 MHz

## Features

- High IP3, +42 dBm typ.
- Low Noise figure, 2.5 dB typ.
- Broadband flat gain response
- Internal voltage regulated
- Over-voltage and transient protected

## Applications

- High dynamic range VHF/UHF
- Mobile radio
- VHF/UHF television or radio
- defense communications



Generic photo used for illustration purposes only

Case Style: FJ893

| Connectors | Model    |
|------------|----------|
| SMA        | ZRL-400+ |

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Electrical Specifications at 25°C

| Parameter                                       | Condition (MHz)        | Min.         | Typ.         | Max.         | Units |
|-------------------------------------------------|------------------------|--------------|--------------|--------------|-------|
| Frequency Range                                 |                        | 150          |              | 400          | MHz   |
| Noise Figure                                    | 150 - 400<br>175 - 300 | —<br>—       | 2.5<br>2.5   | 3.5<br>3.5   | dB    |
| Gain                                            | 150 - 400<br>175 - 300 | 27<br>28     | 31<br>31     | —<br>—       | dB    |
| Gain Flatness                                   | 150 - 400<br>175 - 300 | —<br>—       | ±0.5<br>±0.3 | ±1.0<br>±0.5 | dB    |
| Output Power at 1dB compression                 | 150 - 400<br>175 - 300 | 23.5<br>23.5 | 25<br>25     | —<br>—       | dBm   |
| Output third order intercept point <sup>1</sup> | 150 - 400<br>175 - 300 | —<br>—       | +42<br>+42   | —<br>—       | dBm   |
| Input VSWR                                      | 150 - 400<br>175 - 300 | —<br>—       | 1.5<br>1.5   | —<br>—       | :1    |
| Output VSWR                                     | 150 - 400<br>175 - 300 | —<br>—       | 1.25<br>1.15 | —<br>—       | :1    |
| DC Supply Voltage <sup>2</sup>                  |                        | —            | 12           | —            | V     |
| Supply Current                                  |                        | —            | 450          | 575          | mA    |

1. 1 MHz tone spacing.

2. Unit is internally voltage regulated for 6.5 to 17VDC input voltage range.

## Maximum Ratings

| Parameter                  | Ratings                                    |
|----------------------------|--------------------------------------------|
| Operating Temperature      | -40°C to 80°C case<br>-40°C to 60° ambient |
| Storage Temperature        | -55°C to 100°C                             |
| DC Voltage                 | +17V                                       |
| Input RF Power (no damage) | +10 dBm                                    |

Permanent damage may occur if any of these limits are exceeded.

## Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. L  
M151107  
ZRL-400+  
200513  
Page 1 of 3

## Outline Drawing







## Outline Dimensions (inch/mm)

| A     | B     | C     | D     | E    | F     | G     | H     | J     | K    | L     | M     | N    | P    | wt    |
|-------|-------|-------|-------|------|-------|-------|-------|-------|------|-------|-------|------|------|-------|
| 2.00  | 3.75  | 0.80  | 3.00  | 0.19 | 3.374 | 1.624 | 0.156 | 0.44  | 0.26 | 1.00  | 0.51  | 0.22 | 0.10 | grams |
| 50.80 | 95.25 | 20.32 | 76.20 | 4.83 | 85.70 | 41.25 | 3.96  | 11.18 | 6.60 | 25.40 | 12.95 | 5.59 | 2.54 | 135   |

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Low Noise Amplifier

## ZRL-400+

### Typical Performance Data

| FREQUENCY<br>(MHz) | GAIN<br>(dB)<br>12V | DIRECTIVITY<br>(dB)<br>12V | VSWR (:1) |            | NOISE FIGURE<br>(dB)<br>12V | POUT @ 1 dB<br>COMPRESSION<br>(dBm)<br>12V | OUTPUT IP3<br>(dBm)<br>12V |
|--------------------|---------------------|----------------------------|-----------|------------|-----------------------------|--------------------------------------------|----------------------------|
|                    |                     |                            | IN<br>12V | OUT<br>12V |                             |                                            |                            |
| 150.0              | 31.29               | 21.07                      | 1.51      | 1.24       | 2.61                        | 25.47                                      | 44.82                      |
| 160.0              | 31.59               | 19.06                      | 1.40      | 1.22       | 2.54                        | 25.52                                      | 44.97                      |
| 170.0              | 31.82               | 18.38                      | 1.32      | 1.19       | 2.51                        | 25.56                                      | 45.31                      |
| 180.0              | 32.00               | 17.78                      | 1.29      | 1.17       | 2.28                        | 25.55                                      | 45.79                      |
| 190.0              | 32.10               | 17.48                      | 1.28      | 1.16       | 2.16                        | 25.47                                      | 45.77                      |
| 200.0              | 32.18               | 17.27                      | 1.29      | 1.15       | 2.21                        | 25.38                                      | 45.92                      |
| 210.0              | 32.21               | 16.64                      | 1.31      | 1.14       | 2.14                        | 25.30                                      | 45.83                      |
| 220.0              | 32.23               | 17.26                      | 1.32      | 1.13       | 2.16                        | 25.28                                      | 46.04                      |
| 230.0              | 32.22               | 16.35                      | 1.34      | 1.12       | 2.05                        | 25.18                                      | 46.48                      |
| 240.0              | 32.20               | 16.56                      | 1.34      | 1.12       | 2.05                        | 25.18                                      | 46.46                      |
| 250.0              | 32.19               | 16.78                      | 1.35      | 1.13       | 2.03                        | 25.25                                      | 47.16                      |
| 260.0              | 32.16               | 16.57                      | 1.35      | 1.13       | 2.08                        | 25.22                                      | 47.7                       |
| 270.0              | 32.13               | 16.75                      | 1.35      | 1.14       | 2.03                        | 25.05                                      | 48.26                      |
| 280.0              | 32.08               | 16.32                      | 1.35      | 1.16       | 2.03                        | 25.00                                      | 48.88                      |
| 290.0              | 32.04               | 16.21                      | 1.36      | 1.17       | 2.02                        | 25.02                                      | 49.14                      |
| 300.0              | 31.99               | 15.97                      | 1.37      | 1.19       | 2.03                        | 25.00                                      | 49.14                      |
| 310.0              | 31.92               | 16.22                      | 1.39      | 1.20       | 2.00                        | 25.03                                      | 48.77                      |
| 320.0              | 31.86               | 15.43                      | 1.40      | 1.21       | 2.03                        | 25.01                                      | 47.94                      |
| 330.0              | 31.78               | 15.87                      | 1.42      | 1.22       | 2.02                        | 25.06                                      | 47.77                      |
| 340.0              | 31.70               | 15.94                      | 1.44      | 1.23       | 2.08                        | 25.12                                      | 47.12                      |
| 350.0              | 31.60               | 16.29                      | 1.46      | 1.23       | 2.05                        | 25.09                                      | 47.19                      |
| 360.0              | 31.50               | 15.57                      | 1.47      | 1.22       | 2.05                        | 25.10                                      | 46.82                      |
| 370.0              | 31.39               | 15.37                      | 1.48      | 1.21       | 1.99                        | 25.14                                      | 46.06                      |
| 380.0              | 31.29               | 15.71                      | 1.49      | 1.19       | 2.08                        | 25.13                                      | 46.14                      |
| 390.0              | 31.17               | 16.36                      | 1.49      | 1.18       | 1.99                        | 25.14                                      | 45.79                      |
| 400.0              | 31.03               | 16.34                      | 1.50      | 1.16       | 2.03                        | 25.14                                      | 45.09                      |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)









IF/RF MICROWAVE COMPONENTS



REV. X2  
ZRL-400+  
6/25/2010  
Page 1 of 1

## Typical Performance Curves




# Case Style

# FJ

## Outline Dimensions

## FJ893



| CASE# | A               | B               | C              | D               | E             | F                | G                | H              | J              | K             | L               | M              | N             | P             | WT. GRAMS |
|-------|-----------------|-----------------|----------------|-----------------|---------------|------------------|------------------|----------------|----------------|---------------|-----------------|----------------|---------------|---------------|-----------|
| FJ893 | 2.00<br>(50.80) | 3.75<br>(95.25) | .80<br>(20.32) | 3.00<br>(76.20) | .19<br>(4.83) | 3.374<br>(85.70) | 1.624<br>(41.25) | .156<br>(3.96) | .44<br>(11.18) | .26<br>(6.60) | 1.00<br>(25.40) | .51<br>(12.95) | .22<br>(5.59) | .10<br>(2.54) | 135       |

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

### Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification             | Test/Inspection Condition             | Reference/Spec                                     |
|---------------------------|---------------------------------------|----------------------------------------------------|
| Operating Temperature     | -40° to 60° C<br>Ambient Environment  | Individual Model Data Sheet                        |
| Operating Temperature     | -40° to 80° C<br>Case Temperature     | Individual Model Data Sheet                        |
| Storage Temperature       | -55° to 100° C<br>Ambient Environment | Individual Model Data Sheet                        |
| Stabilization Bake        | (non-operating)<br>125°C, 24 hours    | - - -                                              |
| Burn-in at Elevated Temp. | (DC on)<br>160 hours at 85° C         | MIL-STD-202, Method 108                            |
| Thermal Shock             | -55° to 100°C, 5 cycles               | MIL-STD-202, Method 107, Condition A, except 100°C |