

MMIC Reflectionless High Pass Filter Die XHF-73M-D+

Typical Performance Data

Test Condition @ Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
10	67.07	1.19	1.19
100	56.61	1.19	1.19
500	34.60	1.20	1.20
1000	27.29	1.24	1.24
2000	40.13	1.23	1.23
3000	33.32	1.05	1.05
4000	39.21	1.23	1.23
5200	38.00	1.04	1.04
5700	7.66	1.19	1.19
6200	3.00	1.10	1.10
6700	1.84	1.21	1.20
7000	1.52	1.26	1.24
7500	1.20	1.29	1.27
8000	1.02	1.30	1.29
9000	0.80	1.25	1.24
10000	0.68	1.18	1.18
11000	0.65	1.12	1.12
12000	0.59	1.06	1.06
14000	0.50	1.07	1.06
16000	0.48	1.16	1.14
18000	0.50	1.21	1.19
20000	0.44	1.21	1.19
21700	0.45	1.16	1.11



ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
XHF-73M-D+
5/24/2019
Page 1 of 1