

# Fixed Attenuator Die

# YAT-6A-D+

## Typical Performance Data

| FREQUENCY<br>(GHz) | ATTENUATION<br>(dB) | VSWR<br>(:1) |
|--------------------|---------------------|--------------|
| 0.01               | 5.98                | 1.08         |
| 0.02               | 5.98                | 1.08         |
| 0.04               | 5.98                | 1.08         |
| 0.06               | 5.98                | 1.08         |
| 0.08               | 5.98                | 1.08         |
| 0.10               | 5.98                | 1.08         |
| 0.20               | 5.98                | 1.08         |
| 0.40               | 5.98                | 1.08         |
| 0.60               | 5.98                | 1.08         |
| 0.80               | 5.98                | 1.08         |
| 1.00               | 5.98                | 1.08         |
| 1.20               | 5.98                | 1.08         |
| 1.40               | 5.98                | 1.08         |
| 1.60               | 5.98                | 1.08         |
| 1.80               | 5.98                | 1.08         |
| 2.00               | 5.99                | 1.08         |
| 3.00               | 5.98                | 1.08         |
| 4.00               | 5.98                | 1.08         |
| 5.00               | 5.98                | 1.08         |
| 6.00               | 5.98                | 1.07         |
| 7.00               | 5.97                | 1.07         |
| 8.00               | 5.97                | 1.07         |
| 9.00               | 5.97                | 1.07         |
| 10.0               | 5.97                | 1.07         |
| 11.0               | 5.97                | 1.06         |
| 12.0               | 5.99                | 1.05         |
| 13.0               | 6.02                | 1.05         |
| 14.0               | 6.02                | 1.05         |
| 15.0               | 6.00                | 1.05         |
| 16.0               | 6.00                | 1.05         |
| 17.0               | 6.01                | 1.04         |
| 18.0               | 6.03                | 1.03         |
| 19.0               | 6.03                | 1.03         |
| 20.0               | 6.01                | 1.04         |
| 21.0               | 6.00                | 1.04         |
| 22.0               | 5.98                | 1.03         |
| 23.0               | 5.97                | 1.04         |
| 24.0               | 5.95                | 1.04         |
| 25.0               | 5.94                | 1.04         |
| 26.0               | 5.94                | 1.04         |
| 27.0               | 5.97                | 1.05         |
| 28.0               | 6.00                | 1.05         |
| 29.0               | 5.99                | 1.05         |
| 30.0               | 5.98                | 1.05         |