

Typical Performance Data

FREQ.	INSERTION LOSS	INPUT RETURN LOSS (50Ω)	OUTPUT RETURN LOSS (75Ω)
(MHz)	(dB)	(dB)	(dB)
1.00	0.01	13.99	13.92
10.00	0.01	13.99	13.96
50.00	0.04	13.97	14.05
100.00	0.08	14.02	14.19
150.00	0.12	14.11	14.31
200.00	0.16	14.24	14.43
225.00	0.19	14.32	14.49
250.00	0.21	14.40	14.56
275.00	0.24	14.49	14.61
300.00	0.26	14.58	14.66
350.00	0.29	14.78	14.74
375.00	0.31	14.89	14.81
400.00	0.33	15.01	14.90
450.00	0.36	15.25	15.05
500.00	0.37	15.50	15.16
525.00	0.38	15.63	15.24
550.00	0.38	15.76	15.34
600.00	0.39	16.01	15.54
650.00	0.38	16.26	15.65
700.00	0.37	16.50	15.82
725.00	0.36	16.62	15.94
750.00	0.35	16.73	16.06
800.00	0.33	16.95	16.24
825.00	0.32	17.06	16.36
850.00	0.30	17.17	16.54
875.00	0.29	17.28	16.76
900.00	0.28	17.40	16.99
925.00	0.27	17.52	17.21
950.00	0.26	17.65	17.41
975.00	0.25	17.79	17.64
1000.00	0.25	17.93	17.91
1025.00	0.24	18.09	18.21
1050.00	0.24	18.25	18.53
1075.00	0.24	18.43	18.84
1100.00	0.24	18.62	19.14
1150.00	0.24	19.06	19.85
1200.00	0.25	19.55	20.72
1225.00	0.25	19.82	21.17
1250.00	0.26	20.11	21.62
1300.00	0.27	20.75	22.70
1400.00	0.28	22.19	25.11
1500.00	0.30	23.76	27.45
1600.00	0.31	25.08	28.20
1650.00	0.32	25.46	28.37
1700.00	0.33	25.64	28.33
1750.00	0.34	25.62	28.16
1800.00	0.35	25.44	28.06
1850.00	0.36	25.20	27.90
1900.00	0.37	25.00	27.55
1950.00	0.38	24.83	27.18
2000.00	0.39	24.73	26.69
2050.00	0.40	24.72	26.43
2075.00	0.40	24.75	26.45
2100.00	0.40	24.80	26.38
2125.00	0.40	24.87	26.29
2150.00	0.40	24.97	26.29
2200.00	0.41	25.24	26.55
2250.00	0.41	25.53	26.87
2300.00	0.41	25.87	26.74
2500.00	0.42	27.52	27.17