

Typical Performance Data

Frequency (MHz)	Gain @ 12.5dBm Pin, +25°C (dB)	Gain Comp. @ 12.5dBm Pin, +25°C (dB)	Pout @ 12.5dBm Pin (dBm)	Pout @ 12.5dBm Pin, +25°C (W)	Eff. @ 12.5dBm Pin, +25°C (%)	IRL@ 12.5dBm Pin, +25°C (dB)
2400	42.35	2.30	54.81	302.62	60.45	-11.40
2410	42.39	2.12	54.80	301.99	59.94	-11.45
2420	42.40	2.13	54.85	305.69	59.81	-11.49
2430	42.44	2.26	54.94	311.68	60.02	-11.47
2440	42.50	2.25	54.99	315.29	60.34	-11.31
2450	42.49	2.05	54.99	315.19	60.33	-11.26
2460	42.46	2.10	54.96	313.58	59.87	-11.26
2470	42.45	2.24	54.94	311.92	59.22	-11.17
2480	42.44	2.34	54.89	308.01	58.53	-11.15
2490	42.36	2.31	54.81	302.77	58.21	-11.02
2500	42.24	2.30	54.73	297.05	57.98	-10.96

Frequency (MHz)	Gain @ 14dBm Pin, +65°C (dB)	Gain Comp. @ 14dBm Pin, +65°C (dB)	Pout @ 14dBm Pin (dBm)	Pout @ 14dBm Pin, +65°C (W)	Eff. @ 14dBm Pin, +65°C (%)	IRL@ 14dBm Pin, +65°C (dB)
2400	40.61	2.48	54.57	286.71	58.37	-11.07
2410	40.65	2.29	54.55	285.34	57.84	-11.09
2420	40.64	2.31	54.59	287.82	57.69	-11.10
2430	40.67	2.46	54.66	292.40	57.84	-11.10
2440	40.71	2.43	54.70	295.20	58.12	-10.81
2450	40.70	2.28	54.69	294.37	58.10	-10.73
2460	40.65	2.29	54.65	292.07	57.60	-10.71
2470	40.64	2.50	54.63	290.23	57.02	-10.67
2480	40.61	2.66	54.56	285.80	56.44	-10.63
2490	40.54	2.67	54.49	280.89	56.29	-10.56
2500	40.42	2.70	54.41	275.94	56.23	-10.42



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS