

Amplifier

ZHL-5W-2G+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 24V	DIRECTIVITY (dB) 24V	VSWR IN (:1) 24V	VSWR OUT (:1) 24V	NOISE FIGURE (dB) 24V	Pout at 1dB Comp. (dBm) 24V	FREQUENCY (MHz)	Output IP3 (dBm) 24V
800.0	44.83	40.40	1.31	1.18	8.50	36.16	800.0	44.07
900.0	45.92	39.10	1.33	1.29	8.34	36.81	1000.0	44.17
1000.0	46.48	36.70	1.37	1.27	8.31	37.09	1250.0	44.16
1100.0	46.54	33.20	1.39	1.11	8.38	37.14	1500.0	44.76
1150.0	46.36	30.20	1.38	1.11	8.35	36.93	1750.0	45.25
1200.0	45.98	40.40	1.42	1.19	8.37	36.72	2000.0	44.64
1250.0	45.47	51.70	1.41	1.24	8.39	36.51		
1300.0	45.04	36.00	1.44	1.24	8.42	36.30		
1350.0	44.71	38.30	1.43	1.19	8.42	36.06		
1400.0	44.54	47.70	1.43	1.09	8.45	35.79		
1450.0	44.43	45.80	1.46	1.07	8.42	35.73		
1500.0	44.29	40.10	1.47	1.20	8.38	35.72		
1550.0	44.08	47.90	1.44	1.35	8.43	35.85		
1600.0	43.91	30.40	1.44	1.41	8.35	35.95		
1650.0	43.80	47.50	1.41	1.43	8.28	36.19		
1700.0	43.85	39.30	1.39	1.35	8.19	36.63		
1750.0	43.88	40.50	1.35	1.24	8.14	37.02		
1800.0	44.26	33.70	1.30	1.18	8.10	37.59		
1850.0	44.51	39.80	1.24	1.24	8.00	37.99		
1900.0	44.70	38.40	1.16	1.28	7.91	38.31		
1950.0	44.81	33.50	1.09	1.27	7.85	38.22		
2000.0	44.97	37.10	1.04	1.21	7.73	37.49		

REV. X1
ZHL-5W-2G+
070515
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

