


Case Style

LW

Outline Dimensions

LW1611-1



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
LW1611-1	.435 (11.05)	.560 (14.22)	.120 (3.05)	.060 (1.52)	.170 (4.32)	.100 (2.54)	.140 (3.56)	.280 (7.11)	.040 (1.02)	.050 (1.27)	.160 (4.06)	.244 (6.19)

CASE#	N	P	Q	R	S	T	U	V	W	X	Y	WT.GRAM
LW1611-1	.335 (8.51)	.080 (2.03)	.380 (9.65)	.090 (2.29)	.420 (10.67)	.340 (8.64)	.600 (15.24)	.235 (5.97)	.355 (9.02)	.475 (12.07)	.295 (7.49)	1.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± --; 3Pl. ± .03

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5μinch (.08-.13microns) Gold over 120-240μinch (3.05-6.10microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS