

Wideband Amplifier

ZVA-213+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 12V	DIRECTIVITY (dB) 12V	VSWR IN (:1) 12V	VSWR OUT (:1) 12V	NOISE FIGURE (dB) 12V	Pout at 1dB Comp. (dBm) 12V	FREQUENCY (MHz)	Output IP3 (dBm) 12V
800.0	26.32	49.16	1.47	1.64	4.74	23.89	800.0	36.82
900.0	26.40	50.96	1.43	1.58	4.68	23.80	900.0	37.38
1000.0	26.45	49.60	1.40	1.53	4.66	23.67	1000.0	37.33
1100.0	26.49	54.43	1.38	1.50	4.70	23.73	2000.0	36.86
2000.0	26.83	49.44	1.27	1.28	3.91	23.95	3000.0	36.24
3000.0	26.88	54.76	1.24	1.07	3.46	24.39	4000.0	35.58
4000.0	26.87	50.02	1.23	1.21	3.19	24.80	5000.0	35.10
5000.0	26.75	50.10	1.23	1.41	2.89	25.08	6000.0	34.38
6000.0	26.68	47.03	1.26	1.46	2.74	25.04	7000.0	33.78
7000.0	26.64	49.03	1.30	1.35	2.56	25.43	8000.0	33.26
8000.0	26.53	52.49	1.34	1.17	2.49	25.34	9000.0	32.62
9000.0	26.42	59.55	1.36	1.19	2.48	25.23	10000.0	32.09
10000.0	26.23	53.89	1.36	1.39	2.63	25.09	11000.0	31.27
11000.0	26.12	54.33	1.38	1.52	2.87	24.73	12000.0	30.49
12000.0	26.28	38.47	1.37	1.37	3.25	24.14	13000.0	30.47
13000.0	26.27	56.13	1.37	1.02	3.33	23.68	14000.0	30.19
14000.0	26.03	43.11	1.40	1.38	3.14	23.31	15000.0	29.63
15000.0	26.04	44.40	1.34	1.55	3.31	23.24	16000.0	29.01
16000.0	26.21	34.69	1.12	1.36	3.26	23.06	17000.0	28.88
17000.0	25.90	33.52	1.08	1.01	3.41	22.76	18000.0	28.98
18000.0	25.12	37.12	1.16	1.37	3.72	21.65	19000.0	29.87
19000.0	24.47	36.33	1.15	1.47	4.11	20.85	19500.0	27.95
20000.0	24.06	36.02	1.27	1.27	4.06	19.74		
21000.0	22.91	34.26	1.38	1.17	4.35	18.57		



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MIN-CIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS



REV. X1
ZVA-213+
12/22/2008
Page 1 of 1