

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMP-FEMALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
100	0.06	34.2	33.9
200	0.09	28.6	28.4
300	0.12	26.1	26.1
400	0.14	25.6	25.6
500	0.15	26.8	26.8
600	0.16	30.4	30.4
700	0.17	40.8	41.0
800	0.18	36.9	37.2
900	0.20	29.0	29.1
1000	0.22	25.8	25.9
1100	0.24	24.7	24.8
1200	0.26	25.3	25.2
1300	0.25	27.5	27.3
1400	0.25	33.2	32.8
1500	0.25	53.7	52.9
1600	0.27	31.9	31.8
1800	0.33	24.8	24.5
2000	0.34	25.3	24.7
2500	0.34	26.5	26.1
3000	0.37	36.1	35.0
3500	0.36	25.7	24.3
4000	0.42	32.4	30.0
4500	0.46	34.7	33.5
5000	0.48	27.0	25.0
5500	0.53	30.9	28.4
6000	0.53	29.7	28.6
6500	0.56	24.3	23.5
7000	0.57	35.7	32.0
7500	0.61	26.9	26.6
8000	0.63	26.7	27.4
8500	0.63	29.2	27.2
9000	0.63	25.0	25.9
9500	0.70	24.6	26.3
10000	0.68	28.3	24.5
10500	0.64	23.8	27.0
11000	0.73	25.2	26.2
11500	0.74	25.1	21.7
12000	0.69	22.9	30.9
12500	0.86	26.4	24.5
13000	0.66	24.0	21.3
13500	0.81	23.3	33.4
14000	0.81	27.8	27.9
14500	0.58	20.7	19.0
15000	0.94	22.4	28.4
15500	1.14	27.9	25.5
16000	1.02	21.0	20.4
16500	0.88	23.3	23.6
17000	0.95	23.1	28.1
17500	0.90	18.6	19.7
18000	0.76	26.6	20.7