

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.06	37.5	37.7
200.0	0.09	38.6	39.1
400.0	0.14	42.2	41.4
500.0	0.16	39.6	39.0
600.0	0.17	43.8	44.2
700.0	0.19	46.5	51.1
800.0	0.20	43.0	41.3
900.0	0.22	44.2	42.5
1000.0	0.23	43.1	55.2
1100.0	0.24	39.5	42.8
1250.0	0.26	41.5	42.5
1500.0	0.29	42.8	41.5
1750.0	0.31	39.2	43.7
2000.0	0.33	41.5	44.5
2001.0	0.33	41.5	44.7
2250.0	0.35	39.5	39.3
2500.0	0.38	42.3	44.9
2750.0	0.39	41.4	55.7
3000.0	0.41	34.9	35.2
3250.0	0.42	38.3	39.8
3500.0	0.44	39.0	46.0
3750.0	0.47	34.9	35.4
4000.0	0.48	43.6	45.0
4250.0	0.50	48.5	48.3
4500.0	0.50	34.6	35.3
5000.0	0.53	38.1	41.7
5500.0	0.57	46.7	44.7
6000.0	0.60	26.4	26.6
6500.0	0.64	21.9	21.9
7000.0	0.65	31.6	31.8
7500.0	0.66	44.5	53.5
8000.0	0.69	33.1	32.3
8500.0	0.71	46.5	37.8
9000.0	0.73	34.2	41.3
9500.0	0.75	30.0	27.8
10000.0	0.77	43.3	37.1
10500.0	0.79	34.4	32.5
11000.0	0.79	43.2	30.4
11500.0	0.84	37.8	30.8
12000.0	0.83	33.5	30.5
12500.0	0.87	32.7	23.3
13000.0	0.83	24.9	25.2
13500.0	0.92	23.5	24.1
14000.0	0.85	32.5	26.4
14500.0	0.94	22.7	23.4
15000.0	0.98	21.1	22.9
15500.0	1.00	35.6	28.8
16000.0	1.01	21.6	23.7
16500.0	1.05	23.7	26.1
17000.0	1.08	29.0	27.8
17500.0	1.15	22.8	23.6
18000.0	1.16	38.4	36.1