

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.08	37.1	35.6
200.0	0.11	38.9	37.0
300.0	0.14	37.1	44.0
400.0	0.17	39.3	46.0
800.0	0.24	46.7	53.9
900.0	0.26	43.6	44.5
1000.0	0.27	44.7	42.2
1100.0	0.29	35.7	41.1
1250.0	0.31	37.6	40.2
1750.0	0.37	40.6	47.8
2000.0	0.40	41.0	47.0
2001.0	0.40	41.1	47.2
2250.0	0.43	38.2	40.1
2500.0	0.45	32.7	32.1
2750.0	0.48	46.6	39.9
3000.0	0.50	50.8	42.6
3250.0	0.53	39.6	38.6
3500.0	0.55	32.1	32.0
3750.0	0.58	30.4	30.4
4000.0	0.59	29.9	30.0
4250.0	0.61	32.9	31.2
4500.0	0.63	43.1	42.5
5000.0	0.66	30.6	30.8
5500.0	0.70	29.0	28.5
6000.0	0.73	37.4	35.8
6500.0	0.77	29.7	30.4
7000.0	0.80	31.5	31.6
7500.0	0.83	36.8	35.8
8000.0	0.87	29.8	30.0
8500.0	0.89	40.3	36.6
9000.0	0.93	29.1	27.8
9500.0	0.97	26.1	25.0
10000.0	0.98	32.2	27.7
10500.0	1.03	26.5	26.7
11000.0	1.05	27.4	27.0
11500.0	1.08	28.9	27.3
12000.0	1.01	28.5	26.8
12500.0	1.14	24.4	24.2
13000.0	1.14	28.7	26.6
13500.0	1.19	43.4	25.7
14000.0	1.19	24.8	24.1
14500.0	1.25	23.0	23.8
15000.0	1.30	37.5	28.2
15500.0	1.26	36.7	35.4
16000.0	1.33	27.2	27.7
16500.0	1.37	27.0	26.8
17000.0	1.39	23.9	24.4
17500.0	1.40	39.6	37.9
18000.0	1.40	27.4	29.0