

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	BNC-MALE 1 RETURN LOSS (dB)	BNC-MALE 2 RETURN LOSS (dB)
10	0.04	43.3	44.1
20	0.06	41.3	42.0
30	0.07	40.1	40.4
40	0.08	39.3	39.8
50	0.09	39.2	39.2
60	0.10	39.1	39.7
70	0.11	39.3	40.2
80	0.12	39.8	41.0
90	0.13	40.4	42.1
100	0.13	41.3	43.5
150	0.16	44.6	46.6
170	0.18	43.5	44.0
250	0.21	46.1	47.1
320	0.24	39.8	40.5
400	0.27	40.6	42.6
470	0.30	42.2	42.2
550	0.32	35.7	36.9
700	0.37	33.3	34.1
770	0.38	38.3	40.1
850	0.40	33.8	33.8
920	0.42	31.6	32.5
1000	0.44	40.8	40.3
1070	0.45	30.6	31.5
1150	0.47	38.2	38.4
1220	0.49	32.1	32.9
1300	0.50	32.6	33.5
1370	0.52	36.2	35.9
1450	0.53	29.9	31.4
1520	0.55	42.9	36.2
1600	0.56	29.6	30.1
1670	0.57	34.9	34.5
1750	0.59	30.1	30.3
1820	0.60	29.0	29.5
1900	0.61	34.6	33.5
1970	0.62	28.4	30.2
2050	0.64	39.8	35.7
2120	0.65	27.1	31.5
2200	0.66	31.4	34.6
2270	0.68	30.8	29.9
2350	0.68	26.7	28.9
2420	0.70	40.6	32.6
2500	0.71	25.5	29.7
2570	0.72	32.1	33.8
2650	0.73	26.8	29.8
2720	0.74	25.6	30.3
2800	0.75	34.1	29.8
2900	0.77	25.2	33.8
3000	0.78	30.0	28.9

