

Power Detector

ZX47-55LN+

Typical Performance Data

Output Voltage vs. Input Power @+25°C						
POWER IN (dBm)	@10MHz (V)	@1000MHz (V)	@2000MHz (V)	@5000MHz (V)	@6000MHz (V)	@8000MHz (V)
-55	2.01	2.02	1.99	2.04	2.07	2.11
-50	1.92	1.92	1.88	1.93	1.99	2.07
-45	1.81	1.80	1.75	1.81	1.88	2.00
-40	1.70	1.67	1.63	1.68	1.76	1.90
-35	1.58	1.55	1.51	1.55	1.64	1.79
-30	1.46	1.43	1.39	1.43	1.52	1.67
-25	1.33	1.30	1.26	1.30	1.39	1.56
-20	1.21	1.18	1.14	1.18	1.27	1.44
-15	1.09	1.06	1.02	1.06	1.15	1.33
-10	0.96	0.93	0.89	0.93	1.02	1.21
-5	0.83	0.80	0.76	0.81	0.90	1.09
0	0.70	0.67	0.64	0.68	0.77	0.96
5	0.60	0.57	0.54	0.58	0.65	0.83
10	0.53	0.52	0.51	0.52	0.56	0.72
15	0.50	0.50	0.51	0.52	0.56	0.58

Output Voltage Change Vs Freq						
FREQ (MHz)	@ Input Power -45 dBm			@ Input Power 0 dBm		
	-40°C	+25°C	+85°C	-40°C	+25°C	+85°C
10	0.00	0.00	0.00	0.00	0.00	0.00
20	0.12	0.27	0.35	0.17	-0.06	-0.71
50	0.33	0.49	0.57	-0.61	-0.57	-0.96
100	0.15	0.34	0.41	-0.73	-0.80	-1.26
250	0.19	0.37	0.43	-1.24	-1.47	-2.03
500	-0.17	0.01	0.18	-1.98	-2.43	-3.12
900	-1.11	-0.92	-0.75	-3.16	-4.05	-5.06
1500	-2.11	-1.96	-1.76	-4.88	-6.47	-7.73
1900	-3.25	-3.27	-3.17	-7.04	-9.28	-10.83
2200	-4.50	-4.59	-4.59	-8.52	-11.43	-13.32
3000	-5.26	-5.43	-5.55	-9.88	-13.72	-16.36
3600	-5.31	-5.50	-5.76	-10.29	-13.72	-16.33
4000	-2.30	-2.21	-1.92	-5.93	-8.96	-10.26
4500	-2.52	-2.89	-3.11	-6.32	-9.09	-10.49
5000	-0.11	-0.34	-0.57	-0.93	-2.65	-2.89
5800	2.43	2.05	1.71	5.56	4.88	4.98
6000	4.14	3.96	3.85	10.12	10.18	10.83
6500	6.20	5.71	5.12	14.84	15.56	16.80
7000	7.67	6.85	6.21	20.47	21.94	23.88
7500	9.15	8.36	7.79	26.23	28.62	31.61
8000	11.02	10.32	10.13	33.10	36.74	41.05



ISO 9001 ISO 14001 AS 9100 CERTIFIED

For detailed performance specs & shipping criteria see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 634-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

RF/MICROWAVE COMPONENTS

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCI_Store/terms.jsp.

Power Detector

ZX47-55LN+

Typical Performance Data

Sensitivity vs. Input Power @+25°C						
Measured	@10MHz(mV/dB)			@2000MHz(mV/dB)		
	Output Voltage (V)	Ideal	Deviation from idea	Output Voltage (V)	Ideal	Deviation from idea
-55	2.01	-53.92	-1.08	1.99	-55.00	0.00
-50	1.92	-50.00	0.00	1.88	-50.45	0.45
-45	1.81	-45.60	0.60	1.75	-45.31	0.31
-40	1.70	-40.85	0.85	1.63	-40.28	0.28
-35	1.58	-35.90	0.90	1.51	-35.23	0.23
-30	1.46	-30.83	0.83	1.39	-30.17	0.17
-25	1.33	-25.65	0.65	1.26	-25.00	0.00
-20	1.21	-20.53	0.53	1.14	-20.05	0.05
-15	1.09	-15.35	0.35	1.02	-14.93	-0.07
-10	0.96	-10.00	0.00	0.89	-9.74	-0.26
-5	0.83	-4.55	-0.45	0.76	-4.28	-0.72
0	0.70	0.78	-0.78	0.64	0.85	-0.85
5	0.60	5.11	-0.11	0.54	4.72	0.28
10	0.53	7.76	2.24	0.51	5.88	4.12
15	0.50	9.05	5.95	0.51	5.88	9.12

Sensitivity vs. Input Power @+25°C						
Measured	@6000MHz(mV/dB)			@8000MHz(mV/dB)		
	Output Voltage (V)	Ideal	Deviation from idea	Output Voltage (V)	Ideal	Deviation from idea
-55	2.07	-53.17	-1.83	2.11	-48.77	-6.23
-50	1.99	-50.00	0.00	2.07	-47.17	-2.83
-45	1.88	-45.46	0.46	2.00	-44.21	-0.79
-40	1.76	-40.40	0.40	1.90	-40.00	0.00
-35	1.64	-35.30	0.30	1.79	-35.16	0.16
-30	1.52	-30.20	0.20	1.67	-30.16	0.16
-25	1.39	-25.00	0.00	1.56	-25.11	0.11
-20	1.27	-20.10	0.10	1.44	-20.31	0.31
-15	1.15	-15.02	0.02	1.33	-15.38	0.38
-10	1.02	-9.87	-0.13	1.21	-10.30	0.30
-5	0.90	-4.75	-0.25	1.09	-5.00	0.00
0	0.77	0.52	-0.52	0.96	0.53	-0.53
5	0.65	5.48	-0.48	0.83	5.98	-0.98
10	0.56	9.23	0.77	0.72	10.73	-0.73
15	0.56	9.44	5.56	0.58	16.78	-1.78



For detailed performance specs & shipping criteria see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 534-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

IRF MICROWAVE COMPONENTS

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MC3_Store/terms.jsp.

Power Detector

ZX47-55LN+

Typical Performance Data

POWER IN (dBm)	Slope Vs Input Power Over Temperature								
	Range @ Freq 10MHz			Range @ Freq 500MHz			Range @ Freq 800MHz		
	-40°C	+25°C	+85°C	-40°C	+25°C	+85°C	-40°C	+25°C	+85°C
-55	-20.02	-18.82	-17.62	-21.10	-19.88	-18.18	-8.80	-7.46	-5.82
-50	-20.94	-21.10	-20.92	-23.38	-23.16	-22.78	-15.10	-13.78	-11.86
-45	-22.96	-22.78	-22.58	-24.22	-24.44	-24.48	-20.34	-19.62	-18.26
-40	-23.52	-23.76	-24.00	-24.66	-24.80	-24.98	-23.06	-22.56	-22.32
-35	-24.26	-24.32	-24.14	-24.42	-25.08	-25.22	-23.88	-23.28	-21.40
-30	-24.28	-24.84	-24.96	-24.58	-25.06	-25.38	-24.24	-23.54	-22.36
-25	-23.92	-24.58	-24.60	-23.76	-24.42	-24.86	-22.90	-22.32	-21.50
-20	-24.84	-24.86	-25.34	-24.78	-25.04	-25.18	-23.30	-22.98	-22.44
-15	-25.02	-25.64	-25.84	-25.14	-25.44	-25.74	-24.02	-23.68	-23.38
-10	-25.30	-26.16	-26.30	-25.76	-26.20	-26.30	-24.48	-24.68	-24.66
-5	-24.84	-25.56	-25.52	-23.82	-25.44	-26.18	-25.54	-25.78	-25.96
0	-17.46	-20.74	-21.32	-16.70	-20.58	-22.94	-21.86	-25.38	-27.24
5	-9.10	-12.72	-16.36	-7.76	-11.28	-13.88	-14.98	-22.12	-23.62
10	-4.64	-6.22	-8.32	-3.24	-4.72	-6.06	-28.84	-28.18	-30.88

FREQ (MHz)	Slope Vs Freq Over Temperature Range								
	@ Input Power -45dBm			@ Input Power -25dBm			@ Input Power -5dBm		
	-40°C	+25°C	+85°C	-40°C	+25°C	+85°C	-40°C	+25°C	+85°C
10	-22.96	-22.78	-22.58	-23.92	-24.58	-24.60	-24.84	-25.56	-25.52
250	-24.02	-24.14	-23.82	-23.94	-24.46	-24.80	-24.10	-25.72	-26.46
500	-24.22	-24.44	-24.48	-23.76	-24.42	-24.86	-23.82	-25.44	-26.18
1000	-24.12	-24.68	-24.92	-24.02	-24.50	-24.70	-23.40	-25.38	-26.34
1500	-24.30	-25.04	-25.54	-23.82	-24.54	-24.94	-22.10	-24.62	-25.78
2000	-23.82	-24.38	-24.86	-23.48	-23.96	-24.38	-21.76	-24.86	-26.42
2500	-23.86	-24.32	-24.50	-23.58	-24.02	-24.34	-20.44	-23.90	-25.82
3000	-24.14	-24.44	-24.42	-23.58	-24.06	-24.50	-18.80	-23.02	-25.50
3500	-24.00	-24.22	-24.60	-23.84	-24.30	-24.62	-18.84	-23.12	-25.76
4000	-25.40	-25.38	-24.50	-24.28	-24.86	-25.18	-21.26	-24.58	-26.64
4500	-24.70	-24.84	-24.86	-24.22	-24.78	-24.88	-21.06	-23.98	-25.78
5000	-25.36	-25.50	-25.22	-23.82	-24.26	-24.20	-22.82	-25.36	-26.20
5500	-24.38	-24.76	-24.52	-23.88	-23.98	-23.98	-24.34	-25.74	-25.76
6000	-24.22	-24.50	-24.32	-23.78	-23.72	-23.68	-24.68	-25.50	-25.30
6500	-24.66	-24.66	-24.32	-23.76	-23.64	-23.52	-24.92	-25.34	-25.12
7000	-24.26	-23.72	-22.38	-23.60	-23.56	-23.44	-25.14	-25.32	-25.20
7500	-22.04	-21.06	-19.34	-23.34	-23.20	-22.62	-25.28	-25.44	-25.50
8000	-20.34	-19.62	-18.26	-22.90	-22.32	-21.50	-25.54	-25.78	-25.96



For detailed performance specs & shipping criteria see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 634-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

IFIR MICROWAVE COMPONENTS

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MC3_Store/terms.jsp.

Power Detector

ZX47-55LN+

Typical Performance Data

Output Voltage Change Vs Input Power		
POWER IN (dBm)	Output Voltage Deviation @-40°C relative to +25°C	Output Voltage Deviation @+85°C relative to +25°C
-55	-9.00	5.70
-50	-13.30	13.30
-45	-9.00	10.30
-40	-6.20	7.90
-35	-5.10	6.80
-30	-2.30	5.70
-25	0.40	4.80
-20	2.80	2.70
-15	5.40	1.60
-10	4.80	1.20
-5	7.70	1.30
0	23.20	-6.50
5	44.20	-19.90
10	65.00	-37.50
15	65.00	-38.90

VSWR Vs Freq			
FREQ (MHz)	-40dBm	+25dBm	+85dBm
10	1.04	1.04	1.04
20	1.04	1.03	1.03
50	1.04	1.03	1.03
100	1.04	1.03	1.02
250	1.05	1.04	1.04
500	1.05	1.05	1.07
1000	1.10	1.09	1.10
1500	1.11	1.12	1.12
2000	1.15	1.14	1.14
2500	1.16	1.16	1.15
3000	1.24	1.22	1.22
3500	1.38	1.38	1.37
4000	1.52	1.50	1.48
5000	1.65	1.60	1.59
5500	1.52	1.50	1.49
6000	1.37	1.37	1.38
6500	1.27	1.26	1.25
7000	1.18	1.19	1.15
7500	1.22	1.23	1.21
8000	1.37	1.37	1.32

Temperature Sensor Voltage Vs Ambient	
Temp (°C)	Voltage @ 8000MHz
-55	0.44
-45	0.46
-35	0.48
-25	0.51
-15	0.53
0	0.56
10	0.58
20	0.60
27	0.62
35	0.63
45	0.65
55	0.67
65	0.69
75	0.72
85	0.74
100	0.77



For detailed performance specs & shipping criteria see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 634-4500 Fax (718) 332-4661 www.minicircuits.com Provides ACTUAL Data Instantly at minicircuits.com

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCI_Store/terms.jsp.